



Mikrofonkabel

Microphone cables

Mik-D-Patch Wendelschirm

Verwendung

Für Patch- und Mikrofonanwendungen sowie Rackverkabelungen, sehr dünn und hochflexibel.

Aufbau

Leiter: Cu-Litze, blk.
Leiterraufbau: 18 x 0,10 mm
Aderisolation: PE
Abschirmung: Cu-Wendelschirm, blk.
Mantel: Soft-PVC, schwarz

Technische Eigenschaften

Betriebsspannung: 500 V
Prüfspannung: 1200 V
Kapazität: 60 pF/m

Temperaturbereich: ruhend: -30 °C bis +70 °C
bewegt: -15 °C bis +70 °C

Biegeradius: min. 10 x A-Ø

Aufmachung

Ringe, Trommeln

Mik-D-Patch spiral shield

Application

For patch- and microphone applications as well as rack wiring, slimy and high flexible.

Construction

Conductor: bare stranded copper wire
Structure of conductor: 18 x 0,10 mm
Core insulation: PE
Shield: bare copper spiral screen
Jacket: Soft-PVC, black

Technical characteristics

Operating voltage: 500 V
Testing voltage: 1200 V
Capacity: 60 pF/m

Temperature range: static: -30 °C to +70 °C
dynamic: -15 °C to +70 °C

Bending radius: min. 10 x O.D.

Packaging

Rings, reels

Bestell-Nr. Order-No.	Abmessung dimension	A-Ø O.D.	Gewicht weight	Cu.-Gewicht co.-weight
	(qmm)	(ca. mm)	(kg/km)	(kg/km)
580201409	2 x 0,14	3,0	17,0	9,5