

SmartPro 1kVA 900W Line Interactive Sine Wave UPS, Extended-run & SNMPWEBCARD options, 2U Rack/Tower, LCD, USB, RS232, EPO, 120V

MODEL NUMBER: **SMART1000RML2U**



Description

Tripp Lite SmartPro Line Interactive UPS with enhanced LCD interface offers network-grade power protection for critical server, networking and telecommunications equipment. Line Interactive Uninterruptible Power Supply (UPS) with built-in Auto-Voltage Regulation (AVR) actively corrects brownouts and overvoltages back to usable levels while maintaining a full battery charge in case of power failure. Tripp Lite's unique configuration excels in exceptionally poor-power environments with two separate levels of voltage boost to correct both slight undervoltages and severe brownout conditions. Interactive LCD interface reports UPS operating mode, detailed UPS and site-power data, plus enables a variety of UPS setup and configuration options. Super-fast switchover from line to battery power occurs within milliseconds to maintain operation of connected equipment without interruption or reboot. 97% full load efficiency offers reduced heat emissions and operating costs. Network management interfaces support communications via USB, RS-232 and optional SNMPWEBCARD network interface. HID-compliant USB port enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Network communications ports enable detailed monitoring of equipment load levels, self-test data and utility power conditions. Includes PowerAlert monitoring software and complete cabling. Switched output load banks enable scheduled and real-time remote reboot and load shedding of select outlets. Emergency Power Off (EPO) interface. LCD display panel easily rotates for viewing in rackmount or tower configurations. Audible alarm with push-button momentary alarm-cancel and silent-mode configuration options. Programmable self-test. Field-replaceable, hot-swappable battery modules.

Features

- Tripp Lite SMART1000RML2U line interactive 2U rack/tower UPS with 1000VA / 1kVA / 900 watt capacity
- Line interactive UPS with Automatic Voltage Regulation (AVR) corrects brownouts and overvoltages from 83 to 147V
- NEMA 5-15P input plug; 8 NEMA 5-15R output receptacles, Two independently switchable output load banks
- Maintains uninterrupted operation of connected networking equipment during blackouts, surges, brownouts and overvoltages
- High 97% full load efficiency rating offers reduced power consumption and BTU emissions
- Internal batteries offer 18 minutes at 50% load (450W) and 6.3 minutes at 100% load (900W)

Highlights

- 1kVA / 1000VA / 900W line interactive 2U rack/tower UPS, Sine Wave
- 120V output, Corrects brownouts and overvoltages from 83V to 147V
- 0.9 Power Factor, Interactive LCD interface
- Extended runtime options up to 800W
- 4 post compatible mounting accessories
- 97% line-mode efficiency, 2 switched load banks
- USB, RS232, EPO and slot for SNMPWEBCARD option
- 120V NEMA 5-15P input, 8 NEMA 5-15R outlets

Applications

Ideal for server, networking and telecommunications applications in rackmount, wallmount or tower format

Package Includes

- SMART1000RML2U UPS system
- PowerAlert Software with USB, Serial & EPO cabling
- 4 post rackmount installation kit
- Instruction manual

- Extended runtime is available with optional BP36V15-2U (limit 1); BP36V42-3U (multi-pack compatible); BP36V27-2US (multi-pack compatible), Output is reduced to 1200 watts maximum with external battery packs
- External battery configurations require the use of Tripp Lite's External Battery Configuration Software (see manual)
- Hot-swappable, user-replaceable internal batteries and external battery packs can be replaced with no disruption to connected equipment
- Front panel LCD monitoring screen with MODE and ENTER buttons reports operating mode with 5-bar battery charge graphic, plus 7 selectable screens of detailed UPS and site power information
- LCD interface also supports a number of advanced user setup and operating preferences
- Ships with 4 post rackmount installation hardware; Optional 2POSTRMKITWM enables 2 post rackmount/wallmount installation; Optional 2-9USTAND enables tower placement
- Built-in USB, RS-232 and optional SNMPWEBCARD accessory monitoring options
- HID-compliant USB port enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Included PowerAlert UPS monitoring software; Built-in Emergency Power Off (EPO) interface with cable

Specifications

General Info	
Product Group	UPS SYSTEMS
OUTPUT	
Output Capacity Details	Max output de-rates to 800 watts with external battery packs connected
Output Volt Amp Capacity (VA)	1000
Output kVA Capacity (kVA)	1
Output Watt Capacity (Watts)	900
Power Factor	.9
Nominal Output Voltage(s) Supported	120V
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	120V (+6%, -14%)
Output Voltage Regulation (Battery Mode)	+/-5%
UPS Output Receptacles	8 5-15R outlet(s)
Output Receptacles	Two switchable two outlet 5-15R load banks
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
INPUT	
Rated input current (Maximum Load)	9.2A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P

UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
BATTERY	
Full Load Runtime (min.)	6.3 min. (900w)
Half Load Runtime (min.)	18 min. (450w)
Expandable Battery Runtime	Extended runtime supported via optional external battery packs
External Battery Pack Compatibility	BP36V15-2U (limit 1); BP36V42-3U (multi-pack compatible); BP36V27-2US (multi-pack compatible)
DC System Voltage (VDC)	36
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10 to 90% (typical, full load discharge)
Internal UPS Replacement Battery Cartridge	RBC93-2U
Battery Access	Front panel battery access door
Battery Replacement Description	Hot-swappable, replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 147
Overvoltage Correction	Input voltages between 127 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 104 and 83 are boosted by 14%
LEDS ALARMS & SWITCHES	
Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, frequency, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
Alarm Cancel Operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Switches	3 pushbutton switches control OFF / ON power status, MODE selection and MUTE / ENTER control functions
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	570
EMI / RFI AC Noise Suppression	Yes
AC Suppression Response Time	Instantaneous
PHYSICAL	

Installation Form Factors Supported with Optional Accessories		2 post rackmount (2POSTRMKITWM); Wallmount (2POSTRMKITWM); Tower (2-9USTAND)
Primary Form Factor		Rackmount
UPS Power Module Dimensions (hwd, in.)		3.5 x 17.5 x 13.5
UPS Power Module Dimensions (hwd, cm)		8.9 x 44.4 x 34.3
Rack Height		2U
Secondary Form Factor		Tower (requires 2-9USTAND)
UPS Power Module Weight (lbs.)		45.5
UPS Power Module Weight (kg)		20.7
UPS Shipping Dimensions (hwd / in.)		9 x 23.5 x 23.5
UPS Shipping Dimensions (hwd / cm)		22.9 x 59.7 x 59.7
Shipping Weight (lbs.)		56.5
Shipping Weight (kg)		25.7
Cooling Method		Fan
UPS Housing Material		Steel
ENVIRONMENTAL		
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius	
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius	
Relative Humidity	0 to 95%, non-condensing	
AC Mode BTU / Hr. (Full Load)	89	
Battery Mode BTU / Hr. (Full Load)	540	
AC Mode Efficiency Rating (100% Load)	97%	
COMMUNICATIONS		
Communications Interface	USB (HID enabled); DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface	
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions	
PowerAlert Software	Included	
Communications Cable	USB, DB9 and EPO cabling included	
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications	
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp%20Lite	
LINE / BATTERY TRANSFER		
Transfer Time	4 milliseconds (AC to battery mode), 3 millisecond (Battery to AC mode)	

Low Voltage Transfer to Battery Power (Setpoint)	83
High Voltage Transfer to Battery Power (Setpoint)	147
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks; Schedulable daily hours of economy mode operation
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI)
WARRANTY	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.