


A	14.99	[.590]	+	0.30	[.012]
B	6.60	[.260]	+	0.20	[.008]
C	29.16	[1.148]	+	0.64	[.025]
D	7.44	[.293]	+	0.15	[.006]

CASE DIMENSIONS:


A	18.15	[.715]	+	0.25	[.010]
B	7.05	[.278]	+	0.25	[.010]
C	32.50	[1.280]	+	0.25	[.010]
D	18.90	[.744]	+	0.60	[.024]
E	3.40	[.134]		Ref.	



UNCONTROLLED
DOCUMENT

NET IMPEDANCE (Z)				
Frequency	300 MHz	500 MHz	1 GHz	
Nominal (REF)	274 Ω	350 Ω	256 Ω	
Minimum	- Ω	280 Ω	- Ω	

NET Z,R AND X vs. FREQUENCY



FREQUENCY (MHz)

AGILENT E4981A Impedance/Material Analyzer
HP 16082A-Test Fixture, REF#3899

NOTES:

1. ASSEMBLED PART #: HFA150066-0A2
2. CASE COLOR: BLACK - "0A2"

DIMENSIONS ARE IN mm[INCHES].			
C	REMOVE CORE & CASE P/N REFERENCE	05/17/06	TMB
B	REMOVE NOTES 1, 3, & 4 CHANGE CORE "C" & "D" DIM TOLERANCES TO ± 0.64 [.025] & ± 0.15 [.006] REVISE CASE DIMS A, B, & D ADD DIM E TO CASE	04/01/06	TMB
A	ORIGINAL DRAFT	08/23/04	JRK
REV	DESCRIPTION	DATE	INT

THIS DOCUMENT CONTAINS INFORMATION WHICH IS PROPRIETARY AND CONFIDENTIAL TO STEWARD. NO PRODUCTION OR PUBLICATION OF THIS DOCUMENT IN WHOLE OR IN PART SHALL BE MADE WITHOUT WRITTEN AUTHORIZATION FROM STEWARD.

Steward

PROJECT/PART NUMBER:			
HFA150066-0A2			
DATE:	08/23/04	SCALE:	NTS
CAD #	HFA150066-0A2-C	TOOL #	
PROJECT/PART NUMBER:		REV	C
HFA150066-0A2		PART TYPE:	FERRITE
			SNAP-ON
		DRAWN BY:	JRK
		MATERIAL:	NiZn Ferrite