



VHF TV LINEAR TRANSISTORS


SGS-THOMSON VHF TV/Linear transistors are specifically designed for television broadcast transmitters requiring ultra high linearity. Refractory/gold metallization is employed to assure maximum system availability and ruggedness.




.500 6LFL
(M111)




.500 4L STUD
(M130)




.500 4L .550 STUD
(M164)



2 x .437 x .450 2LFL
(M165)



.400 x .425 8LFL
(M168)



2 x .437 x .450 2LFL
(M175)

55-88 MHz CLASS AB, COMMON EMITTER, VHF TV BAND I

PART NO.	FREQ. (MHz)	P _{OUT} MIN. (W)	P _{IN} (W)	GAIN MIN (dB)	T _{IC} MIN (%)	BIAS		R _{TH(j-c)} MAX (°C/W)	PACKAGE STYLE
						V _{CE} (V)	I _c (mA)		
SD1476	55-88	240	20	12.0	50	32	2 x 400	0.4	M165

174-230 MHz CLASS A, COMMON EMITTER, VHF TV BAND III

PART NO.	FREQ. (MHz)	P _{OUT} MIN (W)	P _{IN} (W)	GAIN MIN (dB)	BIAS		IMD 3 TONES (dBc)	R _{TH(j-c)} MAX (°C/W)	C _{OB} MAX (pF)	PACKAGE STYLE
					V _{CE} (V)	I _c (mA)				
SD1458	225	14	0.55	14	28	2500	-55	1.5	80	M111
SD1455	225	20	3.2	8	25	2500	-51	1.5	85	M130
SD1459	225	30	5.3	7.5	28	3500	-53	1.2	150	M164
SD1456*	225	100	8.0	11.0	28	2 x 100	-51	1.2	80	M168
SD1485*	230	200	16	11.0	32	2 x 500	—	0.45	—	M175

*Class AB

P/N CROSS REFERENCE	
INDUSTRY P/N	SD P/N
TCC3100	SD1456