





4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION					
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.									
LOC		DIST		REVISIONS					
AF		50		P	LTR	DESCRIPTION	DATE	DWN	APVD
				P		REVISED PER ECR-08-030838	30MAR09	HMR	GP
1 SUPPLIED 50,000 PIECES PER REEL. 2 WIRE RANGE IS 1400-3600 CMA CRIMP WIDTH: .090, F TYPE CRIMP HEIGHT: ±.002 = (TOTAL CMA + 7600) / 145,100 FOR APPLICATOR INFORMATION CALL: 1-800-722-1111 FOR PRODUCT INFORMATION CALL: 1-800-522-6752 3 FOREIGN PRODUCTION ONLY.									
									
				SECTION A-A					
3				.000150 MIN NICKEL PLATE		TEMP 3 STEEL		40862-3	
3 OBSOLETE				—		TEMP 3 STEEL		40862-2	
3 OBSOLETE				TIN		TEMP 3 STEEL		40862-1	
				TIN		081 BRASS		40862	
				FINISH		MATERIAL		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN MICHAEL S. FEHER 29SEP2003		Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES				TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
				0 PLC ± - 1 PLC ± - 2 PLC ± .010 3 PLC ± - 4 PLC ± - ANGLES ± 1°		PRODUCT SPEC			
MATERIAL				FINISH		APPLICATION SPEC			
SEE TABLE				SEE TABLE		114-2088			
				WEIGHT		SIZE CAGE CODE DRAWING NO RESTRICTED TO			
				—		A3 00779 C-40862			
				CUSTOMER DRAWING		SCALE 10:1 SHEET 1 OF 1 REV P			