

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
(C) COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.		


PART NUMBER	REV	FIRST USED	TERMINATOR	FEED TYPE	DESCRIPTION
1339548-1	A	-	BENCH & LEADMAKER	MECH POST FEED	HD-I APPLICATOR
7-1339548-1	A	-	BENCH & LEADMAKER	MECH POST FEED	-1 AND SPARE PARTS
7-1339548-7	A	-	-	-	SPARE PARTS KIT

[illegible]

-  1. RECOMMENDED SPARE PARTS.

 2. GREASE RAM, CAM, CAM FOLLOWER AND FEED ROD LIGHTLY.
 3. LUBRICATE DAILY PER THE APPLICATOR INSTRUCTION SHEET SUPPLIED WITH THE APPLICATOR.

VIEW B ROTATED 180°	
POST-FEED 40 mm STROKE LEADMAKER OR BENCH G	POST-FEED 30 mm STROKE K TERMINATOR BENCH MACHINE



LOC		DIST		REVISIONS					DATE		DWN		APVD		
A		66		P	LTR	DESCRIPTION				2-2009		MY		TE	
				A1	ECR-09-002933										
-	1	1	1339548	PRINT, APPLICATOR LOG SHEET				72							
-	1	1	1338705-2	DOCUMENTATION PACKAGE				71							
								70							
								69							
								68							
-	1	1	461264-1	PLATE, IDENTIFICATION				67							
-	2	2	21017-2	SCR,DRIVE(#2X.19)ID PLATE				66							
								65							
-	1	1	986950-1	WASHER, FLAT PRECISION				64							
-	1	1	3-18031-0	SCR,SKT SET(M6X6)RAM				63							
-	1	1	18023-9	SCR,SKT CAP(M4X6)CP DSC				62							
								61							
-	1	1	18024-7	SCR,BHC(M4X10)ANVIL				60							
								59							
-	2	2	1-18023-3	SCR,SHC(M4X16)HOLD DOWN				58							
-	5	5	1-18023-0	SCR,SHC(M4X8)STRIP GUIDE				57							
-	2	2	1-18023-2	SCR,SHC(M4X12)SLUG BLADE				56							
								55							
-	2	2	18029-1	NUT,HEX(M3)DRAG				54							
-	2	2	986965-1	NUT,HEX SL(M4)DRAG STUD				53							
-	2	2	2-18032-2	SCR,SKT SET(M3X10)DRAG				52							
								51							
								50							
-	1	1	18024-3	SCR,BHC(M3X10)CAM				49							
								48							
-	1	1	1338676-1	CAM, POST-FEED 30 & 40 mm ST				47							
-	1	1	1338662-1	APPLICATOR, BASIC (SUBASSY)				46							
-	1	1	690191-1	PLUG, NYLON				45							
-	1	1	1320998-1	RAM				44							
-	1	1	690125-1	WASHER, LAMINATED				43							
-	1	1	690124-1	WASHER, RAM				42							
-	1	1	2-18024-6	SCREW,BHC(M8X25)CRIMPER				41							
-	1	1	23241-1	BALL, STEEL				40							
-	1	1	2-22278-7	SPRING, COMPRESSION				39							
-	1	1	1320922-1	DISC, INSULATION				38							
-	1	1	354777-1	WIRE DISC, PLASTIC				37							
-	1	1	22480-5	WASHER, SPRING				36							
-	1	1	690212-1	POST, RAM				35							
								34							
								33							
-	9	9	18025-2	WASHER,LOCK(M4)SHEAR BL				32							
-	2	2	1-18024-0	SCR,BHC(M4X20)SHEAR PL				31							
								30							
-	2	2	18024-8	SCR,BHC(M4X12)STRIPPER				29							
-	1	1	3-690451-2	SPACER, STRIPPER				28							
-	1	1	240639-1	STRIPPER				27							
								26							
-	2	2	1320906-1	DRAG, STUD				25							
-	1	1	1-1320995-4	STRIP GUIDE				24							
-	1	1	240825-2	PLATE, STRIP HOLD DOWN				23							
-	2	2	4-22281-1	SPRING, DRAG				22							
								21							
-	1	1	1338665-1	DRAG, STOCK				20							
								19							
-	2	2	1338663-3	GUIDE, LOWER STRIP				18							
-	4	4	1-18024-8	SCR,BHC(M6X12)STRIP CD PL				17							
-	1	1	1338708-1	SPACER, SLUG BLADE				16							
								15							
								14							
-	1	1	690481-7	SPACER, HOLD DOWN				13							
-	1	1	23846-1	SPRING, HOLD DOWN				12							
1	-	1	1	240833-4				11							
-	2	2	1-240645-2	SPACER, SHEAR PLATE				10							
1	-	1	1	240642-5				9							
1	1	2	1	1333215-7				8							
-	1	1	1	1-240651-1				7							
-	1	1	1	2-455892-8				6							
-	1	1	1	240641-7				5							
-	1	1	1	238009-1				4							
1	1	2	1	1-456134-9				3							
-	1	1	1	455888-3				2							
1	1	2	1	1-456404-8				1							
-77		-71		-1		PART NO				DESCRIPTION				ITEM NO	
QTY		REQD		PER		ASSY		PARTS LIST							