




MATERIAL LIST:

NO.	PARTS NAME	SPECIFICATION DESCRIPTION
①	CABLE	UL20276 3*(1P*30AWG+D+AL+MYLAR)+7C*30AWG +AL+D+B (AL 60%) OD:6.0±0.2mm COLOR:BLACK
②	DVI CONNECTOR	DVI 12+5 MALE INSULATOR BLACK SOLDER TYPE PIN GOLD PLATED 1u" GOLD PLATED SHELL
③	HD 15P CONNECTOR	HD 15P MALE INSULATOR BLACK SOLDER TYPE PIN GOLD PLATED 1u" GOLD PLATED SHELL
④	SCREW	Ø4*47mm NICKEL PLATED
⑤	SCREW	Ø4*37.7mm NICKEL PLATED
⑥	MOLDING PVC	MOLDING PVC 063 45P COLOR:BLACK
⑦	MOLDING ABS	MOLDING ABS 750 COLOR:BLACK

Marking: Maxxtro C AWM E200765 STYLE 20276 80°C 30V FT2

CN1	WIRE	COLOR	CN2
C1	RED(CEN)		1
C2	GREEN (CEN)		2
C3	BLUE (CEN)		3
C4	WHITE		13
C5	R,G,B/GND		6,7,8
6	BLACK		15
7	RED		12
8	BROWN		14
14	YELLOW		9
15	ORANGE		5,10
16	GREEN		9
SHELL	BRAID		SHELL

ELECTRONIC TEST:

- A.OPEN/SHORT/INTERMITTENCE: 100%.
- B.HI-POT: 300V DC/sec
- C.INSULATION RESISTANCE: 10M ohm (MIN)
- D.CONDUCTIVE RESISTANCE: 5ohm (MAX)

ITEM NO	LENGTH	PVC COLOR	PACKING
103077	3000±50mm	BLACK 0020	BLISTER CARD

REMARK	NO	CHA.NO	SIGNATURE	DATE	
DRAWN BY	Renzhi				SIGN
CHECKED BY					
AUDITED BY		APPROVED BY			
CRAFT		DATE	2011.06.16		PAGE OF

Maxxtro®