


**FOR REFERENCE
ONLY**




**STEWART
CONNECTOR
SYSTEMS, INC.**

R.D. 2, BOX 2020 GLEN ROCK, PENNSYLVANIA 17327

PART NO.: 940-SP-3088R-K1-W
EIGHT CONDUCTOR / EIGHT POSITION LINE CORD MODULE;
CLEAR; FOR ROUND CABLE; FOR CONDUCTORS WITH
MAXIMUM OUTSIDE DIAMETER OF .038 [.965]

R - RADIAL BACK
K1 - KEY OPTION
W - WING



**SPECIFICATIONS OF STEWART CONNECTOR'S
MODULAR PLUGS**

CONTACT MATERIAL: 8% PHOSPHOR BRONZE

CONTACT PLATING: 50 MICRO-INCH (1.27 MICRON)
SELECTIVE 24 CARAT HARD GOLD PLATE IN CONTACT AREA
OVER 100 MICRO-INCH (2.54 MICRON) MINIMUM NICKEL PLATE
PER CURRENT SELECTIVE GOLD PLATING REQUIREMENTS.

PLUG MATERIAL: POLYCARBONATE

PLUG TOLERANCES AND DIMENSIONS: COMPLIES WITH F.C.C REQUIREMENTS
ALL OTHER DIM'S ± 0.005 (± 0.127 MM)
DIM'S WITH ** TO BE CENTRAL ABOUT CENTER LINE

FLAME AUTO EXTINGUISH LEVEL: 94-V0 (U.L. RECOGNIZED-FILE NO. E132408 (N))

OPERATION TEMPERATURE: -40°C TO +125°C

INSERTION/EXTRACTION LIFE: 1000 CYCLES (USING STEWART CONNECTOR JACKS)

CONTACT RESISTANCE: 10 MILLOHMS MAX. (USING STEWART CONNECTOR JACKS)

CURRENT/VOLTAGE: 30 VAC/42 VDC AT 1.5 AMPS