

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
		O		RELEASED(FJ00-1409-97)	07OCT97	S.H H.K
		A		REVISED(FJ00-1740-98)	24SEP98	S.H Y.Y
		B		REVISED(FJ00-1195-00)	17 JUL '00	S.H

NOTE

① MATERIAL

(1) HOUSING : LCP(UL94V-0, BLACK)

(2) CONTACT : PHOSPHOR BRONZE

FINISH : CONTACT AREA ; Au PL. OVER 0.001 MIN. Ni PL.





SOLDERING AREA : 0.001 MIN. TIN-LEAD OVER 0.001 MIN. Ni PL.

(3) G-CONT. WITH RETENTION-LEG : BRASS

FINISH : 0.001 MIN. TIN-LEAD PL. OVER 0.001 MIN. Ni PL.

② INDICATE DATE CODE.

③ THIS DIM. IS 1.6±0.08 WHEN THE CONTACT PUSH TO HOUSING.



注記

① 材料

(1)ハウジング : LCP (UL94V-0, 黒色)

(2)コンタクト : 焼青銅 仕上げ : ニッケル下地めっき0.001以上

接触部 : 金めっき

タイン部 : 半田めっき0.001以上

(3)リテンションレグ付グランドコンタクト : 黄銅


仕上げ : ニッケル下地めっき0.001以上, 半田めっき0.001以上

② デートコード表示

③ ハウジングに押しつけたときの寸法は1.6±0.08とする。

1123283-9	0.0002	80	79	54.2	57.87	66.5	55.27	49.53	66.4	50.165	58.765	62.0	64.7
5-1123283-5	0.00076	40	39	28.8	32.47	41.1	29.87	24.13	41.0	24.765	33.365	36.6	39.3
1123283-5	0.0002	40	39	28.8	32.47	41.1	29.87	24.13	41.0	24.765	33.365	36.6	39.3
PART NO.	Au PL. THK	POS	n	A	B	C	D	E	F	G	H	J	K

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位 : 概
MMMATERIAL
材料TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0-PLC	±0.2:10=<
1-PLC	±0.25:10>,30=<
2-PLC	±0.3:30>
3-PLC	±
4-PLC	±
ANGLES	±3°

FINISH
仕上

DWN 07/OCT/'97

S.HASHIMOTO

CHK 07/OCT/'97

H.KODAMA

APVD 07/OCT/'97

H.KODAMA

PRODUCT SPEC

製品規格

108-5290

APPLICATION SPEC

取付適用規格

WEIGHT

-

CUSTOMER DRAWING

WIRE RANGE
包合電線断面積INSULATION DIA
被覆外径

AMP

Tyco Electronics AMP K.K.

Kawasaki, Japan

NAME

名称

PLUG ASS'Y SMT TYPE, CHAMP.050(I)
BLINDMATE WITH G-CONT.(P.C.B t=0.8mm)

SIZE

A3

CAGE CODE

00779

DRAWING NO

番号

C-1123283

RESTRICTED TO

-

SCALE

尺度

SHEET

1

OF

2

REV

B

