

PJUSB05-4

FEATURES


- SOT-23 6L package allows five separate unidirectional configurations
- Low leakage < 1 μ A@5V
- Breakdown voltage : 6.37V-7.04V@1mA
- Low Capacitance (8.5pF typical)
- ESD Protection Meeting IEC1000-4-2
- Lead free in compliance with EU RoHS 2011/65/EU directive
- Green molding compound as per IEC61249 Std. .
(Halogen Free)

MECHANICAL DATA

- Case : SOT-23 6L, Plastic
- Terminals : Solderable per MIL-STD-750, Method 2026
- Approx. Weight : 0.0005 ounces, 0.014 grams
- Marking : BTW

SOT-23 6L

Unit : inch(mm)




MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Peak Power Dissipation @20 μ s@T _A ≤25 °C (Note 1)	P _{TOT}	150	W
Steady State Power-1 Diode (Note 2)	P _D	385	mW
Thermal Resistance , Junction to Ambient Above 25°C, Derate	R θ _{JA}	212 4.7	°C/W mW/°C
ESD Discharge MIL STD 883C-Method 3015-6 IEC1000-4-2, Air Discharge IEC1000-4-2, Contact Discharge	V _{PP}	16 15 8	kV
Lead Solder Temperature (10 s duration)	T _L	260	°C
Operating Junction and Storage Temperature Range	T _J , T _{STG}	-55 to 150	°C

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

1. Non-repetitive current per Figure 1. Derate per Figure 2.

2. Only 1 diode under power. For all 5 diodes under power, P_D will be 20%. Mounted on FR-4 board with min pad.



PJUSB05-4

ELECTRICAL CHARACTERISTICS

Part Number	Breakdown Voltage V_{BR} @ 1mA(Volts)			Leakage Current I_R @ $V_{RWM} = 5V$	Capacitance@0V Bias	Max V_F @ $I_F=10mA$
	Min.	Nom.	Max.			
	V	V	V		pF	V
PJUSB05-4	6.37	6.7	7.04	1.0	8.5	0.95




Figure 1. Pulse Width




Figure 2. 8 x 20 μs Pulse Waveform




Figure 3. Pulse Derating Curve




Figure 4. Capacitance




Figure 5. Forward Voltage





Figure 6. Clamping Voltage versus Peak Pulse Current (Reverse Direction)

PJUSB05-4

MOUNTING PAD LAYOUT

SOT-23 6L

Unit : inch(mm)



ORDER INFORMATION

- Packing information
 - T/R - 10K per 13" plastic Reel
 - T/R - 3K per 7" plastic Reel

PJUSB05-4

Part No_packing code_Version

PJUSB05-4_R1_00001

PJUSB05-4_R2_00001

PJUSB05-4_S1_00001

PJUSB05-4_S2_00001

For example :

RB500V-40_R2_00001

Part No.

Serial number

Version code means HF

Packing size code means 13"

Packing type means T/R

Packing Code XX				Version Code XXXXX		
Packing type	1 st Code	Packing size code	2 nd Code	HF or RoHS	1 st Code	2 nd ~5 th Code
Tape and Ammunition Box (T/B)	A	N/A	0	HF	0	serial number
Tape and Reel (T/R)	R	7"	1	RoHS	1	serial number
Bulk Packing (B/P)	B	13"	2			
Tube Packing (T/P)	T	26mm	X			
Tape and Reel (Right Oriented) (TRR)	S	52mm	Y			
Tape and Reel (Left Oriented) (TRL)	L	PANASERT T/B CATHODE UP (PBCU)	U			
FORMING	F	PANASERT T/B CATHODE DOWN (PBCD)	D			



PJUSB05-4

Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.