


# EMSL13M2J-137.472M TR



## ELECTRICAL SPECIFICATIONS


|                                                   |                                                                                                                                                                                                                                                                                                                                    |
|---------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Nominal Frequency                                 | 137.472MHz                                                                                                                                                                                                                                                                                                                         |
| Frequency Tolerance/Stability                     | $\pm 50$ ppm Maximum over $-20^{\circ}\text{C}$ to $+70^{\circ}\text{C}$ (Inclusive of all conditions: Calibration Tolerance at $25^{\circ}\text{C}$ , Frequency Stability over the Operating Temperature Range, Supply Voltage Change, Output Load Change, 1st Year Aging at $25^{\circ}\text{C}$ , Reflow, Shock, and Vibration) |
| Aging at $25^{\circ}\text{C}$                     | $\pm 1$ ppm First Year Maximum                                                                                                                                                                                                                                                                                                     |
| Supply Voltage                                    | $+3.3\text{Vdc} \pm 0.3\text{Vdc}$                                                                                                                                                                                                                                                                                                 |
| Input Current                                     | 70mA Maximum (Excluding Load Termination Current)                                                                                                                                                                                                                                                                                  |
| Output Voltage Logic High (Voh)                   | 750mVdc Typical, 600mVdc Minimum                                                                                                                                                                                                                                                                                                   |
| Output Voltage Logic Low (Vol)                    | 25mVdc Typical, 50mVdc Maximum                                                                                                                                                                                                                                                                                                     |
| Rise/Fall Time                                    | 300pSec Typical, 350pSec Maximum (Measured over 20% to 80% of waveform)                                                                                                                                                                                                                                                            |
| Duty Cycle                                        | $50 \pm 5(\%)$ (Measured at 50% of waveform)                                                                                                                                                                                                                                                                                       |
| Load Drive Capability                             | 50 Ohms to ground (Output and Complementary Output)                                                                                                                                                                                                                                                                                |
| Output Logic Type                                 | HCSL                                                                                                                                                                                                                                                                                                                               |
| Logic Control / Additional Output                 | Standby (ST) and Complementary Output                                                                                                                                                                                                                                                                                              |
| Output Control Input Voltage                      | Vih of 70% of Vcc Minimum or No Connect to Enable Output and Complementary Output, Vil of 30% of Vcc Maximum to Disable Output and Complementary Output (High Impedance)                                                                                                                                                           |
| Standby Current                                   | 30 $\mu\text{A}$ Maximum (ST) Without Load                                                                                                                                                                                                                                                                                         |
| Period Jitter (Deterministic)                     | 0.2pSec Typical                                                                                                                                                                                                                                                                                                                    |
| Period Jitter (Random)                            | 2.0pSec Typical                                                                                                                                                                                                                                                                                                                    |
| Period Jitter (RMS)                               | 1.5pSec Typical, 3.0pSec Maximum                                                                                                                                                                                                                                                                                                   |
| Period Jitter (pk-pk)                             | 20pSec Typical, 25pSec Maximum                                                                                                                                                                                                                                                                                                     |
| Period Jitter (Cycle to Cycle)                    | 10pSec Typical                                                                                                                                                                                                                                                                                                                     |
| RMS Phase Jitter (Fj = 637kHz to 10MHz; Random)   | 1.6pSec Typical                                                                                                                                                                                                                                                                                                                    |
| RMS Phase Jitter (Fj = 1.5MHz to 22MHz; Random)   | 0.6pSec Typical                                                                                                                                                                                                                                                                                                                    |
| RMS Phase Jitter (Fj = 1.875MHz to 20MHz; Random) | 0.5pSec Typical                                                                                                                                                                                                                                                                                                                    |
| Start Up Time                                     | 10mSec Maximum                                                                                                                                                                                                                                                                                                                     |
| Storage Temperature Range                         | $-55^{\circ}\text{C}$ to $+125^{\circ}\text{C}$                                                                                                                                                                                                                                                                                    |

## ENVIRONMENTAL & MECHANICAL SPECIFICATIONS

|                              |                                                                   |
|------------------------------|-------------------------------------------------------------------|
| ESD Susceptibility           | MIL-STD-883, Method 3015, Class 2, HBM 2000V                      |
| Flammability                 | UL94-V0                                                           |
| Mechanical Shock             | MIL-STD-883, Method 2002, Condition G, 30,000G                    |
| Moisture Resistance          | MIL-STD-883, Method 1004                                          |
| Moisture Sensitivity Level   | J-STD-020, MSL 1                                                  |
| Resistance to Soldering Heat | MIL-STD-202, Method 210, Condition K                              |
| Resistance to Solvents       | MIL-STD-202, Method 215                                           |
| Solderability                | MIL-STD-883, Method 2003 (Six I/O Pads on bottom of package only) |
| Temperature Cycling          | MIL-STD-883, Method 1010, Condition B                             |
| Thermal Shock                | MIL-STD-883, Method 1011, Condition B                             |
| Vibration                    | MIL-STD-883, Method 2007, Condition A, 20G                        |

# EMSL13M2J-137.472M TR

## MECHANICAL DIMENSIONS (all dimensions in millimeters)



| PIN | CONNECTION           |
|-----|----------------------|
| 1   | Standby (ST)         |
| 2   | No Connect           |
| 3   | Case Ground          |
| 4   | Output               |
| 5   | Complementary Output |
| 6   | Supply Voltage       |

| LINE | MARKING                                                           |
|------|-------------------------------------------------------------------|
| 1    | XXXX or XXXXX<br>XXXX or XXXXX=Ecliptek<br>Manufacturing Lot Code |

Note A: Center paddle is connected internally to oscillator ground (Pad 3).

## Suggested Solder Pad Layout


All Dimensions in Millimeters



All Tolerances are  $\pm 0.1$


# EMSL13M2J-137.472M TR

## OUTPUT WAVEFORM & TIMING DIAGRAM




# EMSL13M2J-137.472M TR

## OUTPUT WAVEFORM & TIMING DIAGRAM



# EMSL13M2J-137.472M TR

## Test Circuit for Tri-State and Complementary Output



Note 1: An external  $0.01\mu F$  ceramic bypass capacitor in parallel with a  $0.1\mu F$  high frequency ceramic bypass capacitor close (less than 2mm) to the package ground and supply voltage pin is required.

Note 2: A low capacitance ( $<12pF$ ), 10X attenuation factor, high impedance ( $>10M\Omega$ ), and high bandwidth ( $>500MHz$ ) passive probe is recommended.


Note 3: Test circuit PCB traces need to be designed for a characteristic line impedance of 50 ohms.

Note 4: A 10 ohm to 33 ohm series resistor is required to limit overshoot.  $R_s$  value is circuit layout dependant.


# EMSL13M2J-137.472M TR

## Tape & Reel Dimensions


Quantity Per Reel: 1,000 units



\*Compliant to EIA 481



## Recommended Solder Reflow Methods



### High Temperature Infrared/Convection

**Ts MAX to TL (Ramp-up Rate)** 3°C/second Maximum

#### Preheat

- Temperature Minimum (Ts MIN) 150°C
- Temperature Typical (Ts TYP) 175°C
- Temperature Maximum (Ts MAX) 200°C
- Time (ts MIN) 60 - 180 Seconds

**Ramp-up Rate (TL to Tp)** 3°C/second Maximum

#### Time Maintained Above:

- Temperature (TL) 217°C
- Time (tL) 60 - 150 Seconds

**Peak Temperature (Tp)** 260°C Maximum for 10 Seconds Maximum

**Target Peak Temperature (Tp Target)** 250°C +0/-5°C

**Time within 5°C of actual peak (tp)** 20 - 40 seconds

**Ramp-down Rate** 6°C/second Maximum

**Time 25°C to Peak Temperature (t)** 8 minutes Maximum

**Moisture Sensitivity Level** Level 1

## Recommended Solder Reflow Methods



### Low Temperature Infrared/Convection 240°C

$T_S$  MAX to  $T_L$  (Ramp-up Rate) 5°C/second Maximum

#### Preheat

- Temperature Minimum ( $T_S$  MIN) N/A
- Temperature Typical ( $T_S$  TYP) 150°C
- Temperature Maximum ( $T_S$  MAX) N/A
- Time ( $t_s$  MIN) 60 - 120 Seconds

Ramp-up Rate ( $T_L$  to  $T_P$ ) 5°C/second Maximum

#### Time Maintained Above:

- Temperature ( $T_L$ ) 150°C
- Time ( $t_L$ ) 200 Seconds Maximum

Peak Temperature ( $T_P$ ) 240°C Maximum

Target Peak Temperature ( $T_P$  Target) 240°C Maximum 2 Times / 230°C Maximum 1 Time

Time within 5°C of actual peak ( $t_P$ ) 10 seconds Maximum 2 Times / 80 seconds Maximum 1 Time

Ramp-down Rate 5°C/second Maximum

Time 25°C to Peak Temperature (t) N/A

Moisture Sensitivity Level Level 1

### Low Temperature Manual Soldering

185°C Maximum for 10 seconds Maximum, 2 times Maximum.

### High Temperature Manual Soldering

260°C Maximum for 5 seconds Maximum, 2 times Maximum.