


Current refinements (click  to remove)

[Search Tips](#) 
 [Region](#)  [USA](#)  [Product Family](#)  [Fork Terminal, Nylon Insulated](#)  [Text Search: 'PN22-2F-M'](#)

Your search criteria matched only one product, shown below.



- Fork design provides for fast and easy installation, without the need to remove fastener
- Metal insulation grip sleeve crimps to wire insulation, providing protection to the crimp joint during high vibration applications
- Internal barrel serrations assure good wire contact and maximum tensile strength
- UL Flammability UL 94V-2/HB, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up to 600 V per UL 486

‡UL and CSA approved tooling/product combinations.

Note: Wire sizes #26 – #22 AWG, are not UL Listed or CSA Certified.

Part Number:	PN22-2F-M
RoHS Compliance Status:	Compliant
Part Description:	Fork Terminal,nylon insulated, 26 – 22 AWG, #2 stud size.
Product Type:	Terminals
CSA Certified:	No
UL Listed:	No
Length (In.):	.66
Width (In.):	.20
Clearance:	.19
Max. Ins.:	.090
Panduit Color Code:	Yellow
Stock:	.02
Stud Size:	#2
Tool:	CT-100A, CT-600-A, CT-1525, CT-2500
Wire Range:	26 – 22 AWG
Min. Order UOM:	PC
Min. Order Qty.:	1000

BOM Qty. (# of Pkgs.)

Add to My Catalog


Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PART NUMBER	STUD SIZE	WIRE RANGE AWG	DIMENSIONS (in.)				
			A <sup>±.03</sup>	W <sup>±.01</sup>	C <sup>±.01</sup>	M <sup>±.02</sup>	H <sup>±.02</sup>
PN22-2F	#2	#26-22	.66 (16.76)	.20 (5.08)	.19 (4.85)	.56 (14.22)	.09 (2.28)

## NOTES

1. RECOMMENDED FOR:
  - A. 300V MAX. VOLTAGE RATING
  - B. #26-22 AWG SOLID OR STRANDED  
COPPER WIRE
  - C. 221°F (105°C) MAX TEMP. RATING
2. MATERIAL:
  - A. STAMPING: .020 (0.51) THK COPPER,  
TIN PLATED.
  - B. HOUSING: YELLOW NYLON
  - C. SLEEVE: TIN PLATED BRASS
3. PACKAGE QUANTITY:   -C = 100  
                                  -M = 1000
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. INSTALLATION TOOLS: CT-520, CT-1525
6. WIRE STRIP LENGTH : 3/16 <sup>+1/32</sup><sub>-0</sub> (4.76 <sup>+0.8</sup><sub>-0</sub>)



A41234\_01

										 <b>PANDUIT</b> CORP.      TINLEY PARK, ILLINOIS			
01		JKD		ADDED CT-1525 TOOL						#26-22 BARREL NYLON INSULATED FORK			
00	7/97	TM	RLS	RELEASED	06083		LCA	RM					
REV	DATE	BY	CHK	DESCRIPTION	ECN #	QA	CUST	PM	APP	DRAWN BY	CHK'D	SCALE	DRAWING NO.
										TSPA	RLS	NONE	A41234