


REV.	DATE	ECR NO.	DESCRIPTION
NC	05/02/00	—	INITIAL RELEASE
A	04/30/08	100014	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex									
8						DRAWN	GRS	04/30/08											
7						CHECKED				PART DESCRIPTION PCB COAXIAL TERMINATION (FOR RG-174, 188, 316/U CABLE)									
6						ISSUED													
5						SHEET	1 OF 1				PART NO. 142293								
4					CAD FILE														
3	FLANGE	BRASS	NICKEL	1	DO NOT SCALE DRAWING		C:/142/142293.DWG				DWG. NO.	142293.DWG		REV.	A	SIZE	A	SCALE	NA
2	BARREL	BRASS	NICKEL	1															
1	PLATE	BRASS	BRT. TIN	1															
	DESCRIPTION	MATERIAL	FINISH	QTY															

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[142293](#)