

# PRECISION POWER WIREWOUND RESISTORS SILICONE COATED 1/2 WATT TO 50 WATT

## 100 SERIES




World's widest range! 0.005Ω ~2MΩ, ±0.005% ~10%, 0.5W ~50W.  
Low cost, available from stock & exclusive **SWIFT™** delivery program.

### OPTIONS

- ☐ Option X: Low Inductance
- ☐ Option P: Increased Pulse Capability
- ☐ Option F: Flameproof Coating UL94V-0
- ☐ Option ER: 100-Hour Burn-In
- ☐ Option B: Increased Power
- ☐ Radial leads (opt.R), low thermal emf (opt.E), matched sets, custom marking, cut & form, Hi-Rel screening, non-standard values, high-voltage, etc. Customized components are RCD's speciality!

**DERATING** (derate W/V/A ratings when ambient temp >25°C):  
Char. U is max. power for ±0.5% typ. operational life stability & 275°C hotspot;  
Char. V is max. power for ±3% stability & 350°C hotspot



| RCD Type  | MIL Type <sup>5</sup> | Std. Wattage Ratings <sup>10</sup> |        | Opt.B Wattage Ratings <sup>10</sup> |        | Resistance Range <sup>6,7</sup> | Maximum Voltage Rating <sup>1,6</sup> | DIMENSIONS [Numbers in brackets are mm] |                                    |                             |                    |
|-----------|-----------------------|------------------------------------|--------|-------------------------------------|--------|---------------------------------|---------------------------------------|-----------------------------------------|------------------------------------|-----------------------------|--------------------|
|           |                       | Char.U                             | Char.V | Char.U                              | Char.V |                                 |                                       | A <sup>3</sup>                          | C <sup>2</sup>                     | D <sup>8</sup> ± .003 [.08] |                    |
|           |                       |                                    |        |                                     |        |                                 |                                       | ± .062 [1.58]                           | 110-155: ± .032<br>156-190: ± .045 | Std.                        | Optional           |
| 102       | -                     | 0.5                                | 0.8    | 0.8                                 | 1.0    | .01Ω - 2K                       | 30V                                   | .16 ± .03 [4 ± .8]                      | .07 ± .02 [1.8 ± .5]               | .020                        | -                  |
| 110       | RW81 (110B)           | 0.8                                | 1.0    | 1.5                                 | 2.0    | .01Ω - 8K                       | 40V                                   | .24 ± .03 [6 ± .8]                      | .085 [2.16]                        | .020                        | .024 (opt. 22)     |
| 115       | -                     | 1.0                                | 1.2    | 1.5                                 | 2.0    | .01Ω - 12K                      | 45V                                   | .312 [7.92]                             | .085 [2.16]                        | .020                        | .024 (opt. 22)     |
| 120       | -                     | 1.0                                | 1.2    | -                                   | -      | .01Ω - 15K                      | 50V                                   | .344 [8.74]                             | .096 [2.44]                        | .020                        | .024 (opt. 22)     |
| Stock 125 | RW70 (125B RW80)      | 1.5                                | 1.8    | 2.0                                 | 2.5    | .01Ω - 20K                      | 55V                                   | .385 [9.78]                             | .096 [2.44]                        | .020                        | .024 (opt. 22)     |
| 130       | -                     | 1.6                                | 2.0    | -                                   | -      | .01Ω - 22K                      | 65V                                   | .530 [13.5]                             | .096 [2.44]                        | .020                        | .024 (opt. 22)     |
| Stock 133 | -                     | 2.0                                | 3.0    | 3.0                                 | 4.0    | .005Ω - 20K                     | 80V                                   | .355 [9.00]                             | .156 [3.96]                        | .031                        | .024 (opt. 22)     |
| Stock 135 | RW69                  | 3.0                                | 4.0    | 4.0                                 | 5.0    | .005Ω - 40K                     | 140V                                  | .500 [12.7]                             | .188 [4.78]                        | .031                        | .024(22), .040(18) |
| 140       | RW79                  | 3.0                                | 4.0    | 4.0                                 | 5.0    | .005Ω - 50K                     | 140V                                  | .550 [14.2]                             | .188 [4.78]                        | .031                        | .040 (opt. 18)     |
| 145       | -                     | 3.5                                | 4.5    | 4.5                                 | 6.5    | .005Ω - 60K                     | 180V                                  | .770 [19.6]                             | .188 [4.78]                        | .031                        | .040 (opt. 18)     |
| 150       | -                     | 3.5                                | 4.5    | 5.0                                 | 7.0    | .005Ω - 60K                     | 150V                                  | .500 [12.7]                             | .225 [5.72]                        | .040                        | .032 (opt. 20)     |
| 155       | -                     | 4.0                                | 5.0    | 6.0                                 | 8.0    | .005Ω - 100K                    | 210V                                  | .625 [15.9]                             | .225 [5.72]                        | .040                        | .032 (opt. 20)     |
| Stock 156 | -                     | 5.0                                | 6.0    | -                                   | -      | .005Ω - 150K                    | 300V                                  | .800 [20.3]                             | .250 [6.35]                        | .040                        | .032 (opt. 20)     |
| Stock 160 | RW74                  | 5.0                                | 7.0    | 7.0                                 | 10     | .005Ω - 200K                    | 400V                                  | .875 [22.2]                             | .312 [7.92]                        | .040                        | .032 (opt. 20)     |
| 165       | RW67                  | 6.0                                | 7.5    | -                                   | -      | .005Ω - 220K                    | 450V                                  | 1.000 [25.4]                            | .312 [7.92]                        | .040                        | .032 (opt. 20)     |
| 170       | -                     | 7.0                                | 9.0    | 10                                  | 12     | .005Ω - 300K                    | 550V                                  | 1.200 [30.9]                            | .312 [7.92]                        | .040                        | .032 (opt. 20)     |
| 171       | -                     | 7.0                                | 8.5    | -                                   | -      | .005Ω - 250K                    | 700V                                  | 1.660 [42.2]                            | .208 [5.28]                        | .031                        | .040 (opt. 18)     |
| 172       | -                     | 8.5                                | 10     | -                                   | -      | .005Ω - 400K                    | 900V                                  | 2.100 [53.3]                            | .225 [5.72]                        | .031                        | .040 (opt. 18)     |
| Stock 173 | -                     | 9.0                                | 11     | 12                                  | 14     | .005Ω - 400K                    | 650V                                  | 1.550 [39.4]                            | .300 [7.62]                        | .040                        | .032 (opt. 20)     |
| Stock 175 | RW68, 78              | 10                                 | 13     | 15                                  | 18     | .005Ω - 500K                    | 900V                                  | 1.720 <sup>4</sup> [43.7]               | .350 <sup>4</sup> [8.89]           | .040                        | .032 (opt. 20)     |
| 176       | -                     | 10                                 | 12     | -                                   | -      | .005Ω - 500K                    | 800V                                  | 1.875 [47.6]                            | .300 [7.62]                        | .040                        | .032 (opt. 20)     |
| 178       | -                     | 13                                 | 15     | -                                   | -      | .01Ω - 750K                     | 1150V                                 | 2.410 [61.2]                            | .350 [8.89]                        | .040                        | .032 (opt. 20)     |
| 180       | RW56                  | 14                                 | 16     | 16                                  | 20     | .01Ω - 800K                     | 1000V                                 | 2.100 [53.3]                            | .500 [12.7]                        | .040                        | -                  |
| 185       | -                     | 20                                 | 25     | -                                   | -      | .015Ω - 1M                      | 1350V                                 | 2.800 [71.1]                            | .500 [12.7]                        | .040                        | -                  |
| 186       | -                     | 25                                 | 30     | -                                   | -      | .010Ω - 1M                      | 1400V                                 | 4.060 [103]                             | .350 [8.89]                        | .040                        | .032 (opt. 20)     |
| 190       | -                     | 40                                 | 50     | -                                   | -      | .025Ω - 2M                      | 1500V                                 | 5.000 [127]                             | .500 [12.7]                        | .040                        | -                  |

<sup>1</sup> Working voltage=(PR)<sup>1/2</sup>, not to exceed max rating (multiply by 0.7 for Opt.X) <sup>2</sup> Allow .032" additional for Opt X, Opt 33, or values <1Ω <sup>3</sup> Coating overflow onto each lead <2x D typ <sup>4</sup> Performance is typical for Char.U with tol ≤1%, & is dependent on resis, options, etc. Consult factory for Char.V & tol >1% <sup>5</sup> Military p/n's are given for reference only & do not imply qualification or exact interchangeability <sup>6</sup> Increased range avail <sup>7</sup> Resis value measured at 3/8" ±1/16" from each end of body <sup>8</sup> Heavier lead gauge option is recommended on low values to enable lower leadwire resis, increased current, & improved TC <sup>9</sup> Lead length applies to bulk packaged units (taped parts generally have shorter leads, refer to taping spec.) <sup>10</sup> Series 100 has dual power rating depending on temp. rise & stability requirements; derate 50% to ensure high reliability & operational life stability

### TYPICAL PERFORMANCE <sup>4</sup>

|                                                                            |                                                                                                                                                                                                             |
|----------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Operational Life (Char.U)                                                  | ±0.5% (±1% on Opt.B & sizes ≥10W)                                                                                                                                                                           |
| Thermal Shock                                                              | ±0.2%                                                                                                                                                                                                       |
| Moisture Resistance                                                        | ±0.2%                                                                                                                                                                                                       |
| Shock and Vibration                                                        | ±0.1%                                                                                                                                                                                                       |
| Overload, 5 Sec                                                            | 5x rated W 102-156, 10x W 160-190                                                                                                                                                                           |
| Dielectric Strength: type 102-130                                          | 300V (for 500V specify opt.23)                                                                                                                                                                              |
| Dielectric Strength: type 133-190                                          | 500V (for 1KV specify opt.33)                                                                                                                                                                               |
| Max. Current (not to exceed wattage or voltage rating)                     | Resistors with .020" lead dia = 11A, .024" = 15A, .032" = 22A, .040" = 30A                                                                                                                                  |
| TCR: temp coefficient of resistance element, tol ≤1% (contact factory >1%) | ≥10Ω 20ppm (5 & 10ppm avail.)<br>1-9.9Ω 50ppm (10, 20, 30ppm avail.)<br>0.1-.99Ω 90ppm (20, 30, 50 ppm avail.)<br>050-.099Ω 300ppm (50, 100, 200ppm avail.)<br>.01Ω -.049Ω 600ppm (100, 200, 300ppm avail.) |

### P/N DESIGNATION:

**135** ☐ - **102** - **J** **B** ☐ **W**

**RCD Type** \_\_\_\_\_

**Options:** X, R, V, P, F, ER, E, B, 76, 75, 33, 22, 20, 18 (leave blank if standard)

**Resis. Code 1% & tighter tols:** 3 signif. digits & multiplier, e.g. R100= 0.1Ω, 1R00= 1Ω, 1000= 100Ω, 1001= 1KΩ.

**2%-10%:** 2digits & multiplier (R10= .1Ω, 1R0=1Ω, 100=10Ω, 102=1K). Use extra digits as needed: R005, R0075, R012, etc.

**Tolerance:** K=10%, J=5%, H=3%, G=2%, F=1%, D=0.5%, C=0.25%, B=0.1%, A=0.05%, Q=0.02%, T=0.01%, V= .005%

**Packaging:** B= Bulk, T= T&R (avail. on type 102 to 176)

**Optional TC:** 5= 5ppm, 10= 10ppm, 20= 20ppm, 30= 30ppm, 50= 50ppm, 101= 100ppm, 201=200ppm (leave blank if std)

**Termination:** W=RoHS (std), Q= Tin/Lead (leave blank if both acceptable)

RCD Components Inc, 520 E.Industrial Park Dr, Manchester, NH, USA 03109 [rccdcomponents.com](http://rccdcomponents.com) Tel: 603-669-0054 Fax: 603-669-5455 Email: [sales@rccdcomponents.com](mailto:sales@rccdcomponents.com)

FA039H Sale of this product is in accordance with GF-061. Specifications subject to change without notice.