



MX23L1611


3.3 Volt 16-Mbit (2M x 8 / 1M x 16) Mask ROM with Page Mode

FEATURES

- Bit organization
 - 2M x 8 (byte mode)
 - 1M x 16 (word mode)
- Fast access time
 - Random access: 100ns (max.)
 - Page access: 30ns (max.)
- Page Size
 - 8 words per page
- Current
 - Operating: 40mA
 - Standby: 15uA
- Supply voltage
 - 100ns @ 3.0V ~ 3.6V
 - 120ns @ 2.7V ~ 3.6V
- Package
 - 44 pin SOP (500mil)
 - 48 pin TSOP (12mm x 20mm)

PIN CONFIGURATION

44 SOP



ORDER INFORMATION

Part No.	Access Page	Access	Package
	Time	Time	
MX23L1611MC-10	100ns	30ns	44 pin SOP
MX23L1611MC-12	120ns	50ns	44 pin SOP
MX23L1611MI-12*	120ns	50ns	44 pin SOP
MX23L1611TC-10	100ns	30ns	48 pin TSOP
MX23L1611TC-12	120ns	50ns	48 pin TSOP
MX23L1611TI-12*	120ns	50ns	48 pin TSOP

*Note: Industrial grade's temperature is -40°C~85°C


PIN DESCRIPTION

Symbol	Pin Function
A0~A19	Address Inputs
D0~D14	Data Outputs
D15/A-1	D15 (Word Mode)/ LSB Address (Byte Mode)
CE	Chip Enable Input
OE	Output Enable Input
Byte	Word/ Byte Mode Selection
VCC	Power Supply Pin
VSS	Ground Pin
NC	No Connection


MODE SELECTION

CE	OE	Byte	D15/A-1	D0~D7	D8~D15	Mode	Power
H	X	X	X	High Z	High Z	-	Stand-by
L	H	X	X	High Z	High Z	-	Active
L	L	H	Output	D0~D7	D8~D15	Word	Active
L	L	L	Input	D0~D7	High Z	Byte	Active

48 TSOP (Normal Type)



BLOCK DIAGRAM



ABSOLUTE MAXIMUM RATINGS

Item	Symbol	Ratings
Voltage on any Pin Relative to VSS	VIN	-1.3V to VCC+2.0V (Note)
Ambient Operating Temperature	Topr	-40 °C to 85 °C
Storage Temperature	Tstg	-65 °C to 125 °C

Note: Minimum DC voltage on input or I/O pins is -0.5V. During voltage transitions, inputs may undershoot VSS to -1.3V for periods of up to 20ns. Maximum DC voltage on input or I/O pins is VCC+0.5V. During voltage transitions, input may overshoot VCC to VCC+2.0V for periods of up to 20ns.

DC CHARACTERISTICS (Ta = -10 °C ~ 70 °C, VCC = 3.0V~3.6V)

Item	Symbol	MIN.	MAX.	Conditions
Output High Voltage	VOH	2.4V	-	IOH = -0.4mA
Output Low Voltage	VOL	-	0.4V	IOL = 1.6mA
Input High Voltage	VIH	2.2V	VCC+0.3V	
Input Low Voltage	VIL	-0.3V	0.2 x VCC	
Input Leakage Current	ILI	-	5uA	0V, VCC
Output Leakage Current	ILO	-	5uA	0V, VCC
Operating Current	ICC1	-	40mA	tRC = 100ns, all output open
Standby Current (TTL)	ISTB1	-	1mA	$\overline{CE}$ = VIH
Standby Current (CMOS)	ISTB2	-	15uA	$\overline{CE}$ > VCC-0.2V
Input Capacitance	CIN	-	10pF	Ta = 25 °C, f = 1MHZ
Output Capacitance	COUT	-	10pF	Ta = 25 °C, f = 1MHZ


AC CHARACTERISTICS (Ta = -10 °C ~ 70 °C, VCC = 3.0V~3.6V)

Item	Symbol	23L1611-10		23L1611-12	
		MIN.	MAX.	MIN.	MAX.
Read Cycle Time	tRC	100ns	-	120ns	-
Address Access Time	tAA	-	100ns	-	120ns
Chip Enable Access Time	tACE	-	100ns	-	120ns
Page Mode Access Time	tPA	-	30ns	-	50ns
Output Enable Time	tOE	-	30ns	-	50ns
Output Hold After Address	tOH	0ns	-	0ns	-
Output High Z Delay	tHZ	-	20ns	-	20ns

Note: Output high-impedance delay (tHZ) is measured from OE or CE going high, and this parameter guaranteed by design over the full voltage and temperature operating range - not tested.

AC Test Conditions

Input Pulse Levels	0.4V~ 2.6V
Input Rise and Fall Times	10ns
Input Timing Level	1.4V
Output Timing Level	1.4V
Output Load	See Figure



Note:


No output loading is present in tester load board.

Active loading is used and under software programming control.


Output loading capacitance includes load board's and all stray capacitance.

TIMING DIAGRAM

RANDOM READ




PAGE READ




PACKAGE INFORMATION

44-PIN PLASTIC SOP



48-PIN PLASTIC TSOP



REVISION HISTORY

REVISION	DESCRIPTION	PAGE	DATE
1.5	Temperature range is revised as -10°C~70°C	P3	NOV/27/1998
1.6	Output hold after address (tOH) spec is revised as 0ns(min.) 120ns speed grade's voltage range is revised as 2.7V~3.6V	P3 P1	JAN/22/1999
1.7	DC characteristics Standby current (ISTB2):5uA-->15uA	P1,3	Dec/30/1999
1.8	Modify Package Information	P5~6	JUL/18/2001



MX23L1611

MACRONIX INTERNATIONAL CO., LTD.

HEADQUARTERS:

TEL: +886-3-578-6688

FAX: +886-3-563-2888

EUROPE OFFICE:

TEL: +32-2-456-8020

FAX: +32-2-456-8021

JAPAN OFFICE:

TEL: +81-44-246-9100

FAX: +81-44-246-9105

SINGAPORE OFFICE:

TEL: +65-348-8385

FAX: +65-348-8096

TAIPEI OFFICE:

TEL: +886-2-2509-3300

FAX: +886-2-2509-2200

MACRONIX AMERICA, INC.

TEL: +1-408-453-8088

FAX: +1-408-453-8488

CHICAGO OFFICE:

TEL: +1-847-963-1900

FAX: +1-847-963-1909

[http : //www.macronix.com](http://www.macronix.com)