




- 1 FLAME RETARDANT 94V-0 RATED THERMOPLASTIC; BLACK.
- 2 2.54µm [.000100] MIN BRIGHT TIN-LEAD ON TERMINATION END, 0.76µm [.000030] MIN GOLD ON CONTACT AREA, ALL OVER 1.27µm [.000050] MIN NICKEL.
- 3 NO SLOT ON THIS END FOR 10 AND 14 POSITION HOUSINGS.
- 4 NO SLOT FOR SNAP-IN POLARIZER ON THIS END FOR 10 AND 14 POSITION HOUSINGS.
- 5. FOR MILITARY POLARIZATION, ORDER SNAP-IN POLARIZER 499991-2 (BULK PACK OF 50).
- 6 POSITION NO 1 INDICATOR.
- 7 COORDINATE DIMENSION APPLIES FROM CENTER OF ACTUAL FEATURE.
- 8 PHOSPHOR BRONZE PER QQ-B-750.
- 9 STRAIN RELIEF 111547 MUST BE ORDERED SEPARATELY.
- 10 2.54µm [.000100] MIN TIN ON TERMINATION END, 0.76µm [.000030] MIN GOLD ON CONTACT AREA, ALL OVER 1.27µm [.000050] MIN NICKEL.
- 11 OBSOLETE
- 12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

CONTACT FINISH	AREA	10	10	89.59 [3.527]	81.13 [3.194]	36.83 [1.450]	29	59	60	2-111492-6	
			10	78.03 [3.072]	68.43 [2.694]	30.48 [1.200]	24	49	50	2-111492-5	
			10	70.41 [2.772]	60.81 [2.394]	26.67 [1.050]	21	43	44	2-111492-4	
			10	65.33 [2.572]	55.73 [2.194]	24.13 [.950]	19	39	40	2-111492-3	
			10	57.71 [2.272]	48.11 [1.894]	20.32 [.800]	16	33	34	2-111492-2	
			10	52.63 [2.072]	43.03 [1.694]	17.78 [.700]	14	29	30	2-111492-1	
			10	47.55 [1.872]	37.95 [1.494]	15.24 [.600]	12	25	26	2-111492-0	
			10	45.01 [1.772]	35.41 [1.394]	13.97 [.550]	11	23	24	1-111492-9	
			11	10	39.93 [1.572]	30.33 [1.194]	11.43 [.450]	9	19	20	1-111492-8
			10	34.85 [1.372]	25.25 [.994]	8.89 [.350]	7	15	16	1-111492-7	
12	SUPERCEDED	10	32.31 [1.272]	22.71 [.894]	7.62 [.300]	6	13	14	1-111492-6		
		10	27.23 [1.072]	17.63 [.694]	5.08 [.200]	4	9	10	1-111492-5		
		11	10	95.81 [3.772]	86.21 [3.394]	39.37 [1.550]	31	63	64	1-111492-4	
		11	2	95.81 [3.772]	86.21 [3.394]	39.37 [1.550]	31	63	64	1-111492-3	
		11	2	89.59 [3.527]	81.13 [3.194]	36.83 [1.450]	29	59	60	1-111492-2	
		11	2	78.03 [3.072]	68.43 [2.694]	30.48 [1.200]	24	49	50	1-111492-1	
		2	70.41 [2.772]	60.81 [2.394]	26.67 [1.050]	21	43	44	1-111492-0		
		11	2	65.33 [2.572]	55.73 [2.194]	24.13 [.950]	19	39	40	111492-9	
		11	2	57.71 [2.272]	48.11 [1.894]	20.32 [.800]	16	33	34	111492-8	
		12	SUPERCEDED	2	52.63 [2.072]	43.03 [1.694]	17.78 [.700]	14	29	30	111492-7
12	SUPERCEDED	12	47.55 [1.872]	37.95 [1.494]	15.24 [.600]	12	25	26	111492-6		
		12	45.01 [1.772]	35.41 [1.394]	13.97 [.550]	11	23	24	111492-5		
		11	2	39.93 [1.572]	30.33 [1.194]	11.43 [.450]	9	19	20	111492-4	
		11	2	34.85 [1.372]	25.25 [.994]	8.89 [.350]	7	15	16	111492-3	
		12	SUPERCEDED	2	32.31 [1.272]	22.71 [.894]	7.62 [.300]	6	13	14	111492-2
		11	2	27.23 [1.072]	17.63 [.694]	5.08 [.200]	4	9	10	111492-1	
		CONTACT FINISH	E	D	C	B	A	NO OF POSN	PART NUMBER	A	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. OBERMAN 8-9-90	Tyco Electronics Corporation	
CHK F. M. HEINEY 11-28-90		Harrisburg, PA 17105-3608		
APVD -		NAME		
DIMENSIONS: mm [INCHES]		PRODUCT SPEC 108-1336		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-7011		
0 PLC ± -		SIZE CAGE CODE DRAWING NO		
1 PLC ± -		A1 00779 111492		
2 PLC ± 0.13[.005]		RESTRICTED TO		
3 PLC ± -		WEIGHT -		
4 PLC ± -		CUSTOMER DRAWING		
MATERIAL MOLDED PARTS: Δ		SCALE 4:1 SHEET 1 OF 1 REV G3		
FINISH CONTACTS: SEE TABLE				