

PU-Series
PU II 1R 130V/40kA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Class II/III surge protection with varistors, **
** with U_C: 130 V**

- Plug-in varistor, top section
- Coded voltage levels, diverse voltage
- high energy absorption with short time to sparkover
- insert can be rotated through 180°;
- no follow current
- installed in Insta distributor
- thermal protection
- Suitable for 120/240V mains systems

General ordering data

Order No.	8859960000
Type	PU II 1R 130V/40kA
Version	PU-Series, Surge protection, Low voltage, 120 V, with telecomm. contact
GTIN (EAN)	4032248583850
Qty.	1 pc(s).

PU-Series
PU II 1R 130V/40kA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	18 mm	Height	97 mm
Depth	64 mm	Net weight	120 g

Temperatures

Operating temperature	-40 °C...+70 °C	Storage temperature	-40 °C...+85 °C
-----------------------	-----------------	---------------------	-----------------

Discharge surge current of top part

Limiting discharge current (8/20 µs) $I_{\max}$	40 kA	Rated discharge current (8/20 µs) I_N	20 kA
---	-------	---	-------

General data

Colour	Arrester red, Black	Design	Installation housing; 1TE
Height with TS 35	63 mm	Lightning arrester	No
Mounting rail	TS 35, TS 35 x 15, TS 35 x 7.5	Optical function display	green = OK; red = arrester is defective - replace
Protection degree	IP 20	Segment	Power distribution

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

technical data

Rated voltage (AC)	130 V	Rated voltage	120 V
Max. continuous voltage, U_c (AC)	130 V	Max. continuous voltage, U_c (DC)	170 V
Highest continuous voltage (AC)	130 V	Temporary surge voltage (over-voltage) - TOV	150 V
Limiting discharge current (8/20 µs) $I_{\max}$	40 kA	Max. discharge surge current per path 8/20 µs (N-PE)	40 kA
Combined pulse U_{OC}	6 kV	Rated discharge current (8/20 µs) I_N	20 kA
Fuse, max.	125 A gL	Discharge current, nominal, per path, (8/20 µs)	20 kA
Discharge current, max. (8/20 µs)	40 kA	Protection level at 5kA (U_p)	< 500 V
Protection level at I_N (U_p)	< 850 V	Signalling contact	250 V 1A 1CO
Colour	Arrester red, Black	AC/DC/UC	AC
Requirements class, acc. to EN 61643-11	T2, T3	Requirements category acc. to IEC 61643-11	Type II, Type III
Response time	≤ 25 ns	Cross-section	25 mm ²

Connection data

Clamping range, rated connection	25 mm ²	Clamping range, rated connection, min.	4 mm ²
Clamping range, rated connection, max.	16 mm ²	Wire connection cross section, stranded, rated connection, min.	4 mm ²
Wire connection cross section, stranded, rated connection, max.	25 mm ²	Tightening torque, min.	2.5 Nm
Tightening torque, max.	3 Nm	Stripping length, rated connection	15 mm
Wire connection cross section, finely stranded, max.	25 mm ²		

PU-Series
PU II 1R 130V/40kA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Power protection Class III

Combined pulse U_{OC}	6 kV	Max. continuous voltage, U_c (AC)	130 V
Max. continuous voltage, U_c (DC)	170 V	Rated voltage (AC)	130 V

Connection data, remote alert

Connection type [remote alert]	pluggable	Max. torque [remote alert]	0.25 Nm
Stripping length [remote alert]	6 mm	Cross-section for connected wire, solid core, min. [remote alert]	0.2 mm ²
Cross-section for connected wire, solid core, max. [remote alert]	1.5 mm ²		

Classifications

ETIM 3.0	EC000941	UNSPSC	30-21-19-21
eClass 5.1	27-13-08-01	eClass 6.2	27-13-08-02
eClass 7.1	27-14-02-01		

Approvals

Approvals



ROHS

Conform

Downloads

Package insert	Instruction sheet PU II
Declaration of Conformity	K294_09_09.pdf
EPLAN	8859960000.ema

PU-Series
PU II 1R 130V/40kA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Electric symbol

