



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	CABLE TIE		DIMENSIONS				COLOR	WEIGHT grams/100pcs
	MIN TENSILE	MAX BUNDLE	'A'	'B' (REF)	'C' (REF)	'D' (REF)		
PUM-049-C2S-_30	50 LBS (222 N)	2.0 " (51 MM)	13.8	7.2	16.5	193	BLACK	140.0



NOTES:

1. SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.
2. (*) DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINK MARKS.
3. APPLICATION SPECIFICATION:
A. NOMINAL HOLE DIAMETER: 4.6 - 4.9 mm
B. NOMINAL PANEL THICKNESS: 0.7 - 3.0 mm



SCALE 1:2

TITLE	
PUM-049-C2S-_30 PUSH MOUNT/CABLE TIE ASSEMBLY	
CUSTOMER DRAWING	
ITEM REVISION NAME	10B015JW/00
DATASET FILE NAME	10B015JW_DC/00 - 10B015JW_REVR
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE METRIC.	
.X ± 0.5	.XXX ± - - -
.XX ± - - -	ANGLES ± - - -
THIRD ANGLE PROJECTION	
DRAWING NUMBER: 10B015JW	
DRAWN BY BWG	DATE 6/04/13
CHK RTFI	SCALE 1:1 UNLESS NOTED
SHT 1 OF 1	
SIZE A	

R	6/04/13	BWG	MPH	RTFI	DRAWING RELEASED.	10B015JW/R
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN