


CCM03 MK2 Series

Features

- **SIM/SAM card acceptance**
- **Hinged and fixed covers**
- **Compatible with pick and place and lead free soldering**

Typical Applications

- **Handheld products**
- **Identification**
- **POS**
- **Automotive**



Mechanical

Number of Contacts	6 or 8
Mechanical life, hinged cover	10,000 cycles min
Mechanical life, fixed cover	50,000 cycles
Card insertion force	Hinged cover: 1N max Fixed cover: 3N max
Card extraction force	Hinged cover: 1N max Fixed cover: 0,80N min / 3N max
Contact force	0,25N min / 0,50N max
Slide locking force	2N min / 6N max
Vibration Frequency	1,8N max. for complete depression 10 to 500 Hz. Acceleration 50m/s ² Duration 6 hours - amplitude 0,35 mm
Max electrical discontinuity	1μs
Shock	Peak value 500 m/s ² – Duration 11 ms 3 shocks in each direction of each axis

Switch Electrical Data

Card detection switch	Normally open
Contact resistance	100 mΩ max
Dielectric strength	250 Vrms min
Current rating	1 mA min / 10m A max
Maximum power	0.2 VA

Environment Data

Operating temperature	-40°C to +85°C
Damp heat	IEC 512 test number 11c (10 days)
Salt mist	IEC 512 test number 11f (96 hours)
RoHS compliant	

Soldering Process

Compatible with lead free SMT soldering process

Contact Electrical Data

Insulation resistance	1,000 MΩ min
Resistance	100 mΩ max
Current rating	10 μA min / 1 A max
Dielectric strength	750 Vrms min




Designation	Contact Plating	Cover	# of Contacts	PCB Version	Card Presence Switch	Operating Life	Total Height (mm)	Dim. (mm)	Packaging
CCM03-3001LFT	inlay	hinged	6		without	10,000	2,55	17,2 x 29,65	reels of 1,000 pcs
CCM03-3002LFT	inlay	hinged	6	2 plastic pegs	without	10,000	2,55	17,2 x 29,65	reels of 1,000 pcs
CCM03-3003LFT	inlay	hinged	8		without	10,000	2,55	17,2 x 29,65	reels of 1,000 pcs
CCM03-3004LFT	inlay	hinged	8	2 plastic pegs	without	10,000	2,55	17,2 x 29,65	reels of 1,000 pcs
CCM03-3009LFT	gold	hinged	6		without	10,000	2,55	17,2 x 29,65	reels of 1,000 pcs
CCM03-3010LFT	gold	hinged	6	2 plastic pegs	without	10,000	2,55	17,2 x 29,65	reels of 1,000 pcs
CCM03-3011LFT	gold	hinged	8		without	10,000	2,55	17,2 x 29,65	reels of 1,000 pcs
CCM03-3012LFT	gold	hinged	8	2 plastic pegs	without	10,000	2,55	17,2 x 29,65	reels of 1,000 pcs
CCM03-3013LFT	gold	hinged	6		with	10,000	2,55	17,2 x 29,65	reels of 1,000 pcs
CCM03-3512LFT	gold	hinged	6	Large soldering pads*	without	10,000	2,55	17,2 x 29,65	reels of 1,000 pcs
CCM03-3504LFT	gold	fixed	8		without	50,000	2,85	17,2 x 25,5	reels of 1,000 pcs
CCM03-3505LFT	gold	fixed	6		without	50,000	2,85	17,2 x 25,5	reels of 1,000 pcs
CCM03-3754LFT	inlay	fixed	6		with	10,000	3,5	16,5 x 18,05	reels of 1,000 pcs
CCM03-3760LFT	inlay	fixed	6		without	10,000	3,45	16,5 x 15,85	reels of 1,000 pcs
CCM03-3764LFT	inlay	none	6		with	10,000	2,9	16,5 x 15,85	reels of 1,000 pcs

* Can go through reflow upside down

CCM03 MK2 Series


CCM03-3001 LFT / CCM03-3009 LFT




SIM/SAM

CCM03 MK2 Series

CCM03-3002 LFT / CCM03-3010 LFT



RECOMMENDED PC BOARD LAYOUT
(Component side)




Dimensions are shown in mm
Specifications and dimensions subject to change

www.ck-components.com

CCM03 MK2 Series

CCM03-3003 LFT



SIM/SAM

Contact location according to ENV1375-1 & GSM11-11




First Angle Projection

Dimensions are shown in mm
Specifications and dimensions subject to change


www.ck-components.com

CCM03 MK2 Series

CCM03-3004 LFT



RECOMMENDED PC BOARD LAYOUT
(Component side)



CCM03-3011 LFT



Figure 1: Mechanical drawing of the contact area of the connector. The drawing shows a top-down view of a connector with dimensions in millimeters. Key dimensions include a total width of 25.5 mm, a central contact area of 23.2 mm, and a plastic outline width of 1.5 mm. The contact foot area is 0.8 x 1 mm. The drawing also shows the positions of contacts C1 through C8, with a 1.27 mm pitch between C5 and C8, and a 1.3 mm pitch between C1 and C4. A 3x2.54 mm area is marked as a prohibited area. The drawing is labeled "Contact location according to ENV1375-1 & GSM11-11".



SIM/SAM

[illegible]

Technical drawing of the contact area of a 12-pin connector. The drawing shows a top-down view of the contact area with dimensions in millimeters. Key features include:

- Plastic outline
- Contact foot area 0,8 x 1
- Pad
- Contact locations C1 through C8
- Hole with diameter $\varnothing 1,2^{+0,2}_0$
- Dimensions: 1.5, 23.2, 1.44, 20.32, 1.8, 5.5, 2.5, 5.5, 1.27, 5.08, 10.16, 8.6, 1.27, 2.54, 3x, 3.81, 3.81, 6.35, 9.34, 25.5, 8x, 0.2, 1.3, 0.1




www.ck-components.com

CCM03-3013 LFT



CCM03 MK2 Series

CCM03-3512 LFT



Dimensions are shown in mm
Specifications and dimensions subject to change

www.ck-components.com

CCM03-3504 LFT / CCM03-3505 LFT

[illegible]

www.ck-components.com

SIM/SAM

SIM/SAM



SIM/SAM




SIM/SAM

SIM/SAM


SIM/SAM

CCM03 MK2 Series

CCM03-3760 LFT



RECOMMENDED PC BOARD LAYOUT
(Component side)



First Angle
Projection

Dimensions are shown in mm
Specifications and dimensions subject to change

www.ck-components.com


SIM/SAM

SIM/SAM



www.ck-components.com

CCM04 MK3 Series



Features

- **SIM and SAM card acceptance**
- **Compatible with pick and place and lead free soldering**

Typical Applications

- **Mobile**
- **POS**
- **Identification**
- **GPS**

Mechanical

Number of contacts	6 or 8
Mechanical life	30,000 cycles
Card insertion force	10N max
Card extraction force	1N min / 10N max
Contact force	0,35N min to 0,65N
Vibration Frequency	10 to 500 Hz. Acceleration 50m/s ² Duration 6 hours - amplitude 0,35mm
Shock	Peak value 500 m/s ² – Duration 11 ms 3 shocks in each direction of each axis
Max elect. discontinuity	1µs

Packaging

See table below

Soldering Process

Compatible with lead free SMT soldering process

Contact Electrical Data

Insulation resistance	1000 MΩ min
Contact resistance max	100 mΩ max
Switching current	10 µA min / 1 A max
Dielectric strength	750 Vrms min

Environmental Data





Operating temperature	-40°C to +85°C
Salt mist	IEC 512 test number 11f (96 hours)
Damp heat	IEC 512 test number 11c (10 days)
RoHS compliant	

SIM/SAM



Designation	# of Contacts	Contact Plating	PCB Version	Height (mm)	Dim. (mm)	Packaging
CCM04-5137LFS	6	gold	SMT IN	1,9	8,15 X 10,45	reels of 1,900 pcs

CCM04 MK3 Series

CCM04-5137 LFS



DETAIL A
Scale 10



RECOMMENDED PC BOARD LAYOUT
(Component side)

