

4		3		2		1													
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS											
© COPYRIGHT - By -		ALL RIGHTS RESERVED.		E		B		P		LTR		DESCRIPTION		DATE		DWN		APVD	
								B2		ECR-15-012328		19AUG2015		KR		TN			
HB01AE 28.8 max 9.2 3.0 max MARKING FACE LEAD LENGTH 20mm MIN DESCRIPTION: LEAD MATERIAL: LEAD CROSS-SECTION: HYBRID PROTECTION: MARKING: HIGH VOLTAGE THICK FILM RESISTOR. TINNED COPPER WIRE 0.6 +/-0.05 DIA CONFORMAL EPOXY COATING AS SHOWN BELOW ON MARKING FACE HB01A VAL. TOL. TCR DATE CODE HB01AS 26.0 max 8.4 max 1.5 max MARKING FACE LEAD LENGTH 20mm MIN DESCRIPTION: LEAD MATERIAL: LEAD CROSS-SECTION: HYBRID PROTECTION: MARKING: HIGH VOLTAGE THICK FILM RESISTOR. TINNED COPPER WIRE 0.6 +/-0.05 DIA SCREEN PRINTED SILICONE COATING AS SHOWN BELOW ON MARKING FACE HB01A VAL. TOL. TCR DATE CODE																			
R TYPICAL SCHEMATIC FOR A SPECIFIC PN FOR A RESISTANCE VALUE AND TOLERANCE, PLEASE REFER TO DMF.																			
RoHS Compliant THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: MM 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH - MATERIAL - DWN DAVE KENNEDY 31OCT2005 CHK J CATCHPOLE 01NOV05 APVD J CATCHPOLE 01NOV05 PRODUCT SPEC APPLICATION SPEC WEIGHT - CUSTOMER DRAWING STE TE Connectivity NAME HB01 SIZE A3 CAGE CODE 00779 DRAWING NO C-1625958 RESTRICTED TO - SCALE NTS SHEET 1 OF 2 REV B2																			

4		3		2		1	
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION			
© COPYRIGHT - By -				ALL RIGHTS RESERVED.			
LOC E		DIST B		REVISIONS			
P		LTR		DESCRIPTION		DATE	
		-		SEE SHEET 1		-	
HB01RE 10.4 max 26.5 max 25.4 min 22.9 3.0 max MARKING FACE DESCRIPTION: LEAD MATERIAL: LEAD CROSS-SECTION: HYBRID PROTECTION: MARKING: HIGH VOLTAGE THICK FILM RESISTOR. TINNED COPPER WIRE 0.6 +/-0.05 DIA CONFORMAL EPOXY COATING AS SHOWN BELOW ON MARKING FACE HB01R VAL. TOL. TCR DATE CODE				HB01RS 8.4 max 26.0 max 25.4 min 22.9 1.5 max MARKING FACE DESCRIPTION: LEAD MATERIAL: LEAD CROSS-SECTION: HYBRID PROTECTION: MARKING: HIGH VOLTAGE THICK FILM RESISTOR. TINNED COPPER WIRE 0.6 +/-0.05 DIA SCREEN PRINTED SILICONE COATING AS SHOWN BELOW ON MARKING FACE HB01R VAL. TOL. TCR DATE CODE			
R TYPICAL SCHEMATIC FOR A SPECIFIC PN FOR A RESISTANCE VALUE AND TOLERANCE, PLEASE REFER TO DMF.				RoHS Compliant THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: MM 0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES ± - ± - ± - ± - ± - ± - MATERIAL - FINISH - DWN DAVE KENNEDY CHK J CATCHPOLE APVD J CATCHPOLE PRODUCT SPEC - APPLICATION SPEC - WEIGHT - CUSTOMER DRAWING 31OCT2005 01NOV05 01NOV05 NAME HB01 SIZE A3 CAGE CODE 00779 DRAWING NO C-1625958 RESTRICTED TO - SCALE NTS SHEET 2 OF 2 REV B2 TE Connectivity HB01 NTS 2 OF 2 B2			