


XDSL SPLITTER FILTER MODULE

B8845NL

SmartER Series



-
-
-
-
-
-

Electrical Specifications @ 25°C		
PARAMETER	FREQUENCY	
ISDN Impedance	1 kHz to 80 kHz	150 Ω
ISDN Insertion Loss	1 kHz to 60 kHz	1.2 dB MAX
	60 kHz to 80 kHz	2.0 dB MAX
ISDN Return Loss	1 kHz to 60 kHz	16 dB MIN
	60 kHz to 80 kHz	14 dB MIN
POTS Impedance	200 Hz to 4 kHz	($Z_R = 220 \Omega + 820 \Omega / 115 \text{ nF}$)
POTS Insertion Loss	@ 1 kHz	1.0 dB MAX
POTS Insertion Loss Distortion	200 Hz to 4 kHz	1.0 dB MAX
POTS Return Loss	300 Hz to 1.6 kHz	15 dB MIN
	1.6 kHz to 3.4 kHz	12 dB MIN
POTS Group Delay Distortion	200 Hz to 4 kHz	<200 μS
Longitudinal Balance	50 Hz to 30 kHz	40 dB MIN
	30 kHz to 1104 kHz	50 dB MIN
	1104 kHz to 30 MHz	30 dB MIN
xDSL Insertion Loss	138 kHz to 150 kHz	55 dB MIN
	150 kHz to 1.1 MHz	65 dB MIN
	1.1 MHz to 30 MHz	55 dB MIN
ISDN Group Delay Distortion	1 kHz to 80 kHz	<20 μS
Metering Pulses	12 kHz and 16 kHz	3 dB MAX
DC Current		80 mA MAX
Total DC Resistance		5.8 Ω MAX

Mechanical and schematic on following page . . .

XDSL SPLITTER FILTER MODULE

B8845NL


SmartER Series



Pulse
A TECHNITROL COMPANY

Mechanical

B8845NL



Weight 8.0 grams


Tray 80/tray

Dimensions: $\frac{\text{Inches}}{\text{mm}}$

Unless otherwise specified,
all tolerances are $\pm \frac{.010}{0,25}$

Schematic

B8845NL



For More Information:

Pulse Worldwide Headquarters
12220 World Trade Dr.
San Diego, CA 92128
U.S.A.

www.pulseeng.com
Tel: 858 674 8100
Fax: 858 674 8262

Pulse Europe
Zeppelinstrasse 15
D-71083 Herrenberg
Germany

Tel: 49 7032 7806 0
Fax: 49 7032 7806 135

Pulse China Headquarters
B402, Shenzhen Academy of Aerospace Technology Bldg.
10th Kejinan Rd.
High-Tech Zone
Nanshan District
Shenzhen, PR China 518057

Tel: 86 755 33966678
Fax: 86 755 33966700

Pulse North China
Room 2704/2705
Super Ocean Finance Ctr.
2067 Yan An Rd. West
Shanghai 200336
China

Tel: 86 21 62787060
Fax: 86 2162786973

Pulse South Asia
135 Joo Seng Rd.
#03-02
PM Industrial Bldg.
Singapore 368363

Tel: 65 6287 8998
Fax: 65 6287 8998

Pulse North Asia
3F, No. 198
Zhongyuan Rd.
Zhongli City
Taoyuan County 320
Taiwan R. O. C.

Tel: 886 3 4356768
Fax: 886 3 4356823 (Pulse)
Fax: 886 3 4356820 (FRE)

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.

© Copyright, 2010. Pulse Engineering, Inc. All rights reserved.