








Copyright FCI.



RECOMMENDED MOUNTING HOLE LAYOUT

rev	ecn no	dr	date
E	S20042	JPEH	2002/04/23
F	S04-0172	JPEH	2004/08/11
G	S04-0224	KBM	2004/10/25
H	S05-0060	KBM	2005/02/28
J	S06-0236	KHL	2005/02/28
K	S10-0205	PR	2009/12/16
-	-	-	-

www.fciconnect.com			surface ISO 1302		- ✓	tolerance std ISO 406 ISO 1101		projection 		MM 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	JPEH	2002/04/23	ANGULAR	LINEAR	0.X		±-		size A3	Scale 10:1		
Eng	JPEH	2004/08/31			0.XX		±0.25					
Chr	KH LEE	2009/12/16			0°	±3°	0.XXX			±-		
Appr	JOEY NG	2009/12/16	Product family				MINITEK		Spec ref -			
FCi			title POL. MINITEK II STR HEADER (DUPLEX)				dwg no 61641				Rev. K	
			catalog no -				CUSTOMER			sheet 1 of 2		

CONFIDENTIAL

A

B

C

D

PRODUCT NO. SEE NOTE 8	POS	DIM A	DIM B	POL. POS	DIM X	DIM Y
61641-X01	2X3	4.0	2.5	3	4	6
-X02	2X22	4.0	2.5	20	42	44
-X03	2X13	4.0	2.5	26	24	26
-X04	2X13	5.27	3.77	26	24	26
-X05	2X16	4.0	2.5	3, 4, 5, 6, 32	30	32

NOTES:

- MATERIAL:
BODY : HIGH TEMPERATURE THERMOPLASTIC UL 94V-0 BLACK
PIN : COPPER ALLOY
- TOLERANCE UNLESS OTHERWISE NOTED ± 0.25
- DIM 1.0 ± 0.15 MOLDED SIDE(S) ONLY. IF SIDE(S) ARE BROKEN.
DIM 1.5 MAX APPLIES.
- RECESS APPLIES TO MOLDED SIDE(S) ONLY.
- PLATING ON MATING LENGTH:
-3YY --- 0.38 μ m Au OVER 1.27 μ m MIN NICKEL UNDERPLATE.
-5YY --- 0.38 μ m PdNi WITH Au FLASH OVER 1.27 μ m MIN NICKEL UNDERPLATE.
-6YY --- 0.76 μ m PdNi WITH Au FLASH OVER 1.27 μ m MIN NICKEL UNDERPLATE.
- SOLDER TAIL PLATING:
a) SOLDER TAIL OF P/N:61641-XXX IS 3.81 μ m MIN TIN/LEAD (90/10) PLATED
OVER 1.27 μ m MIN NICKEL UNDERPLATE.
b) SOLDER TAIL OF P/N:61641-XXXLF IS 2.54 μ m MIN TIN PLATED
OVER 1.27 μ m MIN NICKEL UNDERPLATE (LEADFREE).
- POLARISED BY OMISSION OF PINS. REFER TO TABLE
FOR POL. POS.

8. PART NUMBER INFORMATION

61641-XY YLF



- THE HOUSING WILL WITHSTAND EXPOSURE TO 255°C
PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED
OR VAPOR PHASE REFLOW OVEN.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C
PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER
APPLICATION WITH A 1.57MM MINIMUM THICK CIRCUIT BOARD.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- A $\triangle K$ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE
WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

CONFIDENTIAL

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection size A3	MM Scale 10:1
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	JPEH	2002/04/23	ANGULAR 0° ±3°	LINEAR	0.X	±-
Eng	JPEH	2004/08/31			0.XX	±0.25
Chr	KH LEE	2009/12/16			0.XXX	±-
Appr	JOEY NG	2009/12/16	Product family			ECN S10-0205
			MINITEK			Spec ref -
FCI			POL. MINITEK II			Rev. K
			STR HEADER (DUPLEX)			
			catalog no			
			CUSTOMER			sheet 2 of 2