

SAC-4P-M12MS/ 2,0-28X OD

Order No.: 1454040

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1454040>

Sensor/Actuator cable, 4-position, PE-X halogen-free, Black-gray RAL 7021, Plug, straightLink:M12, A - standard, on Free conductor end, A - standard, Cable length: 2 m

Commercial data

GTIN (EAN)	4 046356 568654
sales group	D111
Pack	1 pcs.
Customs tariff	85444290
Catalog page information	Page 219 (PC-2011)

Product notes

WEEE/RoHS-compliant since:
03/04/2010



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General data**

Rated current at 40°C	4 A
Rated voltage	250 V
Number of positions	4
Volume resistance	≤ 5 mΩ

Insulation resistance	$\geq 100 \text{ M}\Omega$
Length of cable	2 m
Ambient temperature (operation)	-40 °C ... 105 °C

General characteristics

Standards/regulations	M12 connector IEC 61076-2-101
Coding	A - standard
Pollution degree	3
Degree of protection	IP65/IP68/IP69K
Insertion/withdrawal cycles	≥ 100
Torque	0.4 Nm (M12 connector)
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PP
Material of grip body	PP
Material, knurls	High-grade steel
Sealing material	FPM
Status display	No

Conductor data

Cable type	PE-X black
Cable type (abbreviation)	28X
Cable abbreviation	Li2X2X
Conductor cross section	0.5 mm ²
AWG signal line	20
Conductor structure signal line	28x 0.15 mm
Core diameter including insulation	1.6 mm $\pm$ 0.05 mm
Thickness, insulation	~ 0.3 mm (Core insulation)
	~ 0.6 mm (Outer cable sheath)
External cable diameter	5.2 mm $\pm$ 0.2 mm
Wire colors	Brown, white, blue, black
External sheath, color	Black-gray RAL 7021
Insulation resistance	$\geq 100 \text{ M}\Omega \cdot \text{km}$ (at 20°C)
Conductor resistance	max. 39 Ω/m (at 20°C)
Nominal voltage, conductor	$\leq 300 \text{ V}$ (AC)
Test voltage, conductor	$\geq 3000 \text{ V}$ (AC)


Overall twist	4 wires, twisted
Length of twist, overall twist	61.6 mm
Outer sheath, material	PE-X
Material conductor insulation	PE-X
Conductor material	Bare Cu litz wires
Cable weight	44 kg/km
Smallest bending radius, fixed installation	26 mm
Smallest bending radius, movable installation	52 mm
Number of bending cycles	2000000
Bending radius	52 mm
Traversing path	10 m
Traversing rate	3 m/s
Acceleration	10 m/s ²
Ambient temperature (operation)	-40 °C ... 105 °C (cable, fixed installation) -15 °C ... 105 °C (cable, flexible installation)
Flame resistance	According to DIN 60332-1-2 According to DIN EN 50266-2-5
Halogen-free	in accordance with DIN VDE 0472 part 815
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	UV resistant According to DIN VDE 0276-605

Accessories

Item	Designation	Description
General		
1440782	SACC-M12FS-4QO-0,75-VA	Sensor/actuator connector, female connector, straight, 4-pos., M12, A-encoded, QUICKON-ONE, high-grade steel knurl, maximum cable diameter of 8 mm
Tools		
1212513	SAC BIT M12-W14	SAC nut, for assembling M12 connectors with hexagonal high-grade steel knurl, with 4 mm hexagonal drive
1208429	TSD 04 SAC	Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors


Diagrams/Drawings

Dimensioned drawing




M12 x 1 male connector, straight

Circuit diagram



Contact assignment of the M12 plugs

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2011 Phoenix Contact
Technical modifications reserved;