

## VGA Coax Monitor Cable, High Resolution cable with RGB coax (HD15 M/M), 3-ft.

MODEL NUMBER: **P502-003**



### Highlights

- 3ft SVGA Male-Male Cable
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- Resolutions up to 2048 X 1536

### Package Includes

3-ft. SVGA/VGA Monitor Cable  
HD15M to HD15M Gold Connectors w/  
RGB Coax

### Description

Tripp Lite's 3-foot SVGA/VGA monitor replacement cable is the gold standard in video cables. The mini-coax (RGB) and paired video wire construction delivers superior signal quality. Gold plated connectors and gold plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high density DB15 male connectors are molded and have integral strain relief to ensure they last a long time.

### Features

- 3ft SVGA Male-Male Cable
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Resolutions up to 2048 x 1536
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity.
- HD15 male to HD15 male molded connectors

## Specifications

OVERVIEW	
Intended Application	Connecting Peripherals
Style	Monitor Cables
Display Style	Direct Connect
Model Type	VGA
Cable Types	MONITOR
INPUT	

Cable Length (ft.)	3
Cable Length (m)	0.91
<b>UPC ASSIGNMENT</b>	
Unit Carton UPC#	037332146946
<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Connector A	HD15 (MALE)
Connector B	HD15 (MALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.