

[Products & Services](#) [Brands](#) [Technologies](#) [Our Company](#) [Partners & Suppliers](#)Search United States [\[Change\]](#)

## Electrical Commercial and Industrial

[Products](#) | [Documentation & Literature](#) | [News & Tradeshow](#) | [Support](#) |[United States](#) > [Products & Services](#) > [Electronics, Electrical, and Communications](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Cable Ties and Accessories](#) > [3M™ Dual Lock Fasteners](#) > 3M™ Dual Lock™ Reclosable Fastener SJ4570 Low Profile Clear, 3/4 in x 50 yd 0.105 in (2.7 mm) , 2 per case Bulk[Find An Account Rep](#)[Where To Buy \(Find A Distributor\)](#)[Contact Us](#)

## 3M™ Dual Lock™ Reclosable Fastener SJ4570 Low Profile Clear, 3/4 in x 50 yd 0.105 in (2.7 mm) , 2 per case Bulk

UPC# 00021200462399 3M Product Number SJ4570-3/4"x50yd-Clear 3M ID 70070967578

[Print](#)[Share](#)

A low surface energy adhesive on the back of a clear polypropylene reclosable fastener. Low profile. 0.10 inch engaged thickness. Closure life 100.

- Low profile, polyolefin fastener is half the thickness of standard Dual Lock reclosable fasteners and is self-mating.
- Designed to bond to metals, glass, many plastics and powder coated paints and medium to low surface energy materials.
- General Industrial, Speciality Vehicles, Transportation, Military, Packaging, Medical, Point of Purchase Displays, Exhibits, Electronics, Construction, Furniture, Maintenance Repair and Operations (MRO).
- Speaker Grill Attachment, Screen Door Attachment, Muntin Bars, Access Panels, Signs, Display Components, and Multi-Media Packaging.

**Need Help?****Questions?** We can help  
[Contact Us](#)[View All Images](#)☒ **Network Access Message: The page****Overview****Support****Specifications**

Adhesive Type	Low Surface Energy Acrylic Adhesive
Applications	Attaching Graphics
Brand	Dual Lock
Closure Life	100
Color	Clear
Engaged Thickness	0.098 Inch
Flame Retardant	No
Indoor/Outdoor	Indoor
Industry - Use	Construction, Electronics, Furniture, General Industrial, Medical, Military & Government, MRO, Packaging, Retail, Transportation
Length	50 Linear Yard
Length (metric)	45.72 Linear Metre
Liner Thickness	6.2 Milli-inch (mil)
Liner Type	83# Polycoated Kraft Paper (PCK)
Low Profile	Yes
Maximum Operating Temperature (Fahrenheit)	158 Degree Fahrenheit
Product Form	Roll
Units per Case	2
Width	0.75 Inch

Width (metric)

19.05 Millimetre

**3M:** [News](#) | [Careers](#) | [Investor Relations](#) | [MSDS Search](#) | [Transport Information Search](#) | [A-Z Product Index](#) | [Contact 3M](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2012. All Rights Reserved.

