




- |                                                                                     |                                                                                                  |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------|
|  | CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS                                                    |
|  | USE WITH #26-#30 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS |
|  | THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE          |
|  | POINT OF MEASUREMENT FOR PLATING THICKNESS                                                       |
| 5                                                                                   | FOR STRIP ASSEMBLIES SEE PART NUMBER 103959                                                      |
|  | POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)                                        |
|  | CONTACTS: .000100-.000200 BRIGHT TIN-LEAD<br>OVER .000050 NICKEL                                 |
|  | CONTACTS: .000100-.000200 MATTE TIN<br>OVER .000050 NICKEL                                       |
|  | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI                                  |

|                                                                                                   |                                                                                       |                           |                  |                                                                                                  |
|---------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------|------------------|--------------------------------------------------------------------------------------------------|
| <br>OBSOLETE   |    | 2-104257-4                | 25               |  7-103641-4   |
|                                                                                                   |    | 2-104257-3                | 24               |  7-103641-3   |
|                                                                                                   |    | 2-104257-2                | 23               |  7-103641-2   |
|                                                                                                   |    | 2-104257-1                | 22               |  7-103641-1   |
|                                                                                                   |    | 2-104257-0                | 21               |  7-103641-0   |
|                                                                                                   |    | 1-104257-9                | 20               |  6-103641-9   |
|                                                                                                   |    | 1-104257-8                | 19               |  6-103641-8   |
|                                                                                                   |    | 1-104257-7                | 18               |  6-103641-7   |
|                                                                                                   |    | 1-104257-6                | 17               |  6-103641-6   |
|                                                                                                   |    | 1-104257-5                | 16               |  6-103641-5   |
|                                                                                                   |    | 1-104257-4                | 15               |  6-103641-4   |
|                                                                                                   |    | 1-104257-3                | 14               |  6-103641-3   |
| <br>OBSOLETE   |    | 1-104257-2                | 13               | 6-103641-2                                                                                       |
|                                                                                                   |    | 2-104257-4                | 25               |  2-103641-4   |
|                                                                                                   |    | 2-104257-3                | 24               |  2-103641-3   |
|                                                                                                   |   | 2-104257-2                | 23               |  2-103641-2  |
|                                                                                                   |  | 2-104257-1                | 22               |  2-103641-1 |
| <br>OBSOLETE |  | 2-104257-0                | 21               |  2-103641-0 |
|                                                                                                   |  | 1-104257-9                | 20               | 1-103641-9                                                                                       |
|                                                                                                   |  | 1-104257-8                | 19               |  1-103641-8 |
|                                                                                                   |  | 1-104257-7                | 18               |  1-103641-7 |
|                                                                                                   |  | 1-104257-6                | 17               |  1-103641-6 |
|                                                                                                   |  | 1-104257-5                | 16               |  1-103641-5 |
|                                                                                                   |  | 1-104257-4                | 15               |  1-103641-4 |
|  SUPERSEDED  |  | 1-104257-3                | 14               |  1-103641-3 |
| BY 1-103959-1                                                                                     |                                                                                       | 1-104257-2                | 13               |  1-103641-2 |
| BY 1-103959-0                                                                                     |                                                                                       | 1-104257-1                | 12               | 1-103641-1                                                                                       |
| BY 1-103959-9                                                                                     |                                                                                       | 1-104257-0                | 11               | 1-103641-0                                                                                       |
| BY 103959-9                                                                                       |                                                                                       | 104257-9                  | 10               | 103641-9                                                                                         |
| BY 103959-8                                                                                       |                                                                                       | 104257-8                  | 9                | 103641-8                                                                                         |
| BY 103959-7                                                                                       |                                                                                       | 104257-7                  | 8                | 103641-7                                                                                         |
| BY 103959-6                                                                                       |                                                                                       | 104257-6                  | 7                | 103641-6                                                                                         |
| BY 103959-5                                                                                       |                                                                                       | 104257-5                  | 6                | 103641-5                                                                                         |
| BY 103959-4                                                                                       |                                                                                       | 104257-4                  | 5                | 103641-4                                                                                         |
| BY 103959-3                                                                                       |                                                                                       | 104257-3                  | 4                | 103641-3                                                                                         |
| BY 103959-2                                                                                       |                                                                                       | 104257-2                  | 3                | 103641-2                                                                                         |
| BY 103959-1                                                                                       |                                                                                       | 104257-1                  | 2                | 103641-1                                                                                         |
|                                                                                                   | PLATING                                                                               | HOUSING<br>PART<br>NUMBER | NO<br>OF<br>POSN | ASSEMBLY<br>PART<br>NUMBER                                                                       |

|                                        |  |  |                  |  |                                                                                       |  |  |
|----------------------------------------|--|--|------------------|--|---------------------------------------------------------------------------------------|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  |  | DWN<br>11-4-86   |  | Tyco Electronics Corporation                                                          |  |  |
| L A MAYER                              |  |  | CHK<br>11-12-86  |  | Harrisburg, Pa 17105-3608                                                             |  |  |
| P de JONG                              |  |  | APVD<br>11-12-86 |  | NAME                                                                                  |  |  |
| P de JONG                              |  |  | PRODUCT SPEC     |  | RCPT ASSY, AMPMODU MTE, SINGLE<br>, LATCHED & POLARIZED,<br>FOR #26-#30 AWG WIRE SIZE |  |  |
| 108-25034                              |  |  | APPLICATION SPEC |  |                                                                                       |  |  |
| 114-25026                              |  |  | SIZE             |  |                                                                                       |  |  |
| CAGE CODE                              |  |  | DRAWING NO       |  |                                                                                       |  |  |
| RESTRICTED TO                          |  |  | A2               |  | 00779                                                                                 |  |  |
| C-103641                               |  |  | SCALE            |  | SHEET                                                                                 |  |  |
| 4-1                                    |  |  | 1 of 1           |  | REV                                                                                   |  |  |
| T1                                     |  |  |                  |  |                                                                                       |  |  |