






8				7			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION			
COPYRIGHT 20				20			
BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.							
PART NUMBER		REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION	
1852552-1		A	122500-1	LEADMAKER	POST FEED	CUTS CARRIER	
1852552-2		A	565435-5	BENCH MODEL K	PRE FEED	CUTS CARRIER	
1852552-3		A	354500-1	BENCH MODEL G	PRE FEED	CUTS CARRIER	
1852552-6		A	122500-1	LEADMAKER	POST FEED	CONTINUOUS CARRIER	
7-1852552-7		A	-	-	-	SPARE PARTS	

- △ RECOMMENDED SPARE PARTS
- △ GREASE LIGHTLY
- △ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE



TERMINAL NAME: FEMALE GT 280 TERMINAL					
TE PN	MANF PN	PACKARD TERMINAL - PACKARD CRIMP SPECS			
1949491	15496305				
-	-	PAD LTR	CRIMP HEIGHT	WIRE SIZE	
-	-	A	1.10±0.05mm [.043±.002]	0.50mm2	
-	-	B	1.05±0.05 [.041±.002]	0.35mm2	
-	-	C	-	-	
-	-	D	-	-	
-	-	CRIMP	SIZE	TYPE	RANGE
-	-	WIRE	1.75mm [.069]	F	0.35-0.50mm2
-	-	INSUL	1.93mm [.076]	F	1.2-1.85mm
WIRE STRIP LENGTH	TERM APPL SPEC	FEED	APPLICATOR INSTRUCTIONS		SET UP GAGE
4.42-4.80mm	NONE	14.02mm	408-8040		458637-1



-	2	2	2	2	-	4-354779-7	PIN, WIRE DISC, .3225	127
-	2	2	2	2	-	4-354779-2	PIN, WIRE DISC, .3200	126
-	-	-	REF	-	..	455749-1	GUARD WINDOW	116
-	-	-	REF	-	..	679532-1	INSERT, GUARD	115
-	1	1	1	1	-	690603-1	SPRING ASSIST AMP-O-MATOR APPLICATOR	112
-	1	1	1	1	-	1-21002-7	SCR, BTN SKT HD CAP 6-32 X .375	91
-	1	1	1	1	-	318563-1	GUARD, FRONT CHIP	89
-	1	1	1	1	-	4088040	SF APPL INST 408-8040	72
-	1	1	1	1	-	217238-1	GENERAL INSTRUCTION PKG	71
-	1	1	1	1	-	461264-1	PLATE, IDENTIFICATION	67
-	2	2	2	2	-	21017-2	SCREW, DRIVE	66
-	1	1	1	1	-	986950-1	WASHER, FLAT PRECISION	64
-	1	1	1	1	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	63
-	1	1	1	1	-	23030-1	SCR, SKT HD CAP 6-32 x .25	62
-	1	1	1	1	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	60
-	1	1	1	1	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	59
-	1	1	1	1	-	458537-2	PAWL, FEED	56
-	4	4	4	4	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	54
-	2	2	2	2	-	2-21000-9	SCR, SKT HD CAP 8-32 X .750	53
-	1	1	1	1	-	21018-5	NUT, HEX, REG 6-32	52
-	1	1	1	1	-	811242-2	BUMPER, HOLD DOWN	51
-	1	1	1	1	-	690753-1	SPACER, TONKER	50
-	-	-	-	-	..	690602-6	CAM, PRE FEED, 1 5/8	49
-	-	-	-	-	..	690602-5	CAM, PRE FEED, 1 1/8	48
-	1	-	-	-	-	690501-4	CAM, POST FEED, 1 5/8	47
-	1	1	1	1	-	459456-1	APPL. BASIC SUB ASSY (SIDE WISE MQCA)	46
-	1	1	1	1	-	690191-1	PLUG, NYLON	45
-	1	1	1	1	-	455673-1	RAM, SIDE FEED	44
-	1	1	1	1	-	690125-1	SHIM SUB-ASSY	43
-	1	1	1	1	-	690124-1	WASHER, RAM (.115)	42
-	1	1	1	1	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	41
-	1	1	1	1	-	23241-6	BALL, STEEL	40
-	1	1	1	1	-	690170-1	SPRING, COMPRESSION	39
-	1	1	1	1	-	690142-3	DISC, INSULATION	38
-	1	1	1	1	-	354777-1	WIRE DISC, ASSEMBLY	37
-	1	1	1	1	-	22480-5	SPRING, COMPRESSION	36
-	1	1	1	1	-	690212-1	POST, RAM	35
-	1	1	1	1	-	690786-5	TERMINAL SUPPORT	34
-	2	2	2	2	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	33
-	1	1	1	1	-	21024-5	WASHER, SPRG LOCK, REG NO 10	32
-	1	1	1	1	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	31
-	1	1	1	1	-	1-1320908-5	SPACER, STRIP GUIDE	30
-	1	1	1	1	-	1633091-1	ASSEMBLY, STRIP GUIDE	29
-	1	1	1	1	-	1-455888-0	SPACER, CRIMPER	28
-	1	1	1	1	-	21028-2	PIN, SLOTTED SPRING .062 X .250	27
-	1	1	1	1	-	22278-9	SPRING, COMPRESSION	26
-	1	1	1	1	-	854769-4	HOLDER, INS	25
-	1	1	1	1	-	1320928-1	PLATE, STRIP GUIDE	24
-	1	-	-	-	-	690472-2	STRIPPER	22
-	1	1	1	1	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21
-	4	4	4	4	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20
-	-	-	-	-	-	691353-1	STRIPPER	19
-	1	-	-	-	-	679625-1	SHEAR HOLDER, FRONT (NO CUT)	13
-	1	1	1	1	-	3-22280-3	SPRING, COMPRESSION	12
-	1	1	1	1	-	690461-1	STOP, SHEAR	11
-	-	-	-	-	-	690459-1	SHEAR HOLDER, FRONT	10
-	1	1	1	1	-	462006-1	FLOATING SHEAR, FRONT	9
1	1	1	1	1	-	4-1633535-3	ANVIL, COMBINATION	8
-	1	1	1	1	-	2-240641-5	SPACER	7
-	-	-	-	-	..	-	-	6
-	1	1	1	1	-	854772-6	DEPRESSOR, SHEAR	5
-	1	1	1	1	-	1-238011-0	BLOCK, CRIMPER SPACER	4
1	1	1	1	1	-	1-683453-2	CRIMPER, INSULATION PREMIUM	3
-	1	1	1	1	-	455888-9	SPACER, CRIMPER	2
1	1	1	1	1	-	2-1673600-3	CRIMPER, WIRE	1

-77 -6 -3 -2 -1 U/M		PART NO	DESCRIPTION		ITEM NO
THIS DRAWING IS A CONTROLLING DOCUMENT FOR TYCO ELECTRONICS CORPORATION TO BE USED IN THE FABRICATION OF THIS DRAWING. ANY CHANGES OR MODIFICATIONS SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN C REICHELDERFER	Tyco Electronics		
		CHR TELBIN	Harrisburg, PA 17105-3608		
DIMENSIONS:		APVD T RENCHOFF	NAME		
INCHES		PRODUCT SPEC		SIDE FEED HDM APPLICATOR	
		APPLICATION SPEC		-	
9 PLC ±.01		SIZE		CAGE CODE	
10 PLC ±.01		DRAWING NO		RESTRICTED TO	
2 PLC ±.01		A 00779		C=1852552	
3 PLC ±.001		SCALE		3:5	
4 PLC ±.0001		SHEET		1 OF 1	
ANGLES ±.01		REV		A	
MATERIAL		CUSTOMER DRAWING			
FINISH					
-					
-					
-					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1852552-3](#)