







SECTION: C-C



SECTION: D-D



- NOTE**
- 1. MATERIAL: COPPER ALLOY, $t=0.25$.
 - 2. FINISH: PRE-TIN PLATE.
 - 3. RECOMMENDED LENGTH OF WIRE STRIP: 5.0-5.6.
 - 4. INSERTION-EXTRACTION FORCE WITH TAB TERMINAL P/N 35420.
INSERTION FORCE : 0.30 ± 1.0 Kgf.
AFTER SIX TIMES OF INSERTION & EXTRACTION FORCE : 0.15 ± 1.0 Kgf.

NO.	ENG-NO.	TYPE	PART NAME	CABLE SIZE (mm ²)	DEMENSION			
					W1	H1	W2	H2
1	35407-6102	(S)	.090 FEMALE TER'L	AVSS(AVS) 0.3 - 0.5	2.5	2.4	3.4	3.5
2	35407-6202	(L)	.090 FEMALE TER'L	AVSS(AVS) 2.0	3.6	3.5	4.0	4.0
3	35407-6502	(M)	.090 FEMALE TER'L	AVSS(AVS) 0.85 - 1.25	2.6	3.0	4.0	4.0

CHANGED TENSION SPEC. EC NO. KPR2002-0090 DRWNS:JMKIM 02/07/08 CHK'Y:SKJIM 02/07/08 APPR:W.LEE	QUALITY SYMBOLS MAJOR CRITICAL MINOR	GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE 8:1	DESIGN UNITS mm ☒ inch ☐	THIRD ANGLE PROJECTION ☐ mm ☐ inch ☒ mm ONLY	DIMENSIONS: mm ☐ inch ☒ mm ONLY	SHT REV			
		DRAWN BY & DATE B.C.YOON '98.4.10		CHECKED BY & DATE B.K.CHOI '98.4.10							
		APPROVED BY & DATE C.W.LEE '98.4.10		CAD FILENAME SD35407.DGN							
		ANGULAR: $\pm 1^\circ$		MATERIAL NO. 354076102							
C	REV	DESCRIPTION		TITLE: .090 FEMALE TER'L (FT TYPE)		MOLEX INCORPORATED		SHEET NO. 1 OF 1			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		SIZE C					