

1b_frame_D_P_ME_T
Rev. E 2006/04/15

	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1																																											
M	X*NOT TOOLED	ASSEMBLY NUMBER	PART CHARACTERISTICS				X*NOT TOOLED	ASSEMBLY ITEM NUMBER	PART CHARACTERISTICS				CHARACTERISTICS LEGEND																																																		
			EXTERNAL CONNECTOR SIZE	NUMBER OF POSITIONS	P. C. BOARD THICKNESS	MOUNTING EARS OPTION			EXTERNAL CONNECTOR SIZE	NUMBER OF POSITIONS	P. C. BOARD THICKNESS	MOUNTING EARS OPTION	EXTERNAL CONNECTOR BODY DIMENSIONS: AVAILABLE IN 4, 6, AND 8 POSITION BODY																																																		
L	42878-4216	4 POS. BODY	4		.062	YES	42878-6216	6 POS. BODY	6		.062	YES	NUMBER OF CONTACT POSITIONS: CONNECTOR SIZE 4 ACCOMMODATES 2, 4, OR 6 TERMINALS; CONNECTOR SIZE 6 ACCOMMODATES 2, 4, OR 6 TERMINALS; CONNECTOR SIZE 8 ACCOMMODATES 2, 4, 6, 8, OR 10 TERMINALS																																																		
	42878-4218	↑	4		.062	NO	42878-6218	↑	6		.062	NO	POLARIZATION OPTION: (AVAILABLE ON CONNECTOR SIZE 8 ONLY) "NO"= WITHOUT KEYING SLOT "YES"= WITH KEYING SLOT																																																		
	42878-4264		4		.125	YES	42878-6264		6		.125	YES	MOUNTING EARS OPTION: "YES"= PART WITH MOUNTING EARS "NO"= PART WITHOUT MOUNTING EARS																																																		
	42878-4266		4		.125	NO	42878-6266		6		.125	NO	(SEE SHEET 1 & 2 FOR PART DESCRIPTIONS AND DIMENSIONS)																																																		
	42878-4360		2		.062	YES	42878-6360		4		.062	YES																																																			
	42878-4362		2		.062	NO	42878-6362		4		.062	NO																																																			
K	42878-4408	↓	2		.125	YES	42878-6408		4		.125	YES																																																			
	42878-4410	4 POS. BODY	2		.125	NO	42878-6410		4		.125	NO																																																			
J							42878-6504		2		.062	YES																																																			
							42878-6506		2		.062	NO																																																			
							42878-6552	↓	2		.125	YES																																																			
							42878-6554	6 POS. BODY	2		.125	NO																																																			
I																																																															
H																																																															
G																																																															
F																																																															
E																																																															
D																																																															
C																																																															
B																																																															
A																																																															
<table><tr><td rowspan="4">SEE SHEET ONE EC NO: UCP2004-1617 DRAWNLSCHMIDT 2004/03/03 CHKDLSCHMIDT 2004/03/03 APPR.FSMITH 2004/03/03</td><td rowspan="4">DESCRIPTION (REV)</td><td rowspan="4">QUALITY SYMBOLS ▽.0 ▽.0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td rowspan="2">SCALE ---</td><td rowspan="2">DESIGN UNITS INCH</td><td rowspan="2">THIRD ANGLE PROJECTION</td><td rowspan="2">REVISE ON CAD ONLY</td></tr><tr><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>±.---</td><td>±.---</td><td rowspan="2">DIMENSION STYLE IN/MM</td><td rowspan="2">DRAWN BY BAP</td><td rowspan="2">DATE 1992/04/09</td><td rowspan="4">TITLE ASSEMBLY, VERTICAL LOW PROFILE MODULAR JACKS (CONNECTOR SIZE 4 & 6)</td></tr><tr><td>3 PLACES</td><td>±.---</td><td>±.---</td></tr><tr><td>2 PLACES</td><td>±.---</td><td>±.---</td><td rowspan="2">CHECKED BY BAP</td><td rowspan="2">DATE 1992/04/09</td><td rowspan="4">MATERIAL NO. MOLEX</td><td rowspan="4">DOCUMENT NO. SDA-42878-XXXX</td><td rowspan="4">SHEET NO. 4 OF 5</td></tr><tr><td>1 PLACE</td><td>±.---</td><td>±.---</td></tr><tr><td colspan="3">ANGULAR ±1/2°</td><td rowspan="2">APPROVED BY RAS</td><td rowspan="2">DATE 1992/04/09</td><td colspan="3">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr><tr><td colspan="3">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td></tr></table>																					SEE SHEET ONE EC NO: UCP2004-1617 DRAWNLSCHMIDT 2004/03/03 CHKDLSCHMIDT 2004/03/03 APPR.FSMITH 2004/03/03	DESCRIPTION (REV)	QUALITY SYMBOLS ▽.0 ▽.0	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	REVISE ON CAD ONLY	mm	INCH	4 PLACES	±.---	±.---	DIMENSION STYLE IN/MM	DRAWN BY BAP	DATE 1992/04/09	TITLE ASSEMBLY, VERTICAL LOW PROFILE MODULAR JACKS (CONNECTOR SIZE 4 & 6)	3 PLACES	±.---	±.---	2 PLACES	±.---	±.---	CHECKED BY BAP	DATE 1992/04/09	MATERIAL NO. MOLEX	DOCUMENT NO. SDA-42878-XXXX	SHEET NO. 4 OF 5	1 PLACE	±.---	±.---	ANGULAR ±1/2°			APPROVED BY RAS	DATE 1992/04/09	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		
SEE SHEET ONE EC NO: UCP2004-1617 DRAWNLSCHMIDT 2004/03/03 CHKDLSCHMIDT 2004/03/03 APPR.FSMITH 2004/03/03	DESCRIPTION (REV)	QUALITY SYMBOLS ▽.0 ▽.0	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	REVISE ON CAD ONLY																																																							
			mm	INCH																																																											
			4 PLACES	±.---	±.---	DIMENSION STYLE IN/MM	DRAWN BY BAP	DATE 1992/04/09	TITLE ASSEMBLY, VERTICAL LOW PROFILE MODULAR JACKS (CONNECTOR SIZE 4 & 6)																																																						
			3 PLACES	±.---	±.---																																																										
2 PLACES	±.---	±.---	CHECKED BY BAP	DATE 1992/04/09	MATERIAL NO. MOLEX	DOCUMENT NO. SDA-42878-XXXX	SHEET NO. 4 OF 5																																																								
1 PLACE	±.---	±.---																																																													
ANGULAR ±1/2°			APPROVED BY RAS	DATE 1992/04/09				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																																																															
to frame D.P.M.E.T Rev. C 2002/05/05		19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1																																											