


DESCRIPTION

- 44.1 MHz SAW filter with 10 MHz bandwidth for CATV applications.
- 38.6 x 25.7 mm DIP package, 8 pins.
- RoHS compliant.

TYPICAL PERFORMANCE



Horizontal: 2.5 MHz/div

Vertical (from top): Magnitude 10 dB/div
Magnitude 1 dB/div
Group Delay 50 ns/div

SPECIFICATION


Parameter	Min	Typ	Max	Units
Center Frequency (nominal)	-	44.10	-	MHz
Insertion Loss	-	26.50	30	dB
Lower 3 dB point	-	38.80	39.025	MHz
Upper 3 dB point	49.025	49.40	-	MHz
Lower 50 dB point	37.775	38.20	-	MHz
Upper 50 dB point	-	50.10	50.275	MHz
Rejection (10-37.775 MHz)	45	55	-	dB
Rejection (50.275-70 MHz)	45	55	-	dB
Passband Amplitude Ripple	-	0.3	0.6	dB
Passband Phase Ripple	-	3	5	deg p-p
Passband GD Ripple	-	40	75	ns p-p
Absolute Delay	-	2.9	-	us
Ambient Temperature (Tref)	25			°C
Source/Load impedance	50			Ω

- Notes:
1. Average of lower & upper 3 dB frequencies.
 2. Typical change of filter frequency response with temperature is $\Delta f = (T - T_{ref}) * T_c * F_c$, in ppm.

MAXIMUM RATINGS

Parameter	Min	Typ	Max	Units
Storage Temperature Range	-40	50	85	°C
Temperature Coefficient of Frequency (Tc) ²	-	-72	-	ppm/°C
Input Power Level	-	-	+13	dBm


MATCHING CIRCUIT



Notes:

1. External matching components are not required.

PACKAGE OUTLINE



Units: mm

Tolerances are ± 0.15 mm except where indicated.

Pin Configuration:

Input:	1
Input return:	2
Output:	6
Output return:	5
Ground:	3,4,7,8

**ISO 9001
 Registered**

All specifications are believed to be accurate and reliable. However, Spectrum Microwave reserves the right to make changes without notice.
 © 2011 All rights reserved.

Spectrum Microwave, Inc.
400 Nickerson Road, Marlborough, MA 01752, USA • Phone 508-251-6400 • Fax 508-251-6401
www.SpectrumMicrowave.com

DSSF0044BA01954T Rev X3 11-Feb-11
 Page 3 of 3