





PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL


PC BOARD VERSIONS		
PRODUCT NR:	PCB THICKNESS	DIM A
85863-X02/X02LF	1.6	2.90
85863-X12/X12LF	2.4	3.53

LOADING CONFIGURATION
FULLY LOADED

* SPECIFY LOADING P/N SEE PAGE 2



- NOTES:
- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
 - 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - 3 INDICATED HOLES ARE UNPLATED.
 - 4 PLATING SOLDER TAILS 2-8 μ m SnPb 90-97 OR 2-8 μ m PURE Sn
 - 5 PRODUCT MARKING: PART NUMBER & BATCH ID.
 - 6 SET BACK FOR TAIL BLOCK
 - 7 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD.
 - 8 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 - 9 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.



RECOMMENDED HOLE PATTERN, COMPONENT SIDE.

PC BOARD THICKNESS $\approx$ 0.2
(SEE TABLE)

mat'l. code		SEE NOTE		tolerances unless otherwise specified		CUSTOMER COPY		FCI ELECTRONICS	
ltr	ecr	no	dr	date					
H	06-012848	01	05/06/12	linear					
				angles					
D	0604-0104	CLU	041222	dr	R. VISSCHERS	941005			
E	0607-0169	Cent	05/15/07	engr	E. FEIJEN	941005			
F	0608-0171	TER	8/26/08	chr	E. FEIJEN	941005			
G	0609-0068	Cent	06/06/08	app	E. FEIJEN	941005			
sheet	revision	H	H						
index	sheet	1	2						

projection	title	product family	code
ϕ	5 ROW R.A. S.T.B. SIGNAL RECEPT. 12 mm MOD.PP	METRAL (tm)	213
mm	size dwg no		1 of 2
scale	A2	85863	

This data is classified as "unclassified" information. Reproduction or dissemination of this data is not prohibited. However, the use of this data for any purpose other than that for which it was originally intended is prohibited. Property of FCI Inc.

All rights are reserved. Reproduction or use in any form without the written authority of FCI Inc. is prohibited. Property of FCI Inc.

PRODUCT NO	PCB THICKNESS	DIM "A"	ROW	6	5	4	3	2	1
85863-X03 85863-X03LF	1.6	2.90	E	X	X	X	-	X	X
			D	X	X	X	-	X	X
			C	X	X	X	X	-	-
			B	X	X	X	-	X	X
			A	X	X	X	-	X	X

LOAD PATTERN	
X	LOADED
-	NOT LOADED

mat'l. code SEE NOTE				tolerances unless otherwise specified		CUSTOMER COPY		FCI ELECTRONICS www.fciconnect.com	
ltr	ecr	no	dr	date	linear	projection	title	5 ROW R.A. S.T.B. SIGNAL RECEPT. 12 mm MOD.PP	
H					angles				
					dr	R. VISSCHERS 941005	mm	product family	METRAL (tm)
					engr	E. FEIJEN 941005	scale	size dwg no	213
					chr	E. FEIJEN 941005	5:1	A2	85863
					app	E. FEIJEN 941005			sheet 2 of 2
sheet index	revision	sheet							