


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		A1	ADD DASH 1-0, 1-1	29NOV11	SW	RZ

- NOTE:
1. DIMENSIONS IN [] ARE IN INCHES.
 2. 0.5 dB MAX INSERTION LOSS.
 3. 55 dB MIN RETURN LOSS.
 4. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE STANDARD TEC-138-702



60±0.6 [2362±24]	1-5492022-1
40±0.4 [1575±16]	1-5492022-0
6.0±0.08 [236.22±3.15]	5492022-9
30±0.3 [1181±12]	5492022-8
20±0.3 [787±12]	5492022-7
15±0.15 [591±6]	5492022-6
10±0.15 [394±6]	5492022-5
5±0.08 [197±3]	5492022-4
3±0.05 [118±2]	5492022-3
2±0.05 [79±2]	5492022-2
1±0.05 [39±2]	5492022-1
L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.S. VASU 27 JAN 08		 TE Connectivity							
		CHK J. DUNCAN 27 JAN 08									
DIMENSIONS: METERS[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. DUNCAN 27 JAN 08		NAME					
		0 PLC ± -		PRODUCT SPEC		CABLE ASSEMBLY, FIBER OPTIC, SINGLEMODE LDD FC(NG) TO FC(NG), OPTIMATE					
		1 PLC ± -		—							
		2 PLC ± -		—							
		3 PLC ± -		APPLICATION SPEC							
		4 PLC ± -		—							
MATERIAL		FINISH		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
—		—		—		A2	00779	C=5492022	—		
CUSTOMER DRAWING						SCALE	1:1	SHEET	1 of 1	REV	A1