



DS1489/DS1489A

Quad Line Receiver


General Description

The DS1489/DS1489A are quad line receivers designed to interface data terminal equipment with data communications equipment. They are constructed on a single monolithic silicon chip. These devices satisfy the specifications of EIA Standard RS-232D. The DS1489/DS1489A meet and exceed the specifications of MC1489/MC1489A and are pin-for-pin replacements.

Features


- Four separate receivers per package
- Programmable threshold
- Built-in input threshold hysteresis
- "Fail safe" operating mode: high output for open inputs
- Inputs withstand $\pm 30V$

Schematic and Connection Diagrams



(1/4 of unit shown)
DS1489: $R_F = 10k$
DS1489A: $R_F = 2k$

Dual-In-Line Package



Top View

Top View
Order Number DS1489M, DS1489N
DS1489AM or DS1489AN
See NS Package Number M14A or N14A

See NS Package Number M14A or N14A

AC Test Circuit and Voltage Waveforms




FIGURE 1.

Absolute Maximum Ratings (Note 2)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/Distributors for availability and specifications.

Power Supply Voltage	10V
Input Voltage Range	$\pm 30V$
Output Load Current	20 mA
Power Dissipation (Note 3)	1W
Operating Temperature Range	0°C to +75°C

Storage Temperature Range -65°C to +150°C

Maximum Power Dissipation (Note 1) at 25°C

Molded DIP Package	1207 mW
SO Package	1042 mW

Lead Temperature (Soldering, 4 sec.) 260°C

Note 1: Derate molded DIP package 9.7 mW/°C above 25°C; derate SO package 8.33 mW/°C above 25°C.

Electrical Characteristics (Notes 3, 4, 5)

DS1489/DS1489A: The following apply for $V_{CC} = 5.0V \pm 1\%$, $0°C \leq T_A \leq +75°C$ unless otherwise specified.

Symbol	Parameter	Conditions			Min	Typ	Max	Units
V_{TH}	Input High Threshold Voltage	$V_{OUT} \leq 0.45V$, $I_{OUT} = 10\text{ mA}$	DS1489	$T_A = 25°C$	1.0	1.25	1.5	V
					0.9		1.6	V
		$V_{OUT} \geq 2.5V$, $I_{OUT} = -0.5\text{ mA}$	DS1489A	$T_A = 25°C$	1.75	2.00	2.25	V
					1.55		2.40	V
V_{TL}	Input Low Threshold Voltage	$V_{OUT} \geq 2.5V$, $I_{OUT} = -0.5\text{ mA}$		$T_A = 25°C$	0.75	1.00	1.25	V
					0.65		1.35	V
		$V_{IN} = +25V$			+3.6	+5.6	+8.3	mA
					-3.6	-5.6	-8.3	mA
I_{IN}	Input Current	$V_{IN} = +3V$			+0.43	+0.53		mA
					-0.43	-0.53		mA
		$V_{IN} = -3V$			2.6	3.8	5.0	V
					2.6	3.8	5.0	V
V_{OH}	Output High Voltage	$I_{OUT} = -0.5\text{ mA}$	$V_{IN} = 0.75V$		0.33	0.45	0.45	V
V_{OL}	Output Low Voltage	$V_{IN} = 3.0V$, $I_{OUT} = 10\text{ mA}$						
I_{SC}	Output Short Circuit Current	$V_{IN} = 0.75V$			-3.0			mA
I_{CC}	Supply Current	$V_{IN} = 5.0V$				14	26	mA
P_d	Power Dissipation	$V_{IN} = 5.0V$			70	130		mW

Switching Characteristics

$V_{CC} = 5V$, $T_A = 25°C$

Symbol	Parameter	Conditions	Min	Typ	Max	Units
t_{pd1}	Input to Output "High" Propagation Delay	$R_L = 3.9k$, (Figure 1) (AC Test Circuit)		28	85	ns
t_{pd0}	Input to Output "Low" Propagation Delay	$R_L = 390\Omega$, (Figure 1) (AC Test Circuit)		20	50	ns
t_r	Output Rise Time	$R_L = 3.9k$, (Figure 1) (AC Test Circuit)		110	175	ns
t_f	Output Fall Time	$R_L = 390\Omega$, (Figure 1) (AC Test Circuit)	9	20		ns

Note 2: "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. Except for "Operating Temperature Range" they are not meant to imply that the devices should be operated at these limits. The table of "Electrical Characteristics" provides conditions for actual device operation.

Note 3: Unless otherwise specified min/max limits apply across the 0°C to +75°C temperature range for the DS1489 and DS1489A.

Note 4: All currents into device pins shown as positive, out of device pins as negative, all voltages referenced to ground unless otherwise noted. All values shown as max or min on absolute value basis.

Note 5: These specifications apply for response control pin = open.

Typical Characteristics $V_{CC} = 5.0V$, $T_A = +25^\circ C$ unless otherwise noted




FIGURE 2. Input Current




FIGURE 5. Input Threshold Voltage vs Temperature




FIGURE 3. DS1489 Input Threshold Voltage Adjustment




FIGURE 6. Input Threshold vs Power Supply Voltage




FIGURE 4. DS1489A Input Threshold Voltage Adjustment





FIGURE 7. Noise Rejection vs Capacitance for DS1489A


Typical Application Information



*Optional for noise filtering.

Applications Using the Response Control Pin


Noise Filter



DS005777-13

Threshold Shift See Figures 3, 4


3.000



DS005777-14


Noise Filter and Threshold Shift

S. S. JAGAN, ET AL.




DS005777-15



Application of DS1488, DS1489A and INS8250



DS005777-16



Physical Dimensions inches (millimeters) unless otherwise noted



Molded Dual-In-Line Package (N)
Order Number DS1489N or DS1489AN
NS Package Number N14A

LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF NATIONAL SEMI-CONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.



National Semiconductor Corporation
Americas
Tel: 1-800-272-9959
Fax: 1-800-737-7018
Email: support@nsc.com
www.national.com

National Semiconductor Europe
Fax: +49 (0) 1 80-530 85 86
Email: europe.support@nsc.com
Deutsch Tel: +49 (0) 1 80-530 85 85
English Tel: +49 (0) 1 80-532 78 32
Français Tel: +49 (0) 1 80-532 93 58
Italiano Tel: +49 (0) 1 80-534 16 80

National Semiconductor Asia Pacific Customer Response Group
Tel: 65-2544466
Fax: 65-2504466
Email: sea.support@nsc.com

National Semiconductor Japan Ltd.
Tel: 81-3-5620-6175
Fax: 81-3-5620-6179