

Ultrafast Rectifier

80 A, 1000 V

RURG80100-F085

Description

The RURG80100-F085 is an ultrafast diode with low forward voltage drop and soft recovery characteristics. Its low voltage drop and ultrafast soft recovery minimize conduction loss and electrical noise in power switching circuit. Meanwhile, the robust design and high quality manufacture process make it a reliable device for heavy duty automotive applications.

This device is intended to be used in a variety of automotive power-train applications for purposes like freewheeling, clamping, rectification, bootstrap and snubber, etc. It's also an ideal device for non-automotive applications which requires a higher reliability performance.

Features

- Ultrafast and Soft Recovery
- Low Forward Voltage ($V_F = 1.56 \text{ V (Typ.) @ } I_F = 80 \text{ A}$)
- High Speed Switching ($t_{rr} = 242 \text{ ns (Typ.) @ } I_F = 80 \text{ A}$)
- Avalanche Energy Rated
- AEC-Q101 Qualified and PPAP Capable
- This is a Pb-Free Device


Applications

- EV and HEV On-Board Charger
- Stationary Charger
- Other Automotive Applications
- General Power Supply Requiring Higher Reliability




ON Semiconductor®

www.onsemi.com



TO-247-2LD
CASE 340CL

MARKING DIAGRAM



RURG80100	= Specific Device Code
\$Y	= ON Semiconductor Logo
&Z	= Assembly Plant Code
&3	= Data Code (Year & Week)
&K	= Lot

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

RURG80100–F085

ABSOLUTE MAXIMUM RATINGS $T_C = 25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Ratings	Units
V_{RRM}	Peak Repetitive Reverse Voltage	1000	V
V_{RWM}	Working Peak Reverse Voltage	1000	V
V_R	DC Blocking Voltage	1000	V
$I_{F(AV)}$	Average Rectified Forward Current @ $T_C = 25^\circ\text{C}$	80	A
I_{FSM}	Non-repetitive Peak Surge Current (Halfwave 1 Phase 50 Hz)	240	A
E_{AVL}	Avalanche Energy (1.6 A, 40 mH)	50	mJ
T_J, T_{STG}	Operating Junction and Storage Temperature	-55 to +175	$^\circ\text{C}$

THERMAL CHARACTERISTICS $T_C = 25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Max.	Units
$R_{\theta JC}$	Maximum Thermal Resistance, Junction to Case	0.3	$^\circ\text{C/W}$
$R_{\theta JA}$	Maximum Thermal Resistance, Junction to Ambient	45	$^\circ\text{C/W}$

PACKAGE MARKING AND ORDERING INFORMATION


Device Marking	Device	Package	Pacing Type	Qty per Tube
RURG80100	RURG80100–F085	TO–247	–	30

ELECTRICAL CHARACTERISTICS $T_C = 25^\circ\text{C}$ unless otherwise noted


Symbol	Parameter	Conditions		Min.	Typ.	Max	Units
I _R	Instantaneous Reverse Current	V _R = 1000 V	T _C = 25°C	–	–	250	μA
			T _C = 175°C	–	–	1.5	mA
V _{FM} (Note 1)	Instantaneous Forward Voltage	I _F = 80 A	T _C = 25°C	–	1.56	2.0	V
			T _C = 175°C	–	1.35	1.7	V
t _{rr} (Note 2)	Reverse Recovery Time	I _F = 1 A, di/dt = 100 A/μs, V _{CC} = 650 V	T _C = 25°C	–	122	158	ns
		I _F = 80 A, di/dt = 100 A/μs, V _{CC} = 650 V	T _C = 25°C T _C = 175°C	– –	242 979	314 –	ns ns
t _a	Reverse Recovery Time	I _F = 80 A, di/dt = 100 A/μs, V _{CC} = 650 V	T _C = 25°C	–	74	–	ns
t _b			–	168	–	ns	
Q _{rr}	Reverse Recovery Charge		–	751	–	nC	

1. Pulse: Test Pulse width = 300 μs , Duty Cycle = 2%.
2. Guaranteed by design.


TEST CIRCUIT AND WAVEFORMS




t_{rr} Test Circuit



t_{rr} Waveforms and Definitions



Avalanche Energy Test Circuit



Avalanche Current and Voltage Waveforms

Figure 1. Test Circuit and Waveforms

TYPICAL PERFORMANCE CHARACTERISTICS (continued)




Figure 2. Typical Forward Voltage Drop vs. Forward Current




Figure 3. Typical Reverse Current vs. Reverse Voltage




Figure 4. Typical Junction Capacitance




Figure 5. Typical Reverse Recovery Time vs. di/dt




Figure 6. Typical Reverse Recovery Current vs. di/dt




Figure 7. Forward Current Derating Curve

TYPICAL PERFORMANCE CHARACTERISTICS (continued)




Figure 8. Reverse Recovery Charge





Figure 9. Transient Thermal Response Curve

TO-247-2LD
CASE 340CL
ISSUE A


DATE 03 DEC 2019



NOTES: UNLESS OTHERWISE SPECIFIED.

- A. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
- B. ALL DIMENSIONS ARE IN MILLIMETERS.
- C. DRAWING CONFORMS TO ASME Y14.5 - 2009.
- D. DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED BY L1.
- E. LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY L1.

GENERIC
MARKING DIAGRAM*



XXXX = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
ZZ = Assembly Lot Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON13850G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TO-247-2LD	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales