

**SURFACE MOUNT
GLASS PASSIVATED BRIDGE RECTIFIERS**

**REVERSE VOLTAGE – 50 to 1200 Volts
FORWARD CURRENT – 1.5 Amperes**


FEATURES

- Rating to 1200V PRV
- Ideal for printed circuit board
- Low forward voltage drop high current capability
- Reliable low cost construction utilizing molded plastic technique
- UL recognized file # E95060

MECHANICAL DATA

- Case Material: molding compound, UL flammability classification 94V-0
- Polarity: As marked on the body
- Mounting Position: Any
- Weight: 360mg (Approximate)

DF-S



DF-S		
DIM	MIN	MAX
A	8.20	8.50
B	6.20	6.50
C	9.80	10.30
D	7.40	7.90
E	2.40	2.60
F	5.00	5.20
G	1.00	--
H	.076	.330
I	.220	.300
J	1.02	1.53
All dimension in millimeter		

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

ABSOLUTE RATINGS

PARAMETER	SYMBOL	DF15005S	DF1501S	DF1502S	DF1504S	DF1506S	DF1508S	DF1510S	DF1512S	UNIT
Device marking code	Note	DF15005S	DF1501S	DF1502S	DF1504S	DF1506S	DF1508S	DF1510S	DF1512S	--
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	1200	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	1200	V
Average rectified output current per device @ $T_C = 120^\circ\text{C}$	$I_{(AV)}$	1.5								A
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load (JEDEC METHOD)	I_{FSM}	50								A
Peak forward surge current 1 ms single half sine-wave superimposed on rated load (JEDEC METHOD)	I_{FSM}	100								A
$I^2 t$ rating for fusing ($t < 8.3\text{ms}$)	$I^2 t$	10.4								A^2S
Operating and storage temperature range	T_J, T_{STG}	-55 to +150								$^\circ\text{C}$

STATIC ELECTRICAL CHARACTERISTICS

PARAMETER	TEST CONDITION		SYMBOL	MAX.	UNIT
Forward voltage	$I_F = 1.5\text{A}$	$T_J = 25^\circ\text{C}$	V_F	1.1	V
Leakage current	V_R at rated	$T_J = 25^\circ\text{C}$ $T_J = 125^\circ\text{C}$	I_R	10 500	μA
Typical junction capacitance (Note 1)			C_J	25	pF

THERMAL CHARACTERISTICS

PARAMETER	SYMBOL	TYP.	UNIT
Typical thermal resistance (Note 2)	R_{thJA}	40	$^\circ\text{C/W}$
	R_{thJC}	8	
	R_{thJL}	20	

Note :

- (1) Measured at 1.0MHz and applied reverse voltage of 4.0V DC
- (2) Thermal resistance junction to ambient, case and lead in accordance with JESD-51. Unit mounted on P.C.B with 0.5 x 0.5" (13 x 13 mm) copper pad per pin.

REV. 14, MAR.-2015, KBDA02

RATING AND CHARACTERISTIC CURVES DF1505S thru DF1512S

LITEON

FIG.1- FORWARD CURRENT DERATING CURVE




FIG.2- MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.3- TYPICAL FORWARD CHARACTERISTICS




FIG.4- TYPICAL JUNCTION CAPACITANCE




FIG.5- NON-REPETITIVE SURGE CURRENT





FIG.6- TYPICAL REVERSE CHARACTERISTICS



Important Notice and Disclaimer

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

LSC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does LSC assume any liability for application assistance or customer product design. LSC does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.