

Precision Voltage References

FEATURES

- Trimmed Output $\pm 0.3\%$
- Low Drift— $5\text{ppm}/^\circ\text{C}$ Typ
- Low Noise— $3\text{ppm}_{(\text{P-P})}$
- High Line Rejection
- Temperature Output—REF-02
- Low Supply Current 1.4mA Max

APPLICATIONS

- A/D and D/A Converters
- Precision Regulators
- Constant Current Sources
- V/F Converters
- Bridge Excitation

DESCRIPTION


The REF-01/REF-02 are precision 10V and 5V bandgap references which provide stable output voltages over a wide range of operating conditions. Output voltage is accurate to $\pm 0.3\%$ with a low $5\text{ppm}/^\circ\text{C}$ typical temperature coefficient. The REF-01 and REF-02 are excellent choices for applications where low drift, moderate accuracy, low power consumption and low cost are considerations.

The REF-02 includes a temperature output pin which provides a linear voltage proportional to absolute temperature.


For lower drift and higher accuracy references, please see the LT1019 and LT1021 data sheets.

LT, LTC and LT are registered trademarks of Linear Technology Corporation.

TYPICAL APPLICATION



Output Voltage Temperature Drift



REF-01/REF-02

ABSOLUTE MAXIMUM RATINGS (Note 1)

REF-01/REF-02 A, E, H	40V
REF-01C/REF-02C	30V
Power Dissipation	500mW
Output Short-Circuit Duration	
To Ground	Indefinite
To $V_{IN} \leq 16V$	Indefinite
To $V_{IN} > 16V$	Not Allowed

Storage Temperature Range	–65°C to 150°C
Operating Temperature	
REF-01/REF-02, REF-01A/REF-02A ...	–55°C to 125°C
REF-01E/REF-02E, REF-01H/REF-02H,	
REF-01C/REF-02C, REF-01D/REF-02D	0°C to 70°C
Lead Temperature (Soldering, 10 sec)	300°C

PACKAGE/ORDER INFORMATION

TOP VIEW NC* 1 8 NC* INPUT 2 7 NC* TEMP** 3 6 OUTPUT 4 5 TRIM GND (CASE) H PACKAGE 8-LEAD TO-5 METAL CAN $T_{JMAX} = 150^{\circ}\text{C}$, $\theta_{JA} = 150^{\circ}\text{C/W}$, $\theta_{JC} = 45^{\circ}\text{C/W}$ * INTERNALLY CONNECTED. DO NOT CONNECT EXTERNALLY. ** DO NOT CONNECT ON REF-01	ORDER PART NUMBER <table><tr><td>REF01AH</td><td>REF02AH</td></tr><tr><td>REF01H</td><td>REF02H</td></tr><tr><td>REF01EH</td><td>REF02EH</td></tr><tr><td>REF01HH</td><td>REF02HH</td></tr><tr><td>REF01CH</td><td>REF02CH</td></tr><tr><td></td><td>REF02DH</td></tr></table>	REF01AH	REF02AH	REF01H	REF02H	REF01EH	REF02EH	REF01HH	REF02HH	REF01CH	REF02CH		REF02DH
REF01AH	REF02AH												
REF01H	REF02H												
REF01EH	REF02EH												
REF01HH	REF02HH												
REF01CH	REF02CH												
	REF02DH												
TOP VIEW NC* 1 8 NC* INPUT 2 7 NC* TEMP** 3 6 OUTPUT 4 5 TRIM N8 PACKAGE 8-LEAD PDIP $T_{JMAX} = 100^{\circ}\text{C}$, $\theta_{JA} = 130^{\circ}\text{C/W}$ * INTERNALLY CONNECTED. DO NOT CONNECT EXTERNALLY. ** DO NOT CONNECT ON REF-01	ORDER PART NUMBER <table><tr><td>REF01EN8</td><td>REF02EN8</td></tr><tr><td>REF01HN8</td><td>REF02HN8</td></tr><tr><td>REF01CN8</td><td>REF02CN8</td></tr><tr><td></td><td>REF02DN8</td></tr></table>	REF01EN8	REF02EN8	REF01HN8	REF02HN8	REF01CN8	REF02CN8		REF02DN8				
REF01EN8	REF02EN8												
REF01HN8	REF02HN8												
REF01CN8	REF02CN8												
	REF02DN8												
TOP VIEW NC* 1 8 NC* INPUT 2 7 NC* TEMP** 3 6 OUTPUT 4 5 TRIM J8 PACKAGE 8-LEAD CERDIP $T_{JMAX} = 150^{\circ}\text{C}$, $\theta_{JA} = 100^{\circ}\text{C/W}$	ORDER PART NUMBER <table><tr><td>REF01EJ8</td><td>REF02EJ8</td></tr><tr><td>REF01HJ8</td><td>REF02HJ8</td></tr><tr><td>REF01CJ8</td><td>REF02CJ8</td></tr><tr><td></td><td>REF02DJ8</td></tr></table>	REF01EJ8	REF02EJ8	REF01HJ8	REF02HJ8	REF01CJ8	REF02CJ8		REF02DJ8				
REF01EJ8	REF02EJ8												
REF01HJ8	REF02HJ8												
REF01CJ8	REF02CJ8												
	REF02DJ8												

OBSOLETE PACKAGE

Consider the N Package for Alternate Source

OBSOLETE PACKAGE

Consider the N Package for Alternate Source

Consult LTC Marketing for parts specified with wider operating temperature ranges.

ELECTRICAL CHARACTERISTICS $V_{IN} = 15V$, $T_A = 25^\circ C$ unless otherwise noted.

SYMBOL	PARAMETER	CONDITIONS	REF-01A/E, REF-02A/E			REF-01H, REF-02H			UNITS
			MIN	TYP	MAX	MIN	TYP	MAX	
V_O	Output Voltage	$I_L = 0mA$	9.97	10	10.03	9.95	10	10.05	V
			4.985	5	5.015	4.975	5	5.025	V
	Output Adjustment Range	$R_P = 10k\Omega$	± 3	5, –27		± 3	5, –27		%
			± 3	5, –13		± 3	5, –13		%
e_{nP-P}	Output Voltage Noise	0.1Hz to 10Hz (Note 7)		20			20		μV_{P-P}
				10			10		μV_{P-P}
V_{IN}	Input Voltage Range		12		40	12		40	V
			7		40	7		40	V
$\frac{\Delta V_{OUT}}{\Delta V_{IN}}$	Line Regulation (Note 2)	$(V_{OUT} + 3V) \leq V_{IN} \leq 33V$		0.0001	0.010		0.0001	0.010	%/V
$\frac{\Delta V_{OUT}}{\Delta I_{OUT}}$	Load Regulation (Note 2)	$I_L = 0mA$ to 10mA	REF-01	0.0005	0.008	REF-01H	0.0005	0.010	%/mA
				0.0010	0.010		0.001	0.010	%/mA
I_Q	Quiescent Supply Current	No Load		0.65	1.4		0.65	1.4	mA
I_{OUT}	Load Current Sink Current		10	20		10	20		mA
			–0.3	–20		–0.3	–20		mA
I_{SC}	Short-Circuit Current	$V_O = 0V$		25			25		mA
V_T	Temperature Voltage Output	(Note 3)	REF-02 Only	620			620		mV

ELECTRICAL CHARACTERISTICS $V_{IN} = 15V$, $T_A = 25^\circ C$ unless otherwise noted.

SYMBOL	PARAMETER	CONDITIONS	REF-01C, REF-02C			REF-02D			UNITS
			MIN	TYP	MAX	MIN	TYP	MAX	
V_O	Output Voltage	$I_L = 0mA$	9.9	10	10.1				V
		REF-01 REF-02	4.95	5	5.05	4.9	5	5.1	V
	Output Adjustment Range	$R_P = 10k\Omega$		5, -27					%
		REF-01 REF-02	± 2.7	5, -13		± 2	5, -13		%
e_{NP-P}	Output Voltage Noise	0.1Hz to 10Hz (Note 7)		30 12			12		μV_{P-P} μV_{P-P}
$\frac{\Delta V_{OUT}}{\Delta V_{IN}}$	Line Regulation (Note 2)	$(V_{OUT} + 3V) \leq V_{IN} \leq 33V$		0.0001	0.015		0.0001	0.04	%/V
$\frac{\Delta V_{OUT}}{\Delta I_{OUT}}$	Load Regulation (Note 2)	$I_L = 0mA$ to 8mA $I_L = 0mA$ to 4mA		0.0005	0.015		0.001	0.04	%/mA %/mA
I_Q	Quiescent Supply Current	No Load		0.65	1.6		0.65	2	mA
I_{OUT}	Load Current Sink Current		8 -0.2	20 20		8 -0.2	20 20		mA mA
I_{SC}	Short-Circuit Current	$V_O = 0V$		25			25		mA
V_T	Temperature Voltage Output	(Note 3) REF-02 Only		620			620		mV

The ● denotes the specifications which apply over the full operating temperature range, otherwise specifications are at $T_A = 25^\circ C$.
 $V_{IN} = 15V$, $-55^\circ C \leq T_A \leq \pm 125^\circ C$ for REF-01A/REF-02A and REF-01/REF-02, $0^\circ C \leq T_A \leq 70^\circ C$ for REF-01E/REF-02E and REF-01H/REF-02H, $I_L = 0mA$ unless otherwise noted.

SYMBOL	PARAMETER	CONDITIONS		REF-01A/E, REF-02A/E			REF-01H/REF-02H			UNITS
				MIN	TYP	MAX	MIN	TYP	MAX	
$\frac{\Delta V}{\Delta T}$	Output Voltage Change with Temperature (Notes 4, 5)	$0^\circ C \leq T_A \leq 70^\circ C$ $-55^\circ C \leq T_A \leq 125^\circ C$	● ●		0.02 0.09	0.06 0.15		0.035 0.144	0.17 0.45	% %
TC	Output Voltage Temperature Coefficient	(Note 6)	●		5	8.5		8	25	ppm/ $^\circ C$
	Change in V_O Temperature Coefficient with Output Adjustment	$R_P = 10k\Omega$	●		0.5			0.5		ppm/%
$\frac{\Delta V_{OUT}}{\Delta V_{IN}}$	Line Regulation $(V_{OUT} + 3V) \leq V_{IN} \leq 33V$ (Note 2)	$0^\circ C \leq T_A \leq 70^\circ C$ $-55^\circ C \leq T_A \leq 125^\circ C$	● ●		0.0001 0.0001	0.012 0.015		0.0001 0.0001	0.012 0.015	%/V %/V
	Load Regulation ($I_L = 0mA$ to 8mA) (Note 2)	$0^\circ C \leq T_A \leq 70^\circ C$ $-55^\circ C \leq T_A \leq 125^\circ C$	● ●		0.002 0.002	0.010 0.012		0.002 0.002	0.012 0.015	%/mA %/mA
	Temperature Voltage Output Temperature Coefficient	(Note 3) REF-02	●		2.1			2.1		mV/ $^\circ C$

ELECTRICAL CHARACTERISTICS

The ● denotes the specifications which apply over the full operating temperature range, otherwise specifications are at $T_A = 25^\circ\text{C}$. $V_{IN} = 15\text{V}$, $0^\circ\text{C} \leq T_A \leq 70^\circ\text{C}$ and $I_L = 0\text{mA}$ unless otherwise noted.

SYMBOL	PARAMETER	CONDITIONS		REF-01C, REF-02C			REF-02D			UNITS
				MIN	TYP	MAX	MIN	TYP	MAX	
$\frac{\Delta V}{\Delta T}$	Output Voltage Change with Temperature	(Notes 4, 5)	●			0.45			1.7	%
TC	Output Voltage Temperature Coefficient	(Note 6)	●		8	65		8	250	ppm/ $^\circ\text{C}$
	Change in V_O Temperature Coefficient with Output Adjustment	$R_P = 10\text{k}\Omega$	●		0.5			0.5		ppm/%
$\frac{\Delta V_{OUT}}{\Delta V_{IN}}$	Line Regulation (Note 2)	$V_{IN} = 8\text{V to } 30\text{V}$	●		0.0001	0.018		0.0001	0.05	%/V
$\frac{\Delta V_{OUT}}{\Delta I_{OUT}}$	Load Regulation (Note 2)	$I_L = 0\text{mA to } 5\text{mA}$	●		0.002	0.018		0.002	0.05	%/mA
	Temperature Voltage Output Temperature Coefficient	(Note 3) REF-02	●		2.1			2.1		mV/ $^\circ\text{C}$

Note 1: Absolute Maximum Ratings are those values beyond which the life of a device may be impaired.

Note 2: Line and load regulation specifications include the effect of self heating.

Note 3: Limit current in or out of Pin 3 to 50nA and capacitance on Pin 3 to 30pF.

Note 4: ΔV is defined as the absolute difference between the maximum output voltage and the minimum output voltage over the specified temperature range expressed as a percentage of nominal output.

$$\Delta V = \left| \frac{V_{MAX} - V_{MIN}}{V_{OUT}} \right| \cdot 100$$

Note 5: ΔV specification applies trimmed or untrimmed.



Note 6: TC is defined as ΔV divided by the temperature range, i.e.,

$$TC = \frac{\Delta V}{T_{MAX} - T_{MIN}}$$

Note 7: 0.1Hz to 10Hz noise cannot be 100% tested on modern high speed test equipment, so Linear Technology does not put a guaranteed maximum specification on this parameter for standard units. 100% bench testing of 0.1Hz to 10Hz noise is available on special request. To ensure low output noise, Linear Technology *does* 100% test 10Hz to 1kHz noise. Consult factory for details.

PACKAGE DESCRIPTION

H Package
8-Lead TO-5 Metal Can (.230 Inch PCD)
 (Reference LTC DWG # 05-08-1321)



* LEAD DIAMETER IS UNCONTROLLED BETWEEN THE REFERENCE PLANE AND 0.045" BELOW THE REFERENCE PLANE


** FOR SOLDER DIP LEAD FINISH, LEAD DIAMETER IS $0.016 - 0.024$ (0.406 - 0.610)

H8 (TO-5) 0.230 PCD 1197

OBSOLETE PACKAGE

PACKAGE DESCRIPTION




J8 Package
8-Lead Cerdip (Narrow .300 Inch, Hermetic)
(Reference LTC DWG # 05-08-1110)



OBSOLETE PACKAGE

PACKAGE DESCRIPTION

N8 Package
8-Lead PDIP (Narrow .300 Inch)
 (Reference LTC DWG # 05-08-1510)



*THESE DIMENSIONS DO NOT INCLUDE MOLD FLASH OR PROTRUSIONS.
 MOLD FLASH OR PROTRUSIONS SHALL NOT EXCEED 0.010 INCH (0.254mm)

N8 1098

RELATED PARTS

PART NUMBER	DESCRIPTION	COMMENTS
LT1019	0.05%, 5ppm/°C Precision Reference	Pin Compatible with the REF-01, REF-02, Improved Specs