

PRODUCT NUMBER
89885-XXXXLF

RoHS COMPATIBLE, SEE NOTE 5

OPTIONAL LETTER

H: HIGH TEMPERATURE PRODUCT

NUMBER OF POSITIONS: 02 TO 50.

PLATING CODE

3= 0.76µm GOLD ON CONTACT AREA.
2µm MIN MATTE TIN ON TAIL.

4= 2µm MIN MATTE TIN FULL PLATED

8= 0.38µm GOLD ON CONTACT AREA.
2µm MIN MATTE TIN ON TAIL.

1.27µm Ni MIN UNDERPLATING

NOTES:

1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-0 .
LOW TEMPERATURE: COLOR BLUE.
HIGH TEMPERATURE: COLOR GREY

2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.

3 - 2 UP TO 4 POSITIONS PRODUCT PACKED IN PLASTIC BOX.

5 UP TO 50 POSITIONS PRODUCT PACKED IN TUBE.

4 - TO DETERMINE DIMENSIONS:

N = NUMBER OF POSITIONS

EXAMPLE: 8 POS: (N×2.54)-0.08=20.24 mm.

5 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

d - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.



b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.

c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004




mat'l. code				surface			tolerance			projection		product family	
SEE NOTES				ISO 1302			ISO 406 ISO 1101			DUBOX			
ltr	ecm no	dr	date	tolerances unless otherwise specified							title		
K	F03-0264	DLE	03.10.14	angles			±0.3				BtB RECEPT. VERT SR TMT		
L	F04-0347	DLE	04.11.10	linear									
M	F05-0236	DLE	05.08.08	#2					scale 5:1				
N	F06-0204	DLE	06.06.21	dr			G.SANCHEZ		02.01.25				
P	F07-0108	DLE	07.01.16	engr			P.NIZZI		94.02.10				
R	B-19123	LMU	14.10.21	chr			D.LEGRAND		02.01.25				
				appd			P.NIZZI		94.02.10				
sheet	revision	R	D										
index	sheet	1	2										




FCIconnect.com

Copyright FCI



FCIconnect.com

Copyright FCI

mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DUBOX											
ltr	ecn no	dr	date	tolerances unless		otherwise specified		 mm scale 5:1		title BtB RECEPT. VERT SR TMT											
A	F04—0347	DLE	04.11.10	angles	linear	±0.3															
B	F05—0230	DLE	05.08.08																		
C	F06—0204	DLE	06.06.21			±2'															
D	F07—0109	DLE	07.01.16	dr	D LEGRAND		04.11.10				dwg no				sheet 2 of —				size		
				engr	P.NIZZI		04.11.10				89885				A4						
				chr	D.LEGRAND		04.11.10														
				appd	P.NIZZI		04.11.10														
sheet index		revision sheet																			