

MN101C485 , MN101C487


Type			MN101C485	MN101C487
ROM (×8-bit) External memory can be expanded			8 K	16 K
RAM (×8-bit) External memory can be expanded			0.5 K	0.5 K
Package			LQFP064-P-1414 *Pb free, TQFP064-P-1010B *Pb free	
Minimum Instruction Execution Time			0.10 μs (at 4.5 V to 5.5 V, 20 MHz) 0.25 μs (at 2.7 V to 5.5 V, 8 MHz) 125 μs (at 2.0 V to 5.5 V, 32 kHz)	
Interrupts			• RESET • Watchdog • External 0 • External 1 • External 2 • External 4 • Timer 2 • Timer 3 • Timer 4 • Timer 5 • Time base • Serial 0 • A/D conversion finish	
Timer Counter			<p>Timer counter 2 : 8-bit × 1 (square-wave/8-bit PWM output, event count, synchronous output event) Clock source 1/1, 1/4 of system clock frequency; 1/1 of XI oscillation clock frequency; external clock input Interrupt source coincidence with compare register 2</p> <p>Timer counter 3 : 8-bit × 1 (square-wave output, event count, generation of remote control carrier, serial 0 baud rate timer) Clock source 1/4, 1/16 of system clock frequency; 1/1 of OSC oscillation clock frequency; external clock input Interrupt source coincidence with compare register 3</p> <p>Timer counter 2, 3 can be cascade-connected.</p> <p>Timer counter 4 : 16-bit × 1 (square-wave/16-bit PWM output, event count, synchronous output event, input capture) Clock source 1/4, 1/16 of system clock frequency; 1/1 of OSC oscillation clock frequency; external clock input Interrupt source coincidence with compare register 4</p> <p>Time base timer (one-minute count setting, independently operable 8-bit timer counter 5) Clock source 1/4 of system clock frequency; 1/1, 1/8192 of OSC oscillation clock frequency; 1/1, 1/8192 of XI oscillation clock frequency Interrupt source coincidence with compare register 5; 1/8192 prescaler overflow</p> <p>Watchdog timer Interrupt source 1/65536, 1/262144, 1/1048576 of system clock frequency (ROM option)</p>	
Serial Interface			Serial 0 : synchronous type/simple UART (half-duplex) × 1 Clock source 1/2, 1/4, 1/16 of system clock frequency; 1/2 of timer counter 3 frequency	
I/O Pins	I/O	36	• Common use • Specified pull-up resistor available • Input/output selectable (bit unit) • Specified pull-down resistor partially selectable	
	Input	11	• Common use • Specified pull-up resistor available • Specified pull-down resistor partially selectable	
A/D Inputs			10-bit × 8-ch. (with S/H)	
LCD			• 25 segments • 4 commons • Static • 1/2, 1/3, or 1/4 duty	
Special Ports			Buzzer output, remote control carrier signal output, high-current drive port	

Electrical Characteristics

Supply current

Parameter	Symbol	Condition	Limit			Unit
			min	typ	max	
Operating supply current	IDD1	fosc = 8 MHz, VDD = 5 V		10	25	mA
	IDD2	fx = 32 kHz, VDD = 3 V		15	100	μA
Supply current at HALT	IDD3	fx = 32 kHz, VDD = 3 V, Ta = 25°C		4	8	μA
	IDD4	fx = 32 kHz, VDD = 3 V, Ta = -40°C to +85°C			30	μA
Supply current at STOP	IDD5	VDD = 5 V, Ta = 25°C			1	μA
		VDD = 5 V, Ta = -40°C to +85°C			25	μA

Pin Assignment



LQFP064-P-1414 *Pb free

TQFP064-P-1010B *Pb free

Support Tool

In-circuit Emulator

PX-ICE101C / D + PX-PRB101C09-TQFP064-P-1010B
 PX-ICE101C / D + PX-PRB101C09-LQFP064-P-1414

EPROM Built-in Type

Type MN101CP487

ROM (× 8-bit) 16 K

RAM (× 8-bit) 0.5 K

Minimum instruction execution time 0.10 μs (at 4.5 V to 5.5 V, 20 MHz)

0.25 μs (at 2.7 V to 5.5 V, 8 MHz)

125 μs (at 2.3 V to 5.5 V, 32 KHz)

Package LQFP064-P-1414 *Pb free, TQFP064-P-1010B *Pb free

Request for your special attention and precautions in using the technical information and semiconductors described in this material

- (1) An export permit needs to be obtained from the competent authorities of the Japanese Government if any of the products or technologies described in this material and controlled under the "Foreign Exchange and Foreign Trade Law" is to be exported or taken out of Japan.
- (2) The technical information described in this material is limited to showing representative characteristics and applied circuit examples of the products. It does not constitute the warranting of industrial property, the granting of relative rights, or the granting of any license.
- (3) The products described in this material are intended to be used for standard applications or general electronic equipment (such as office equipment, communications equipment, measuring instruments and household appliances).
Consult our sales staff in advance for information on the following applications:
 - Special applications (such as for airplanes, aerospace, automobiles, traffic control equipment, combustion equipment, life support systems and safety devices) in which exceptional quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or harm the human body.
 - Any applications other than the standard applications intended.
- (4) The products and product specifications described in this material are subject to change without notice for reasons of modification and/or improvement. At the final stage of your design, purchasing, or use of the products, therefore, ask for the most up-to-date Product Standards in advance to make sure that the latest specifications satisfy your requirements.
- (5) When designing your equipment, comply with the guaranteed values, in particular those of maximum rating, the range of operating power supply voltage and heat radiation characteristics. Otherwise, we will not be liable for any defect which may arise later in your equipment.
Even when the products are used within the guaranteed values, redundant design is recommended, so that such equipment may not violate relevant laws or regulations because of the function of our products.
- (6) When using products for which dry packing is required, observe the conditions (including shelf life and after-unpacking standby time) agreed upon when specification sheets are individually exchanged.
- (7) No part of this material may be reprinted or reproduced by any means without written permission from our company.

Please read the following notes before using the datasheets

- A. These materials are intended as a reference to assist customers with the selection of Panasonic semiconductor products best suited to their applications.
Due to modification or other reasons, any information contained in this material, such as available product types, technical data, and so on, is subject to change without notice.
Customers are advised to contact our semiconductor sales office and obtain the latest information before starting precise technical research and/or purchasing activities.
- B. Panasonic is endeavoring to continually improve the quality and reliability of these materials but there is always the possibility that further rectifications will be required in the future. Therefore, Panasonic will not assume any liability for any damages arising from any errors etc. that may appear in this material.
- C. These materials are solely intended for a customer's individual use.
Therefore, without the prior written approval of Panasonic, any other use such as reproducing, selling, or distributing this material to a third party, via the Internet or in any other way, is prohibited.