




- 1 HOUSING MATERIAL: GLASS-FILLED POLYMER.
- 2 CONTACT MATERIAL: COPPER ALLOY.
- 3 RECOMMENDED HOLE SIZE FOR MANUAL APPLICATION OF CONNECTOR ONTO PC BOARD.
- 4 PART NUMBER, DATE CODE IDENTIFICATION, CSA LOGO THIS APPROXIMATE AREA.
- 5 CONTACT POINT.
- 6 MARKING ON THIS SIDE.
- 7 CONTACT FINISH: CONFIRMS TO PERFORMANCE REQUIREMENT OF DIN 41612 CLASS 2 IN CONTACT AREA, 0.00127[.000050] NICKEL UNDERPLATE ALL OVER, TIN PLATE ON POSTS.

SUPERSEDED BY 5650895-5	$\triangle 1$	1 THRU 32	X	X	X	96	7-5650895-5
SUPERSEDED BY 5650895-4	$\triangle 2$	1 THRU 32	X	X	X	96	7-5650895-4
	$\triangle 3$	1 THRU 32	X	X	X	96	5650895-5
	$\triangle 4$	1 THRU 32	X	X	X	96	5650895-4
FINISH	POSITIONS LOADED	C	B	A	NO. OF LOADED POSITION	ASSY PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. POLIGNONE 03JUN05	TE Connectivity				
DIMENSIONS: mm [INCHES]		CHK A. SHARPE 03JUN05	NAME ASSEMBLY, RECEPTACLE, EUROCARD, TYPE R				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. SHARPE 03JUN05	96 POS, 2.79 SOLDER POSTS WITH BOARD LOCKS				
0 PLC $\pm$ -		PRODUCT SPEC	SIZE				
1 PLC $\pm$ -		APPLICATION SPEC	CAGE CODE				
2 PLC $\pm$ 0.13 [0.005]		WEIGHT 0.000000	DRAWING NO				
3 PLC $\pm$ -		00779	REV				
4 PLC $\pm$ -		5650895	SHEET 1 OF 1				
ANGLES $\pm$ -		CUSTOMER DRAWING	SCALE 4:1				
MATERIAL		SEE TABLE	REV B				