


3M™ TWIN AXIAL CABLE, SL8800 SERIES



		HORIZONTAL FLAME VERSION	VW1 VERSION
SIGNAL WIRE PLATING	SILVER	SL8801/12-10DA5-00	SL8801/12-1FDG5-00
	TIN	SL8801/12-11DA5-00	SL8801/12-1GDG5-00
PRODUCT SPEC.		PS-0105	PS-0163
IMPEDANCE SPEC.		100 ±5 OHMS	95 ±5 OHMS

DESIGN REFERENCE		NEXT ASSEMBLY		REV.	ISSUE DATE AND DESCRIPTION		
DRAFT	MWL	DATE	ECO		DATE	MFG	DATE
				CHKD	RE	APPVL	DATE
DIVISION		DIVISION CODE		 3M Center St. Paul, MN 55144 © 3M COPYRIGHT 2013 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.			
DO NOT SCALE DRAWING	SCALE <u>15</u> 1	TOLERANCES EXCEPT AS NOTED	 INCHES .0 ± .00 .000 ± .0000 ±				
THIRD ANGLE PROJECTION		 INTERPRET PER ASME Y14.5 - 1994		MILLIMETERS	0 ± .0 ± .00 ± .10 .000 ±		REV.
MAX SURFACE ROUGHNESS		125 ✓ ALL SURFACES MARKED ONLY		CAGE NUMBER	SIZE	DRAWING NO.	
				C	78-5100-2412-4		D
				MODEL	DET.	LISTS	YES X NO
					SHT	1	OF 1