


REV.	DATE	DESCRIPTION
B	01/12/98	ADD INSULATOR/ STRIPPING DIM'S
C	02/11/99	MODIFY 'O'-RING DIMENSIONS
D	05/22/03	UPDATE DRAWING FORMAT



REV.	DATE	DESCRIPTION
B	01/12/98	ADD INSULATOR/ STRIPPING DIM'S
C	02/11/99	MODIFY 'O'-RING DIMENSIONS
D	05/22/03	UPDATE DRAWING FORMAT
8		
7		
6	FERRULE	BRASS
5	LOCK WASHER	BRASS
4	GASKET	SILICONE
3	CONTACT PIN	BER. COPPER
2	INSULATOR	TEFLON
1	BODY	BRASS
	DESCRIPTION	MATERIAL
		FINISH
		QTY
		DO NOT SCALE DRAWING
		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.
		UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
		0.5 - 8mm ± 0.20mm
		8 - 30mm ± 0.40mm
		30 - 120mm ± 0.50mm
		UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
		.020 - .315 = ± 0.007"
		.315 - 1.180 = ± 0.015"
		1.180 - 4.724 = ± 0.020"
	APPROVALS	DATE
	DRAWN G.R.S.	05/22/03
	CHECKED	
	ISSUED	
	SHEET 1 OF 1	
	CAD FILE	C:/132/132106.DWG
	PART DESCRIPTION	SMA DIRECT SOLDER BULKHEAD JACK (FOR .141" SEMI-RIGID CABLE)
	PART NO.	132106
	DWG. NO.	132106.DWG
	REV.	D
	SIZE	A
	SCALE	NA

Amphenol Connex