




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



SPECIFICATIONS

TUSONIX STYLE:		801-040
D (Diameter):		.350 ±.035 [8.89 ±0.89]
T (Thickness):		.120 ±.040 [3.05 ±1.02]
S (Lead Wire Spacing):		.250 ±.060 [6.35 ± 1.52]
L (Lead Wire Length):		1.250 [31.75] MIN.
E (Lead Wire Diameter):		.025 +.004-.001 [0.64 +0.10-0.03] (# 22 AWG.)
P (Coating on Leads Max.):		.125 [3.18]
Capacitance Value:		2200 pF
Capacitance Tolerance:		± 20%
Temperature Coefficient:		X5U (AW)
Voltage:	Working:	500 VDC
	Test:	1250 VDC
	Life:	1000 VDC

NOTE:
QUALIFIED TO MIL-C-11015/10,
STYLE CK61AW222M.

Marking: TMK, MIL PART NO., DATE CODE

REVISION RECORD Original Release C.O. 20031007-3-01	0	--TOLERANCES-- Unless Otherwise Specified		Title DISC CAPACITOR	
		DECIMAL ±		Drawn S.M. 10-07-03	
		ANGLES ±		Approved B.Mc. 10-07-03	
		TUSONIX TUCSON, ARIZONA		A	801-040-X5U0-222M