

ISSUE 1
4/29/92 YN

ISSUE 2
REFORMATTED
TEMECULA
WAS CARSON
9/13/95 DS

1. Electrical specifications

- 1.1 Input voltage: AC 120V ±10% 60 Hz ±0.5 Hz
1.2 Output voltage and current: AC 24V at 830mA

Vin	830mA Load	83mA Load
108	19.1 VAC MIN	—
120	22.0–25.0 VAC	27.1 VAC MAX
132	—	30.4 VAC MAX


NOTE: Specification applies after 10 minutes warm-up with 830mA load and at any operating temperature

- 1.3 Operating temperature: 0 ° C to +40 ° C
1.4 Storage temperature: -20 ° C to +85 ° C
1.5 Operating and Storage Humidity: 0 to 95% without condensation
1.6 Withstand voltage: AC 1500Vrms 1 minute @ input to output
1.7 Input earth prong is connected to output "G" terminal



2. Typical performance data test condition: Ta = +25° C, measured after 10 minute warm-up with input at 120V 60Hz

3. Safety agencies
UL File No. E82180
CSA File No. LR38236

4. Nameplate: See drawing P-N1-11161 for detail



5. Mechanical Specifications;
All dimensions shown are nominal unless otherwise specified



PREPARED BY:

K. Brennan

ENGINEER:

D. Suzuki

QUALITY CONTROL:

V. Casey

APPROVED:

O. Vulf

DWG CONTROL NO.
P-A7-10679
ACAD\PS\A7106791.DWG

REV
A

UL/CSA AC 24V 830mA
POWER SUPPLY

TAMURA CORPORATION OF AMERICA
43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624
(909) 699-1270 FAX 9096769482

830A0067-03

MODEL SPECIFICATION

DIM: mm(In) SCL: NONE SH: 1 OF 1

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.