



REV. Status	TCA NO.	MODEL NO.	RATED CURRENT (ADC)	INDUCTANCE (uH)±20%	DCR (ohm MAX)
ISSUE 1 11/20/95 TS	P-A4-11401-01	SKC-109	5	1200	0.081
	P-A4-11401-02	SKC-110	5	1800	0.099

SKC-109 & 110


Schematic Diagram;



Country of origin



Mechanical Specifications;



TOLERANCES (mm)

$\leq 4 \pm 0.2$
 $4 \leq 20 \pm 0.3$
 $20 \leq 50 \pm 0.4$

PREPARED BY:

K. Brennan

NOTE: Inductance is measured at 1 KHz, 1 Vrms with specified DC current

ENGINEER: T. Shiozawa	DWG CONTROL NO. P-A4-11466 ACAD\MISCX\A4114661.DWG	REV —	POWER INDUCTOR FOR SWITCH MODE POWER SUPPLIES	SKC-109 & 110
QUALITY CONTROL: V. Casey	CONTENTS OF THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTICE	TAMURA CORPORATION OF AMERICA 43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624 (909) 699-1270 FAX 9096769482	MODEL SPECIFICATION	DIM: mm(in) SCL: NONE SH: 1 OF 1
APPROVED: V. Casey	PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.			