

# MAXIM

## Quad, SPST Analog Switches

### General Description


The DG308A/DG309 are quad, single-pole-single-throw (SPST) analog switches. The DG308A is normally open (SPST, NO), while the DG309 is normally closed (SPST, NC). Both parts feature fast switching speeds and low on-resistance over the analog range. Other features include a turn-on time under 120ns, a turn-off time under 90ns, and a channel on-resistance of 60Ω. CMOS inputs provide reduced input loading and very low leakage currents.

Both parts feature a 44V maximum breakdown voltage rating that allows 30V peak-to-peak switch-off blocking capacity. The DG308A/DG309 can be used with split supplies ( $\pm 5V$  to  $\pm 20V$ ) or a single positive supply (+5V to +30V), while retaining CMOS-logic-compatible inputs.

### Applications

Sample-and-Hold Circuits  
Test Equipment  
Communications Systems  
PBX, PABX  
Guidance and Control Systems  
Heads-Up Displays  
Military Radios

### Typical Operating Circuit



### Features

- ♦ 60Ω  $r_{DS(ON)}$
- ♦ Single/Bipolar-Supply Operation
- ♦ CMOS Logic Compatible
- ♦ Monolithic, Low-Power CMOS Design

### Ordering Information


| PART      | TEMP. RANGE     | PIN-PACKAGE    |
|-----------|-----------------|----------------|
| DG308ACJ  | 0°C to +70°C    | 16 Plastic DIP |
| DG308ACY  | 0°C to +70°C    | 16 Narrow SO   |
| DG308ACK  | 0°C to +70°C    | 16 Cerdip      |
| DG308AC/D | 0°C to +70°C    | Dice*          |
| DG308ADJ  | -40°C to +85°C  | 16 Plastic DIP |
| DG308ADY  | -40°C to +85°C  | 16 Narrow SO   |
| DG308ADK  | -40°C to +85°C  | 16 Cerdip      |
| DG308AAK  | -55°C to +125°C | 16 Cerdip**    |
| DG309CJ   | 0°C to +70°C    | 16 Plastic DIP |
| DG309CY   | 0°C to +70°C    | 16 Narrow SO   |
| DG309CK   | 0°C to +70°C    | 16 Cerdip      |
| DG309C/D  | 0°C to +70°C    | Dice*          |
| DG309DJ   | -40°C to +85°C  | 16 Plastic DIP |
| DG309DY   | -40°C to +85°C  | 16 Narrow SO   |
| DG309DK   | -40°C to +85°C  | 16 Cerdip      |
| DG309AK   | -55°C to +125°C | 16 Cerdip**    |

\* Contact factory for dice specifications.

\*\* Contact factory for availability and processing to MIL-STD-883.

### Pin Configuration/Truth Table

TOP VIEW



DIP/SO

TRUTH TABLE

| LOGIC | DG308A | DG309 |
|-------|--------|-------|
| 0     | OFF    | ON    |
| 1     | ON     | OFF   |

MAXIM

Maxim Integrated Products 1

For free samples & the latest literature: <http://www.maxim-ic.com>, or phone 1-800-998-8800

DG308A/DG309

# Quad, SPST Analog Switches

## ABSOLUTE MAXIMUM RATINGS

Voltage Referenced to V-

V+ .....+44V

GND .....+25V

Digital Inputs V<sub>S</sub>, V<sub>D</sub>.....(V- - 2V) to (V+ + 2V) or 20mA,  
whichever occurs first

Current into Any Terminal (except S or D).....30mA

Continuous Current (S or D).....20mA

Peak Current (S or D)  
(pulsed at 1ms, 10% duty cycle max) .....70mA

Continuous Power Dissipation (T<sub>A</sub> = +70°C) (Note 1)

Plastic DIP (derate 10.53mW/°C above +70°C) .....842mW

Narrow SO (derate 8.70mW/°C above +70°C) .....696mW

CERDIP (derate 10.00mW/°C above +70°C) .....800mW

Operating Temperature Ranges

DG308AC\_/DG309C\_ .....0°C to +70°C

DG308AD\_/DG309D\_ .....-40°C to +85°C

DG308AAK/DG309AK .....-55°C to +125°C

Storage Temperature Range .....-65°C to +150°C

Lead Temperature (soldering, 10sec) .....+300°C

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

## ELECTRICAL CHARACTERISTICS

(V+ = 15V, V- = -15V, T<sub>A</sub> = T<sub>MIN</sub> to T<sub>MAX</sub>, unless otherwise noted.) (Note 2)

| PARAMETER                                | SYMBOL              | CONDITIONS                                                                                                                  |                                             | DG30_AK<br>MIN   TYP   MAX |        |     | DG30_C/D<br>MIN   TYP   MAX |       |     | UNITS |
|------------------------------------------|---------------------|-----------------------------------------------------------------------------------------------------------------------------|---------------------------------------------|----------------------------|--------|-----|-----------------------------|-------|-----|-------|
| SWITCH                                   |                     |                                                                                                                             |                                             |                            |        |     |                             |       |     |       |
| Analog Signal Range                      | V <sub>ANALOG</sub> |                                                                                                                             | T <sub>A</sub> = +25°C                      | -15                        |        | 15  | -15                         |       | 15  | V     |
| Drain-Source<br>On-Resistance            | r <sub>DS(ON)</sub> | V <sub>IN</sub> = 11V (DG308A),<br>V <sub>IN</sub> = 3.5V (DG309),<br>I <sub>S</sub> = 1mA,<br>V <sub>D</sub> = 10V or -10V | T <sub>A</sub> = +25°C,<br>T <sub>MIN</sub> | 60                         |        | 100 | 60                          |       | 100 | Ω     |
|                                          |                     |                                                                                                                             | T <sub>A</sub> = T <sub>MAX</sub>           | 95                         |        | 150 | 80                          |       | 125 |       |
| Source-Off<br>Leakage Current            | I <sub>S(OFF)</sub> | V <sub>IN</sub> = 3.5V (DG308A),<br>V <sub>IN</sub> = 11V (DG309),<br>V <sub>S</sub> = 14V, V <sub>D</sub> = -14V           | T <sub>A</sub> = +25°C                      | -1                         | 0.1    | 1   | -5                          | 0.1   | 5   | nA    |
|                                          |                     |                                                                                                                             | T <sub>A</sub> = T <sub>MAX</sub>           | -100                       |        | 100 | -100                        |       | 100 |       |
|                                          |                     | V <sub>IN</sub> = 3.5V (DG308A),<br>V <sub>IN</sub> = 11V (DG309),<br>V <sub>S</sub> = -14V, V <sub>D</sub> = 14V           | T <sub>A</sub> = +25°C                      | -1                         | -0.1   | 1   | -5                          | 0.1   | 5   |       |
|                                          |                     |                                                                                                                             | T <sub>A</sub> = T <sub>MAX</sub>           | -100                       |        | 100 | -100                        |       | 100 |       |
| Drain-Off<br>Leakage Current             | I <sub>D(OFF)</sub> | V <sub>IN</sub> = 3.5V (DG308A),<br>V <sub>IN</sub> = 11V (DG309),<br>V <sub>S</sub> = 14V, V <sub>D</sub> = -14V           | T <sub>A</sub> = +25°C                      | -1                         | 0.1    | 1   | -5                          | 0.1   | 5   | nA    |
|                                          |                     |                                                                                                                             | T <sub>A</sub> = T <sub>MAX</sub>           | -100                       |        | 100 | -100                        |       | 100 |       |
|                                          |                     | V <sub>IN</sub> = 3.5V (DG308A),<br>V <sub>IN</sub> = 11V (DG309),<br>V <sub>S</sub> = -14V, V <sub>D</sub> = 14V           | T <sub>A</sub> = +25°C                      | -1                         | 0.1    | 1   | -5                          | 0.1   | 5   |       |
|                                          |                     |                                                                                                                             | T <sub>A</sub> = T <sub>MAX</sub>           | -100                       |        | 100 | -100                        |       | 100 |       |
| Drain-On<br>Leakage Current              | I <sub>D(ON)</sub>  | V <sub>IN</sub> =11V (DG308A),<br>V <sub>IN</sub> = 3.5V (DG309),<br>V <sub>S</sub> = V <sub>D</sub> = +14V                 | T <sub>A</sub> = +25°C                      | -2                         | 0.1    | 2   | -5                          | 0.1   | 5   | nA    |
|                                          |                     |                                                                                                                             | T <sub>A</sub> = T <sub>MAX</sub>           | -200                       |        | 200 | -200                        |       | 200 |       |
|                                          |                     | V <sub>IN</sub> = 11V (DG308A),<br>V <sub>IN</sub> = 3.5V (DG309),<br>V <sub>S</sub> = V <sub>D</sub> = -14V                | T <sub>A</sub> = +25°C                      | -2                         | 0.1    | 2   | -5                          | 0.1   | 5   |       |
|                                          |                     |                                                                                                                             | T <sub>A</sub> = T <sub>MAX</sub>           | -200                       |        | 200 | -200                        |       | 200 |       |
| INPUT                                    |                     |                                                                                                                             |                                             |                            |        |     |                             |       |     |       |
| Input Current with<br>Input Voltage High | I <sub>INH</sub>    | V <sub>IN</sub> = 15V                                                                                                       | T <sub>A</sub> = +25°C,<br>T <sub>MAX</sub> | -1                         | 0.001  | 1   | -1                          | 0.001 | 1   | μA    |
| Input Current with<br>Input Voltage Low  | I <sub>INL</sub>    | V <sub>IN</sub> = 0V                                                                                                        | T <sub>A</sub> = +25°C,<br>T <sub>MAX</sub> | -1                         | -0.001 | 1   | -1                          | 0.001 | 1   | μA    |

# Quad, SPST Analog Switches

DG308A/DG309

## ELECTRICAL CHARACTERISTICS (continued)

(V+ = 15V, V- = -15V, T<sub>A</sub> = T<sub>MIN</sub> to T<sub>MAX</sub>, unless otherwise noted.) (Note 2)

| PARAMETER               | SYMBOL                                  | CONDITIONS                                                                                                                          |                                   | DG30_AK |        |    | DG30_C/D |        |     | UNITS |     |     |     |     |  |
|-------------------------|-----------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|---------|--------|----|----------|--------|-----|-------|-----|-----|-----|-----|--|
| MIN                     |                                         |                                                                                                                                     |                                   |         |        |    |          |        |     | TYP   | MAX | MIN | TYP | MAX |  |
| SUPPLY                  |                                         |                                                                                                                                     |                                   |         |        |    |          |        |     |       |     |     |     |     |  |
| Positive Supply Current | I+                                      | All channels on or off, V <sub>IN</sub> = 0V or 15V                                                                                 | T <sub>A</sub> = +25°C            | -10     | 0.001  | 10 | -100     | 0.001  | 100 | μA    |     |     |     |     |  |
|                         |                                         |                                                                                                                                     | T <sub>A</sub> = T <sub>MAX</sub> | 100     |        |    | 100      |        |     |       |     |     |     |     |  |
| Negative Supply Current | I-                                      | All channels on or off, V <sub>IN</sub> = 0V or 15V                                                                                 | T <sub>A</sub> = +25°C            | -10     | -0.001 | 10 | -100     | -0.001 | 100 | μA    |     |     |     |     |  |
|                         |                                         |                                                                                                                                     | T <sub>A</sub> = T <sub>MAX</sub> | -100    |        |    | -100     |        |     |       |     |     |     |     |  |
| DYNAMIC                 |                                         |                                                                                                                                     |                                   |         |        |    |          |        |     |       |     |     |     |     |  |
| Turn-On Time            | t <sub>ON</sub>                         | Figure 1                                                                                                                            |                                   | 130     | 200    |    | 130      | 200    |     | ns    |     |     |     |     |  |
| Turn-Off Time           | t <sub>OFF</sub>                        | Figure 1                                                                                                                            |                                   | 90      | 150    |    | 90       | 150    |     | ns    |     |     |     |     |  |
| Charge Injection        | Q                                       | C <sub>L</sub> = 0.01μF, V <sub>GEN</sub> = 0V, R <sub>GEN</sub> = 0Ω                                                               |                                   | -10     |        |    | -10      |        |     | pC    |     |     |     |     |  |
| Off Isolation (Note 3)  | OIRR                                    | V <sub>IN</sub> = 0V (DG308A), V <sub>IN</sub> = 15V (DG309), Z <sub>L</sub> = 75Ω, V <sub>S</sub> = 2V <sub>p-p</sub> , f = 500kHz |                                   | 78      |        |    | 78       |        |     | dB    |     |     |     |     |  |
| Source-Off Capacitance  | C <sub>S(OFF)</sub>                     | V <sub>IN</sub> = 0V (DG308A), V <sub>IN</sub> = 15V (DG309), f = 140kHz, V <sub>S</sub> = 0V                                       |                                   | 11      |        |    | 11       |        |     | pF    |     |     |     |     |  |
| Drain-Off Capacitance   | C <sub>D(OFF)</sub>                     | V <sub>IN</sub> = 0V (DG308A), V <sub>IN</sub> = 15V (DG309), f = 140kHz, V <sub>S</sub> = 0V                                       |                                   | 8       |        |    | 8        |        |     | pF    |     |     |     |     |  |
| Channel-On Capacitance  | C <sub>D(ON)</sub> + C <sub>S(ON)</sub> | V <sub>IN</sub> = 0V (DG308A), V <sub>IN</sub> = 15V (DG309), V <sub>D</sub> = V <sub>S</sub> = 0V                                  |                                   | 27      |        |    | 27       |        |     | pF    |     |     |     |     |  |

**Note 1:** All leads are soldered or welded to the PC board.

**Note 2:** The algebraic convention where the most negative value is a minimum and the most positive value a maximum is used in this data sheet.

**Note 3:** Off isolation = 20log<sub>10</sub> V<sub>D</sub>/V<sub>S</sub>, V<sub>D</sub> = output, V<sub>S</sub> = input to off switch.








Figure 1. Switching-Time Test Circuit

# Quad, SPST Analog Switches

## Typical Operating Characteristics

( $T_A = +25^\circ\text{C}$ , unless otherwise noted.)



## Pin Description

| PIN          | NAME    | FUNCTION                                               |
|--------------|---------|--------------------------------------------------------|
| 1, 8, 9, 16  | IN1-IN4 | Logic Control Inputs                                   |
| 2, 7, 10, 15 | D1-D4   | Drain Output                                           |
| 3, 6, 11, 14 | S1-S4   | Source Input                                           |
| 4            | V-      | Negative Supply Voltage Input                          |
| 5            | GND     | Ground                                                 |
| 12           | N.C.    | No Connect. Not internally connected.                  |
| 13           | V+      | Positive Supply Voltage Input. Connected to substrate. |

## Applications Information

The DG308A/DG309 switch positive analog signals while using a single positive supply, allowing use in applications where only one supply is available. The disadvantages of using a single supply are slower switching speed and increased  $r_{DS(ON)}$ . The *Power-Supply Current and Voltage vs. Temperature* graph shows the typical curve for a single-supply design. As stated in the Absolute Maximum Ratings, the analog voltage should not go above or below the supply voltages, which are  $V_+$  and 0V in single-supply operation.

Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

4 Maxim Integrated Products, 120 San Gabriel Drive, Sunnyvale, CA 94086 (408) 737-7600

© 1991 Maxim Integrated Products

Printed USA

**MAXIM** is a registered trademark of Maxim Integrated Products.