







1. CABLE USED WITHOUT SPACER
2. CABLE USED WITH SPACER
3. SEE INSTRUCTION SHEET 408-2798
4. PARTS PACKAGED UNASSEMBLED
5. USE WITH HAND TOOL FRAME 354940-1
6. USE WITH HANDTOOL 69710-1, OR
PNEUMATIC TOOL 69365 & 69365-3
7. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

RECOMMENDED STRIP LENGTH

SUPERSEDED BY 8-227079-2	OBSELETE	H.P. RED TRIAXIAL	—	58330-1	69477-4	C	1.090	1-938013-3	—	—	9-329461-0	9-227322-0	413530-6	4-227079-0
	OBSELETE	RG-180/U,180A/U,180B/U & 195/U	—	58330-1	69477-4	A	1.090	—	—	—	9-329461-0	9-221607-4	413530-5	3-227079-7
	OBSELETE	RG-188/U DOUBLE BRAIDED	—	58330-1	69477-4	A	1.090	—	227194-1	—	9-329049-0	9-227322-0	413530-6	3-227079-3
	OBSELETE	BELDEN 9248	—	220244-1	220247-1	A	1.090	—	—	—	9-50427-0	1-221607-7	413530-3	3-227079-2
	OBSELETE	BELDEN 9248	—	220244-1	220247-1	A	1.090	—	—	—	9-50427-0	1-221607-8	413530-3	3-227079-1
SUPERSEDED BY 2-227079-2	OBSELETE	BELDEN 9248 & 9114	—	220244-1	220247-1	A	1.090	—	—	—	9-50427-0	1-221607-6	413530-3	3-227079-0
	OBSELETE	RG-179/U & 187/U	220217-3	220210-1	220009-5	A	1.090	—	227194-1	—	9-328666-0	227322-4	227074-2	2-227079-2
SUPERSEDED BY 2-227079-0	OBSELETE	RG-179/U & 187/U	220217-3	220210-1	220009-5	A	1.090	—	227194-1	—	9-328666-0	227322-3	413530-6	2-227079-1
	OBSELETE	BELDEN 8218,AMPHENOL 21-597 & BELDEN NH SPECIAL	—	58330-1	69477-4	A	1.090	—	227194-1	—	9-328666-0	9-227322-1	413530-6	2-227079-0
SUPERSEDED BY 1-227079-9	OBSELETE	BELDEN 8218,AMPHENOL 21-597 & BELDEN NH SPECIAL	—	58330-1	69477-4	A	1.090	—	—	—	9-329461-0	2-221607-2	413530-5	1-227079-9
	OBSELETE	BELDEN 8218,AMPHENOL 21-597 & BELDEN NH SPECIAL	—	58330-1	69477-4	A	1.090	—	—	—	9-329461-0	2-221607-1	413530-5	1-227079-8
SUPERSEDED BY 1-227079-6	OBSELETE	RG-174/U & 188/U	220217-3	220210-1	220009-5	A	1.090	—	227194-1	—	9-328666-0	227322-8	227074-2	1-227079-6
	OBSELETE	RG-174/U & 188/U	220217-3	220210-1	220009-5	A	1.090	—	227194-1	—	9-328666-0	227322-7	413530-6	1-227079-5
	OBSELETE	RG-174/U & 188/U	220217-3	220210-1	220009-5	A	1.090	—	227194-1	—	9-328666-0	9-227322-0	413530-6	1-227079-4
	OBSELETE	BELDEN 9266	—	220189-5	—	A	1.090	—	—	—	9-50428-0	221607-5	413530-2	1-227079-3
	OBSELETE	RG-71/U & 71A/U	220217-2	220189-2	220187-2	B	1.090	—	—	227423-1	1-329460-1	221607-8	413530-2	1-227079-2
SUPERSEDED BY 227079-6	OBSELETE	RG-59/U,59A/U & 59B/U	220217-2	220189-2	220187-2	A	1.090	—	—	227423-1	9-50428-0	221607-8	413530-2	1-227079-1
	OBSELETE	RG-62/U,62A/U & 62B/U	220217-2	220189-2	220187-2	B	1.090	—	—	227423-1	9-50428-0	221607-8	413530-2	1-227079-1
	OBSELETE	RG-55/U,55A/U,55B/U, & 223/U	220217-1	220189-1	220187-1	A	1.280	—	—	—	9-225382-0	221607-7	227074-1	1-227079-0
	OBSELETE	RG-58/U,58A/U,58B/U,58C/U & 141/U	220217-1	220189-1	220187-1	A	1.090	—	—	—	9-50427-1	221607-7	227074-1	227079-9
	OBSELETE	RG-59/U,59A/U & 59B/U	220217-2	220189-2	220187-2	A	1.090	—	—	227423-1	9-50428-0	221607-6	227080-1	227079-7
	OBSELETE	RG-62/U,62A/U & 62B/U	220217-2	220189-2	220187-2	B	1.090	—	—	227423-1	9-50428-0	221607-6	227080-1	227079-7
	OBSELETE	RG-55/U,55A/U,55B/U, & 223/U	220217-1	220189-1	220187-1	A	1.280	—	—	—	9-225382-0	221607-5	227074-1	227079-6
	OBSELETE	RG-58/U,58A/U,58B/U,58C/U & 141/U	220217-1	220189-1	220187-1	A	1.090	—	—	—	9-50427-1	221607-5	227074-1	227079-5
	OBSELETE	RG-71/U & 71A/U	220217-2	220189-2	220187-2	B	1.090	—	—	227423-1	1-329460-1	9-221607-1	413530-2	227079-4
	OBSELETE	RG-59/U,59A/U & 59B/U	220217-2	220189-2	220187-2	A	1.090	—	—	227423-1	9-50428-0	9-221607-1	413530-2	227079-3
SUPERSEDED BY 227079-6	OBSELETE	RG-62/U,62A/U & 62B/U	220217-2	220189-2	220187-2	B	1.090	—	—	227423-1	9-50428-0	9-221607-1	413530-2	227079-3
	OBSELETE	RG-55/U,55A/U,55B/U, & 223/U	220217-1	220189-1	220187-1	A	1.280	—	—	—	9-225382-0	9-221607-0	227074-1	227079-2
OBSELETE	RG-58/U,58A/U,58B/U,58C/U & 141/U	220217-1	220189-1	220187-1	A	1.090	—	—	—	—	9-50427-1	9-221607-0	227074-1	227079-1
		CABLE SIZE	DIE SET 	DIE SET 	CRIMP TOOL	VIEW	A	 TUBING,HEAT SHRINK QTY=1	 TUBING QTY=1	 SPACER QTY=1	 FERRULE QTY=1	 CONTACT, PLUG QTY=1	 PLUG ASSY, COML BNC QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN CLAMAN 10-9-89		 TE Connectivity						
				CHK R.E.RUTH 10/27/89								
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:				APP'D J. GIBBS 11/06/89		NAME				
		PRODUCT SPEC				PLUG, COMMERCIAL, BNC						
		108-12044										
		APPLICATION SPEC										
		SIZE								CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT										
MATERIAL	-	FINISH	-			A1	00779	C-227079	SCALE 4:1	SHEET 1 OF 2	REV AV3	
CUSTOMER DRAWING												

8		7		6		5		4		3		2		1	
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION											
COPYRIGHT - By -				ALL RIGHTS RESERVED.											