







.050	1.27	-	-
.040	1.02	.800	20.32
.035	0.89	.535	13.59
.032	0.81	.310	7.87
.030	0.76	.295	7.49
.025	0.64	.225	5.72
.020	0.51	.200	5.08
.015	0.38	.150	3.81
.010	0.25	.140	3.56
.008	0.20	.130	3.30
.005	0.13	.125	3.18
.003	0.08	.100	2.54
.001	0.03	.063	1.60
IN	MM	IN	MM

CONVERSION TABLE



- 1
- POST TO WITHSTAND 13 NEWTONS (3LBS.) MIN. AXIAL FORCE IN BOTH DIRECTIONS SHOWN WITHOUT DISLODGING.
- 2
- TOLERANCES APPLY TO SOLDER SIDE OF BOARD.
- 3
- MEASURED AT SURFACE -A-
- 4
- PLASTIC FLASH PERMITTED IN THIS AREA.
5.
- PARTS COMPLY WITH AMP SOLDERABILITY SPEC. NO. 109-11-2.
- 6
- ONE HOLE MAY BE UNDERSIZED (.035/.032 DIA.) FOR ASSEMBLY RETENTION DURING WAVE SOLDERING.
- 7
- MATERIAL: HEADER-THERMOPLASTIC POLYESTER
94V-0(NATURAL)
POST-COPPER ALLOY (TIN PLATED)
- 8
- COORDINATE DIMENSION APPLIES FROM CENTER OF ACTUAL FEATURE.
9.
- PLASTIC BURRS CAUSED BY CUT-OFF TOOLING ARE PERMITTED WITHIN THE MAXIMUM TOLERANCE ENVELOPE.
- 10
- POST TO BE MEASURED WHEN STRIP IS HELD FLAT.
- 11
- POST MUST WITHSTAND TWO 90° BENDS AGAINST EXTRUSION WITHOUT BREAKING.
- 12
- DIMENSION SHOULD BE .130 MIN WHEN MATING WITH A MTA 100 CONNECTOR ASSEMBLY OR WHEN MATING WITH A CST 100 CONNECTOR.
- 13
- PIN BURR OF .005 MAX VERTICAL AND .003 MAX HORIZONTAL PERMITTED AT POST TIPS ON BOTH ENDS.
- 14
- COLOR STRIPE BLACK IN APPROXIMATE LOCATION SHOWN.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± 0° 30'

MATERIAL

7

DWN

B. LEWIS

1-11-95

CHK

R. SWING

1-11-95

APVD

B. GENTRY

1-23-95

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

NAME

MTA-100 HEADER ASSEMBLY, FRICTION LOCK, NOTCHED, .025 SQUARE STRAIGHT POST, TIN PLATED,

SIZE

A1

CAGE CODE

00779

DRAWING NO

644832

RESTRICTED TO

-

SCALE

8:1

SHEET

1

OF

1

REV

C1