

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

4XE1

4XE1

M

DRAWING
NUMBER

2

X

ISSUE

84

REPLACES

RELEASE NO. PR-1047

CHECK

69

DEC 69

3 DEC 69

69

CHECK

69

3 DEC 69

69


CHECK

69

NOV 69



SRH

14



CORROSION RESISTANT TREATED METAL ENCLOSURE

CORROSION RESISTANT STEEL PLUNGER



NOTE-

- 1 MOUNTING HOLES WILL ACCEPT .087 MAX DIA PINS OR SCREWS ON .188 ± .002 CENTERS
- 2 ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- 3 WEIGHT OF SWITCH ONLY IS .16 OZ MAX. WEIGHT OF SWITCH WITH WIRE LEADS IS .5 OZ MAX

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE-----5-17 OZ
RELEASE FORCE-----4 OZ MIN
RELEASE TRAVEL-----.004 MIN
DIFFERENTIAL TRAVEL-----.005 MAX
OVERTRAVEL-----.004 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L7

7A 250 VAC

91

SCALE 2 TO 1

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		

WEIGHT

3