

# MN4538B / MN4538BS

## Dual Precision Monostable Multivibrators

### ■ Description

The MN4538B/S are monostable multivibrators with the capability of reset and re-trigger.

Trigger can be performed from both the positive and negative going edge of the input pulse.

A wide range of precise output pulses can be obtained since the width and precision of the output pulse are defined by external  $C_T$  and  $R_T$ .

Output pulse width control is more precisely performed, due to linear CMOS technology.




Total power supply voltage range is obtained as  $t_{WO} = R_T \cdot C_T$  and no other coefficient is included.

The MN4538B/S are equivalent to MOTOROLA MC14538B.

### ■ Truth Table

Input			Output	
$\bar{I}_0$	$I_1$	$\bar{C}_D$	O	$\bar{O}$
	L	H		
H		H		
x	x	L	L	H

### ■ Logic Diagram (1/2)



**■ Maximum Ratings** (Ta=25°C)

Item	Symbol	Ratings	Unit
Supply Voltage	V <sub>DD</sub>	-0.5~+18	V
Input Voltage	V <sub>I</sub>	-0.5~V <sub>DD</sub> +0.5*	V
Output Voltage	V <sub>O</sub>	-0.5~V <sub>DD</sub> +0.5*	V
Peak Input - Output Current	±I <sub>I</sub>	max. 10	mA
Power Dissipation (per package)	Ta=-40~+60°C	max. 400	mW
	Ta=+60~+85°C	Decrease up to 200mW rating at 8mW/°C	
Power Dissipation (per output terminal)	P <sub>D</sub>	max. 100	mW
Operating Ambient Temperature	T <sub>opr</sub>	-40~+85	°C
Storage Temperature	T <sub>stg</sub>	-65~+150	°C

\* V<sub>DD</sub> + 0.5V should be under 18V


**■ DC Characteristics** (V<sub>SS</sub>=0V)

Item	V <sub>DD</sub> (V)	Sym- bol	Conditions	Ta=-40°C		Ta=25°C		Ta=85°C		Unit
				min.	max.	min.	max.	min.	max.	
Quiescent Power Supply Current	5	I <sub>DD</sub>	V <sub>I</sub> =V <sub>SS</sub> or V <sub>DD</sub>	—	20	—	20	—	150	μA
	10			—	40	—	40	—	300	
	15			—	80	—	80	—	600	
Output Voltage Low Level	5	V <sub>OL</sub>	V <sub>I</sub> =V <sub>SS</sub> or V <sub>DD</sub>  I <sub>OL</sub>   < 1μA	—	0.05	—	0.05	—	0.05	V
	10			—	0.05	—	0.05	—	0.05	
	15			—	0.05	—	0.05	—	0.05	
Output Voltage High Level	5	V <sub>OH</sub>	V <sub>I</sub> =V <sub>SS</sub> or V <sub>DD</sub>  I <sub>OH</sub>   < 1μA	4.95	—	4.95	—	4.95	—	V
	10			9.95	—	9.95	—	9.95	—	
	15			14.95	—	14.95	—	14.95	—	
Input Voltage Low Level	5	V <sub>IL</sub>	I <sub>O</sub>   < 1μA V <sub>O</sub> =0.5V or 4.5V V <sub>O</sub> =1V or 9V V <sub>O</sub> =1.5V or 13.5V	—	1.5	—	1.5	—	1.5	V
	10			—	3	—	3	—	3	
	15			—	4	—	4	—	4	
Input Voltage High Level	5	V <sub>IH</sub>	I <sub>O</sub>   < 1μA V <sub>O</sub> =0.5V or 4.5V V <sub>O</sub> =1V or 9V V <sub>O</sub> =1.5V or 13.5V	3.5	—	3.5	—	3.5	—	V
	10			7	—	7	—	7	—	
	15			11	—	11	—	11	—	
Output Current Low Level	5	I <sub>OL</sub>	V <sub>O</sub> =0.4V, V <sub>I</sub> =0 or 5V V <sub>O</sub> =0.5V, V <sub>I</sub> =0 or 10V V <sub>O</sub> =1.5V, V <sub>I</sub> =0 or 15V	0.52	—	0.44	—	0.36	—	mA
	10			1.3	—	1.1	—	0.9	—	
	15			3.6	—	3	—	2.4	—	
Output Current High Level	5	-I <sub>OH</sub>	V <sub>O</sub> =4.6V, V <sub>I</sub> =0 or 5V V <sub>O</sub> =9.5V, V <sub>I</sub> =0 or 10V V <sub>O</sub> =13.5V, V <sub>I</sub> =0 or 15V	0.52	—	0.44	—	0.36	—	mA
	10			1.3	—	1.1	—	0.9	—	
	15			3.6	—	3	—	2.4	—	
Output Current High Level	5	-I <sub>OH</sub>	V <sub>O</sub> =2.5V, V <sub>I</sub> =0 or 5V	1.7	—	1.4	—	1.1	—	mA
Input Leakage Current	15	±I <sub>I</sub>	V <sub>I</sub> =0 or 15V	—	0.3	—	0.3	—	1	μA


**■ Switching Characteristics** ( $T_a = 25^\circ\text{C}$ ,  $V_{SS} = 0\text{V}$ ,  $C_L = 50\text{pF}$ )

Item	$V_{DD}$ (V)	Symbol	min.	typ.	max.	Unit
Output Rise Time	5	$t_{rLH}$	—	60	180	ns
	10		—	30	90	
	15		—	20	60	
Output Fall Time	5	$t_{rHL}$	—	60	180	ns
	10		—	30	90	
	15		—	20	60	
Propagation Delay Time $\bar{I}_0, I_1 \rightarrow 0$	5	$t_{pHL}$	—	150	450	ns
	10		—	70	210	
	15		—	40	120	
Propagation Delay Time $\bar{I}_0, I_1 \rightarrow 0$	5	$t_{pLH}$	—	150	450	ns
	10		—	70	210	
	15		—	40	120	
Propagation Delay Time $\bar{C}_D \rightarrow 0$	5	$t_{pHL}$	—	150	450	ns
	10		—	70	210	
	15		—	40	120	
Propagation Delay Time $C_D \rightarrow \bar{0}$	5	$t_{pLH}$	—	150	450	ns
	10		—	70	210	
	15		—	40	120	
Recovery Time $\bar{C}_D \rightarrow \bar{I}_0, I_1$	5	$t_{RCD}$	—	0	—	ns
	10		—	0	—	
	15		—	0	—	
Recovery Time $0, 0 \rightarrow \bar{I}_0, I_1$	5	$t_{RO}$	—	0	—	ns
	10		—	0	—	
	15		—	0	—	
Minimum Pulse Width $I_0$	5	$t_{wL0L}$	—	60	180	ns
	10		—	30	90	
	15		—	20	60	
Minimum Pulse Width $I_1$	5	$t_{wL1L}$	—	60	180	ns
	10		—	30	90	
	15		—	20	60	
Minimum Pulse Width $\bar{C}_D$	5	$t_{wCDL}$	—	40	120	ns
	10		—	20	60	
	15		—	15	45	
Output Pulse Width ( $R_t = 100\text{k}\Omega$ , $C_t = 0.002\mu\text{F}$ )	5	$t_{wO}$	—	208	—	$\mu\text{s}$
	10		—	208	—	
	15		—	208	—	
Output Pulse Width ( $R_t = 100\text{k}\Omega$ , $C_t = 0.1\mu\text{F}$ )	5	$t_{wO}$	—	10.4	—	ns
	10		—	10.4	—	
	15		—	10.4	—	
Output Pulse Width ( $R_t = 100\text{k}\Omega$ , $C_t = 10\mu\text{F}$ )	5	$t_{wO}$	—	1.04	—	s
	10		—	1.04	—	
	15		—	1.04	—	
Input Capacitance		$C_i$	—	—	7.5	pF
External Timing Resistance		$R_t$	5	—	1000	k $\Omega$
External Timing Capacitance		$C_t$	2000	—	no limit	pF

• Dynamic Signal Waveforms



■ Timing Diagram



- ①: Positive edge triggering
- ②: Positive edge re-triggering/pulse lengthening
- ③: Negative edge triggering
- ④: Reset (pulse shortening)
- ⑤:  $T = R_t \times C_t$