

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOCAD

DISTOO

REVISIIONS

DATE

DWN

APVD

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

101.19

[3.984]

99.06

[3.900]

39

40

9-146472-0

98.65

[3.884]

96.52

[3.800]

38

39

8-146472-9

96.11

[3.784]

93.98

[3.700]

37

38

8-146472-8

93.57

[3.684]

91.44

[3.600]

36

37

8-146472-7

91.03

[3.584]

88.90

[3.500]

35

36

8-146472-6

88.49

[3.484]

86.36

[3.400]

34

35

8-146472-5

85.95

[3.384]

83.82

[3.300]

33

34

8-146472-4

83.41

[3.284]

81.28

[3.200]

32

33

8-146472-3

80.87

[3.184]

78.74

[3.100]

31

32

8-146472-2

78.33

[3.084]

76.20

[3.000]

30

31

8-146472-1

75.79

[2.984]

73.66

[2.900]

29

30

8-146472-0

73.25

[2.884]

71.12

[2.800]

28

29

7-146472-9

70.71

[2.784]

68.58

[2.700]

27

28

7-146472-8

68.17

[2.684]

66.04

[2.600]

26

27

7-146472-7

65.63

[2.584]

63.50

[2.500]

25

26

7-146472-6

63.09

[2.484]

60.96

[2.400]

24

25

7-146472-5

60.55

[2.384]

58.42

[2.300]

23

24

7-146472-4

58.01

[2.284]

55.88

[2.200]

22

23

7-146472-3

55.47

[2.184]

53.34

[2.100]

21

22

7-146472-2

52.93

[2.084]

50.80

[2.000]

20

21

7-146472-1

50.39

[1.984]

48.26

[1.900]

19

20

7-146472-0

47.85

[1.884]

45.72

[1.800]

18

19

6-146472-9

45.31

[1.784]

43.18

[1.700]

17

18

6-146472-8

42.77

[1.684]

40.64

[1.600]

16

17

6-146472-7

40.23

[1.584]

38.10

[1.500]

15

16

6-146472-6

37.69

[1.484]

35.56

[1.400]

14

15

6-146472-5

35.15

[1.384]

33.02

[1.300]

13

14

6-146472-4

32.61

[1.284]

30.48

[1.200]

12

13

6-146472-3

30.07

[1.184]

27.94

[1.100]

11

12

6-146472-2

27.53

[1.084]

25.40

[1.000]

10

11

6-146472-1

24.99

[.984]

22.86

[.900]

9

10

6-146472-0

22.45

[.884]

20.32

[.800]

8

9

5-146472-9

19.91

[.784]

17.78

[.700]

7

8

5-146472-8

17.37

[.684]

15.24

[.600]

6

7

5-146472-7

14.83

[.584]

12.70

[.500]

5

6

5-146472-6

12.29

[.484]

10.16

[.400]

4

5

5-146472-5

9.75

[.384]

7.62

[.300]

3

4

5-146472-4

7.21

[.284]

5.08

[.200]

2

3

5-146472-3

4.67

[.184]

2.54

[.100]

1

2

5-146472-2

2.13

[.084]

—

—

—

1

5-146472-1

PLATING

G

F

E

NO. OF POSITIONS

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
E. BRANDBERG
13MAR97

CHK
G. DUBNICZKI
13MAR97

APVD
G. DUBNICZKI
13MAR97

TE Connectivity

DIMENSIONS:
mm [INCHES]

0 PLC ± —

1 PLC ± —

2 PLC ± 0.51[.02]

3 PLC ± 0.127[.005]

4 PLC ± 0.0127[.0005]

ANGLES ± —

TE Connectivity

TE Connectivity

NAME

PRODUCT SPEC

APPLICATION SPEC

—

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

MATERIAL

FINISH

WEIGHT

—

4

SEE TABLE

00779

146472

1:1

2

2

1

A1

4805 (3/11)